



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

3.3-3.8kW Single-Phase Switched PDU, LX Platform Interface, 208/220/230/240V Outlets (8 C13), C20 / L6-20P input, 8 ft. (2.43 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HVNET









Features

- 16/20A 208/230/240V Switched Power Distribution Unit / PDU with built-in web/network interface (Agency derated to 16A continuous)
- C20 inlet; 8.5 ft. / 2.6m C20 power cable with L6-20P plug adapter
- 8 switched C13 outlets
- 1U horizontal rackmount form factor
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage, frequency and loading information
- Digital display reports load level information in amps
- Supports user-specified alarm notification thresholds
- Pre-installed WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20)
 provides enhanced remote management capabilities
- PADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations
- IP-based Auto Probe detects lost connectivity and restores service autonomously
- Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities

Highlights

- Switched 16/20A
 208/220/230/240V PDU, 1U
 Horizontal Rackmount format
- Pre-installed WEBCARDLX with latest version of PADM20 for IPbased Auto Probe feature
- Visual current meter, reversible housing
- C20 inlet; 8ft / 2.4m C20 input cable with L6-20P adapter
- 8 C13 switched outlets with plug lock retention sleeves

Package Includes

- PDUMH20HVNET Switched
 PDU
- · Rack mounting hardware
- (8) Plug-lock inserts
- · Cord retainer
- Configuration cable
- (1) IEC C19-to-C20 AC
 Interconnection cable
- IEC C19-to-L6-20P plug adapter
- Owners' Manuals



- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332139283
PDU Type	Switched
INPUT	
PDU Input Voltage	208; 220; 230; 240
Recommended Electrical Service	20A 208/240V; 16A 230V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Phase	Single-Phase
Input Cord Length (ft.)	8
Input Cord Length (m)	2.44
ОИТРИТ	
Output Capacity Details	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V) / 16A total capacity; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13
Output Nominal Voltage	208; 220; 230; 240
Overload Protection	n/a
Customized Load Management Receptacles	8 individually switched output receptacles
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps





Front Panel LEDs	8 LEDs display power on-off status for each output receptacle
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
Material of Construction	Metal
Minimum Required Rack Depth (cm)	43.43
Minimum Required Rack Depth (inches)	17.1
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	13.72 x 52.58 x 56.90
Shipping Dimensions (hwd / in.)	5.40 x 20.70 x 22.40
Shipping Weight (kg)	6.53
Shipping Weight (lbs.)	14.40
Unit Dimensions (hwd / cm)	4,4 x 44 x 37,52
Unit Dimensions (hwd / in.)	1.72 x 17.33 x 14.77
Unit Weight (kg)	4.08
Unit Weight (lbs.)	9.00
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems
SPECIAL FEATURES	
High Availability PDU Features	Auto Probe Monitoring and Reboot (included)
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), CE (IEC 60950), RoHS compliant, TAA compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

https://www.tripplite.com/products/product-certification-agencies