



## SL-86-911-TP

### MOUNTABLE KEYBOARD WITH TOUCHPAD

The SL-86-911-TP keyboard is designed for vehicle mount in emergency, police, service, transport trucks and marine vessels. Features include a user-friendly integrated touchpad, backlit keys for low-light environments, a one-touch emergency key and mounting holes. The new, easy-to-use integrated touchpad was created to meet public demand for a user-friendly alternative to the traditional HulaPoint™ device. Features: One-Touch Emergency Key PS/2 or USB configurations available

### Product Code SL-86-911-TP

CERTIFICATIONS	NEMA 4X, CE UL60950, FCC Part 15 Class B
SHOCK	3x11 ms pulses of 50g on each of 3 axes
CABLE	LENGTH: 4 ft coiled (1.2m) DESIGN: "Y" PS/2 (providing separate keyboard and mouse connections), or Single-Cable USB
KEY SWITCH	MATERIAL: Industrial Silicone rubber LIFE: Greater than 10 million cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 7.05 oz +/- 1.06 oz (200g +/- 30g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2kHz DURATION OF TEST PER AXIS: 3 hours
POWER	PS/2: KEYBOARD: 200mA@5V (from Keyboard port) TOUCHPAD: 10mA@5V (from Mouse port) USB: 210mA@5V (from CPU port)
COMPATABILITY	PS/2 KEYBOARD/TOUCHPAD: All Windows Operating Systems USB KEYBOARD/TOUCHPAD: All Windows and Macintosh OS
TEMPERATURE RANGE	Storage -40C to +90C (-40F to +194F) Operating -40C to +70C (-40F to +158F)
WEIGHT	2.25 lbs +/- 0.10 lbs (1.02 kg +/- 0.05 kg)
WARRANTY	1 Year Limited Warranty
HUMIDITY	100% Humidity Resistant
DIMENSIONS	11.39" x 7.30" x 1.87" (w-h-d) 289.56mm x 185.42mm x 47.24mm
MODEL NUMBERS	SL-86-911-TP-PS2: With PS/2 cable SL-86-911-TP-USB: With USB cable