


## Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - SC/SC - 1 m

Product ID: 50FIBSCSC1



The 50FIBSCSC11m LSZH SC to SC Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This SC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

### Features

- Immune to electrical interference
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

	Warranty	Lifetime
<b>Hardware</b>	Fiber Size	50/125
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
<b>Performance</b>	Fiber Classification	OM2
	Type	Multi Mode
<b>Connector(s)</b>	Connector A	1 - Fiber Optic SC Duplex Male
	Connector B	1 - Fiber Optic SC Duplex Male
<b>Physical Characteristics</b>	Cable Length	3.3 ft [1 m]
	Color	Orange
	Product Length	3.3 ft [1 m]
	Weight of Product	1.1 oz [31 g]
<b>Packaging Information</b>	Package Height	0.7 in [17 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	1.4 oz [40 g]
<b>What's in the Box</b>	Included in Package	1 - 1m Multimode 50/125 Duplex Fiber Patch Cable SC - SC

Product appearance and specifications are subject to change without notice.