

Lenovo recommends Windows Vista® Business.

**THINKCENTRE® M57 & M57p:**  
ENGINEERED TO PERFORM.  
GREAT FOR YOUR BALANCE SHEET.

**MANAGEABILITY:**

- ThinkCentre M57 and M57p offer the strongest manageability in the ThinkCentre family
- Latest Intel® vPro™ processor technology: AMT 3.0 new features including industry standard WS-MAN/DASH, the next-generation management standard
- ThinkVantage® Rescue and Recovery™ provides simple-to-use effective backup and recovery for end users; including a pre-OS environment for recovering when the primary OS will not boot

**EFFICIENCY:**

- Energy Star 4.0 compliant with all form factors (select models)
- Intel® vPro™ processor technology with increased performance and lower power consumption (M57p models)
- Less heat emission for improved power supply reliability
- Less maintenance and longer hardware life to improve customer TCO

**STABILITY:**

- Global models for easy worldwide deployments
- Platform & Software image stability
- Industry-leading IBM service and support

**SECURITY:**

- TPM 1.2 supports Windows Vista® BitLocker function and provides a central location to manage credentials thereby denying access to illegitimate users
- USB Ports that can be individually switched on/off
- Chassis Intrusion switch
- Combine ThinkVantage® Client Security Solution with an optional fingerprint reader keyboard to create the most secure industry-standard PC available.

**lenovo**™

□ NEW WORLD. NEW THINKING.™

Lenovo recommends Windows Vista® Business.

## THINKCENTRE M57 & M57p: THE WORLD'S BEST ENGINEERING IN ACTION.

ThinkCentre M57 and M57p desktops are engineered exclusively for the way you work. Equipped with the latest Intel® Dual Core/Quad Core technology, desktop performance is truly maximized. With the latest Intel® vPro™ processor technology and platform stability, the M57p provides outstanding manageability. Superior security features like USB ports that can be disabled individually, TPM capability across all platforms and ThinkVantage® Client Security Solution make the M57 and M57p by far the most secure ThinkCentre desktops. In addition, features like complete hard drive back-up and immediate System Recovery safeguard your data at all times.



### MAXIMIZED PERFORMANCE AND OPTIMIZED FEATURES:

The latest Intel® Dual Core/Quad Core technology maximizes your performance. The discrete graphics card in compliance with DirectX10 enhances performance and meets the new Windows Vista® Premium logo requirements. E-SATA support provides you with a 5x higher transfer speed with external HDD instead of a USB. 4 DIMMs slots + system memory of up to 8 GB, renders flexibility, expandability and higher performance feasibility.

### EXQUISITELY DESIGNED SMALL FORM FACTOR:

ThinkCentre M57 and M57p desktops have a totally new small form factor design. The Discrete graphics card provides you with better graphic performance. 4 DIMMs offer more expandability. Moreover, the standard 280W auto-sensing PSU makes the desktops globally compatible. ThinkCentre M57 and M57p also come in Ultra Small Form Factor, Desktop and Tower.

### IMPROVED ACOUSTIC DESIGN:

Lenovo's thoughtful airflow design coupled with Intel® QST (Quiet System Technology) make ThinkCentre M57 and M57p desktops up to 5dB quieter and cooler than the previous desktops.

# Lenovo recommends Windows Vista® Business.

## Machine type Tower:

(6010, 6069, 6075, 6081, 6086, 9174)

## Machine type Desktop:

(6008, 6068, 6074, 6079, 6082, 9172)

## Machine type Small Form Factor:

(6019, 6066, 6072, 6077, 6087, 9181)

## Machine type Ultra Small Form Factor:

(6062, 6065, 6071, 6076, 6089, 9182)

## THINKCENTRE M57 SPECIFICATIONS

### Processor

Intel® Core™2 Quad Processors  
Intel® Core™2 Duo Processors  
Intel® Pentium® Dual-Core Processors  
Intel® Celeron® Processors

### Preloaded operating system<sup>3</sup>

Genuine Windows® XP Professional  
Genuine Windows Vista® Home Basic  
Genuine Windows Vista® Business

### Hard disk drive<sup>2</sup>

SATA II drive support, up to 500 GB

### Memory<sup>1</sup>

DDR2 667MHz/800 MHz memory, up to 8 GB

### Core chipset

Intel® Q35 Express Chipset, up to 1333 MHz FSB

### Optical drive

DVD-ROM, Combo, DVD Recordable

### Integrated communications

Intel® 82566DM Gigabit Ethernet Controller

### Expansion

#### Tower:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/2 PS2/E-SATA port as optional, 2 FH  
PCI expansion slots, 1 FH PCI-e 1x and 1 FH PCI-e  
16x, 2 Front audio ports: Headphone and Microphone,  
3 Rear audio ports: Line-in, Line-out and Microphone

### Desktop:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/2 PS2/E-SATA port as optional, 2 LP  
PCI expansion slots, 1 LP PCI-e 1x and 1 LP PCI-e 16x,  
2 Front audio ports: Headphone and Microphone,  
3 Rear audio ports: Line-in, Line-out and Microphone

### SFF:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/E-SATA, 1 LP PCI expansion slot,  
1 LP PCI-e 16x, 2 Front audio ports: Headphone and  
Microphone, 3 Rear audio ports: Line-in, Line-out  
and Microphone

### USFF:

8 USB Ports (2 Front/6 Rear), 1xParallel/1xSerial/  
Audio/E-SATA, 1 FH PCI Expansion slot, 2 Front  
audio ports: Headphone and Microphone, 2 Rear  
audio ports: Line-in and Line-out

### Dimensions

#### Tower:

Height: 432 mm (17 in.)  
Width: 175 mm (6.9 in.)  
Depth: 400 mm (15.7 in.)

#### Desktop:

Height: 107 mm (4.21 in.)  
Width: 325 mm (12.8 in.)  
Depth: 410 mm (16.14 in.)

#### Small Form Factor:

Height: 99 mm (3.9 in.)  
Width: 317 mm (12.5 in.)  
Depth: 341 mm (13.4 in.)

#### Ultra Small Form Factor:

Height: 89 mm (3.5 in.)  
Width: 273 mm (10.7 in.)  
Depth: 276 mm (10.9 in.)

### Keyboard

Preferred Pro USB Keyboard, Optional: Preferred Pro  
USB Fingerprint Keyboard

### Graphic Card

Integrated: Intel® GMA 3100 (DX9),

Discrete:

ATI Radeon HD 2400 Pro 128M Low Profile

(DMS59+TV-Out)

ATI Radeon HD 2400 Pro 128M Full Height

(DMS59+TV-Out)

ATI Radeon HD 2400 XT 256M Low Profile

(DMS59+TV-Out)

ATI Radeon HD 2400 XT 256M Full Height

(DMS59+TV-Out)

ATI Radeon HD 2600 XT 512M Full Height

(2\*DVI-I+TV-Out)

All discrete graphic cards are DirectX10 compliant

All models are able to support DID via ADD2 card

### Limited warranty<sup>4</sup>

Up to 4 years

### Included software (preloaded in Vista)<sup>5</sup>

Adobe® Acrobat Reader

Diskeeper Lite

Latest ThinkVantage Technologies suite

Microsoft® Office 2007 Trial

Microsoft Windows® Live Portal

Norton™ Internet Security (90 days of virus definitions)

PC Doctor for Windows®

### Note:

- 1: Ultra Small Form Factor supports up to 4 GB.  
8 GB support is based on physical level, some  
operating systems can only use a maximum of 3/4 GB
- 2: For USFF, PATA Slim DVD-ROM and DVD  
Recordable will be supported
- 3: Ultra Small Form Factor doesn't support discrete  
graphic card
- 4: ATI Radeon HD 2600XT 512 MB graphic card is  
supported by Tower
- 5: For Small Form Factor Intel® Core™2 Quad  
Processors will be available after January 2008

## Machine type Tower:

(9013, 9019, 9088, 9160, 9164, 9194)

## Machine type Desktop:

(9012, 9018, 9087, 9096, 9163, 9193)

## Machine type Small Form Factor:

(6064, 6067, 6073, 6078, 6088, 9196)

## Machine type Ultra Small Form Factor:

(9011, 9014, 9071, 9089, 9162, 9303)

## THINKCENTRE M57p SPECIFICATIONS

### Processor

Intel® Core™2 Duo Processors (E6x50 series)

### Preloaded operating system<sup>3</sup>

Genuine Windows® XP Professional  
Genuine Windows Vista® Home Basic  
Genuine Windows Vista® Business

### Hard disk drive<sup>2</sup>

SATA II drive support, up to 500 GB

### Memory<sup>1</sup>

DDR2 667 MHz/800 MHz memory, up to 8 GB

### Core chipset

Intel® Q35 Express Chipset, up to 1333 MHz FSB

### Optical drive

DVD-ROM, Combo, DVD Recordable

### Integrated communications

Intel® 82566DM Gigabit Ethernet Controller

### Expansion

#### Tower:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/2 PS2/E-SATA port as optional, 2 FH  
PCI expansion slots, 1 FH PCI-e 1x and 1 FH PCI-e  
16x, 2 Front audio ports: Headphone and Microphone,  
3 Rear audio ports: Line-in, Line-out and Microphone

### Desktop:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/2 PS2/E-SATA port as optional, 2 LP  
PCI expansion slots, 1 LP PCI-e 1x and 1 LP PCI-e 16x,  
2 Front audio ports: Headphone and Microphone,  
3 Rear audio ports: Line-in, Line-out and Microphone

### SFF:

10 USB Ports (2 Front/6 Rear/2 Internal), 1 Parallel/  
1 Serial/Audio/E-SATA, 1 LP PCI expansion slot,  
1 LP PCI-e 16x, 2 Front audio ports: Headphone and  
Microphone, 3 Rear audio ports: Line-in, Line-out  
and Microphone

### USFF:

8 USB Ports (2 Front/6 Rear), 1xParallel/1xSerial/  
Audio/E-SATA, 1 FH PCI Expansion slot, 2 Front  
audio ports: Headphone and Microphone, 2 Rear  
audio ports: Line-in and Line-out

### Dimensions

#### Tower:

Height: 432 mm (17 in.)  
Width: 175 mm (6.9 in.)  
Depth: 400 mm (15.7 in.)

#### Desktop:

Height: 107 mm (4.21 in.)  
Width: 325 mm (12.8 in.)  
Depth: 410 mm (16.14 in.)

#### Small Form Factor:

Height: 99 mm (3.9 in.)  
Width: 317 mm (12.5 in.)  
Depth: 341 mm (13.4 in.)

#### Ultra Small Form Factor:

Height: 89 mm (3.5 in.)  
Width: 273 mm (10.7 in.)  
Depth: 276 mm (10.9 in.)

### Keyboard

Preferred Pro USB Keyboard, Optional: Preferred Pro  
USB Fingerprint Keyboard

### Graphic Card

Integrated: Intel® GMA 3100 (DX9),

Discrete:

ATI Radeon HD 2400 Pro 128M Low Profile

(DMS59+TV-Out)

ATI Radeon HD 2400 Pro 128M Full Height

(DMS59+TV-Out)

ATI Radeon HD 2400 XT 256M Low Profile

(DMS59+TV-Out)

ATI Radeon HD 2400 XT 256M Full Height

(DMS59+TV-Out)

ATI Radeon HD 2600 XT 512M Full Height

(2\*DVI-I+TV-Out)

All discrete graphic cards are DirectX10 compliant

All models are able to support DID via ADD2 card

### Limited warranty<sup>4</sup>

Up to 4 years

### Included software (preloaded in Vista)<sup>5</sup>

Adobe® Acrobat Reader

Diskeeper Lite

Latest ThinkVantage Technologies suite

Microsoft® Office 2007 Trial

Microsoft Windows® Live Portal

Norton™ Internet Security (90 days of virus definitions)

PC Doctor for Windows®

### Manageability and Security

All M57p Form Factor support the latest Intel® vPro™  
technology with AMT3.0/VT/TXT5

### Note:

- 1: Ultra Small Form Factor supports up to 4 GB.  
8 GB support is based on physical level, some  
operating systems can only use a maximum of 3/4 GB
- 2: For Ultra Small Form Factor, PATA Slim DVD-ROM  
and DVD Recordable will be supported.
- 3: Ultra Small Form Factor doesn't support discrete  
graphic card
- 4: ATI Radeon HD 2600XT 512 MB graphic card is  
supported by Tower
- 5: AMT (Active Management Technology), VT  
(Virtualization Technology), TXT (Trusted Execution  
Technology) and VT/TXT feature available depends  
on ISV's supporting

Lenovo recommends Windows Vista® Business.

DESIGNED TO DO THE  
UNEXPECTED  
MAKE AN AMAZING PC  
EVEN BETTER.



THINKCENTRE M57/M57p ACCESSORIES:



**THINKVISION TFT RADIAL ARM** (919K4464) Allows ergonomic positioning by enabling easy movement of the monitor to the desired height, angle and position.



**LENOVO LASER MOUSE** (41U3074) Utilizes optical tracking technology for precision control.



**THINKVISION USB SOUNDBAR** (40Y7616) Dual speakers with two watts of total Root Mean Square (RMS) output for full range business audio sound, compatible with 15" to 22" Lenovo monitors.



**1 GB PC2-5300 667 MHz DDR2 SDRAM UDIMM MEMORY** (73P4984) Offers maximum data transfer rates up to 5300 MB/sec (1) to enhance performance of memory intensive applications such as streaming video, graphics and CAD programs.



**KENSINGTON MICROSAVER SECURITY CABLE LOCK FROM LENOVO** (73P2582) Is a 6-foot (1.8 m) steel composite cable with Kevlar brand fiber, equipped with a 7-inch diameter lock barrel.



**LENOVO L220X WIDE MONITOR** (4433HB2) enables users to view images in a 16x10 wide aspect ratio and is best suited for general business applications and multiple-monitor environments.

800 938 838  
lenovo.com/hk

**lenovo**<sup>™</sup>  
NEW WORLD. NEW THINKING.<sup>™</sup>

© Lenovo 2008. All Rights Reserved. All offers subject to availability. Lenovo reserves the right to alter product offerings and specifications at any time without notice. Lenovo is not responsible for photographic or typographic errors. For a copy of applicable product warranties, visit [www.lenovo.com/hk/warranty](http://www.lenovo.com/hk/warranty).  
Lenovo makes no representation or warranty regarding third-party products or services. Lenovo may not offer the products, services or features discussed in this document in all countries. Information is subject to change without notice. Consult your local Lenovo representative for information on offerings available in your area. IBM and Lenovo logos and trademarks used under licence. Contact Lenovo for details. Certain IBM and ThinkCentre logo products are not manufactured, warranted or supported by IBM or Lenovo. Lenovo makes no representation or warranty regarding third-party products or services. Lenovo, the Lenovo logo, ImageUltra, PS/2, Rescue and Recovery, ScrollPoint, Secure Data Disposal, System Migration Assistant, ThinkCentre and ThinkVantage are trademarks of Lenovo. All rights are reserved. Lenovo's marks may not be used in connection with any product or service that is not Lenovo's in any manner that is likely to cause confusion, or in any manner that disparages or discredits Lenovo. IBM, the IBM logo, Lotus, Lotus Notes and Lotus SmartSuite are trademarks of International Business Machines Corporation in the United States, other countries, or both and are used under licence. Celeron, Celeron Inside, Centrino, Centrino Logo, Core Inside, Intel, Intel Logo, Intel Core, Intel Inside, Intel Inside Logo, Intel Viiv, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, Xeon, and Xeon Inside are trademarks of Intel Corporation in the U.S. and other countries. Java, JRE, Sun and all Java-based trademarks are trademarks of Sun Microsystems, Inc. in the United States, other countries, or both. Linux is a trademark of Linus Torvalds in the United States, other countries, or both. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation in the United States, other countries, or both. Other company, product and service names may be trademarks, or service marks of others. Footnotes: [1] Memory: Total accessible memory will be less and will vary depending on the system configuration. [Maximum capacity may require purchase of optional component] [2] Hard disk drive: GB = billion bytes. Accessible capacity is less; up to 5.1GB is service partition. [Maximum capacity may require the replacement of installed component with largest supported component available. [3] Operating system: Level of support varies by operating system. Operating systems not preloaded on the system may not provide full-feature functionality. Refer to [lenovo.com/pc/support](http://lenovo.com/pc/support) and enter your machine type and model number for more information. [4] Lenovo limited warranty: Telephone support may be subject to additional charges. [5] Included Software: may differ from its retail version (if available) and may not include user manuals or all program functionality. License agreements may apply.

Visit [lenovo.com/safecomputing](http://lenovo.com/safecomputing) periodically for the latest information on safe and effective computing.