



HP ProLiant ML115 G5 Server

Data sheet

Empower your business with an affordable, ready-to-grow server based on the reliable HP ProLiant platform and powered by AMD processors.

Keep your business moving—and stay on budget

To keep your business moving forward, you need servers that are reliable, versatile, and easy to manage. To keep pace with changing IT demands, your business needs servers that allow you to add capacity and deploy upgrades quickly.

With the HP ProLiant ML115 G5 server you get all of this without upsetting your budget. This entry-level server provides a resource-efficient computing solution designed to meet both the IT and the budgetary requirements of your business.

Reliability and versatility

An affordable, functional server, the ProLiant ML115 G5 brings you the proven reliability of ProLiant technology and Quad-Core AMD Opteron™ processor or Dual-Core and Single-Core AMD Athlon™ processor. This expandable, ready-to-grow server includes one PCI and three PCI-Express slots, four DIMM slots, and four bays for hard disk drives.

With its versatile configurations, the ProLiant ML115 G5 is ideal for a wide range of business needs. This is a good server for file and print serving, Web messaging, business applications and databases, and shared Internet access and LAN infrastructure. With its optional, cost-effective HP ProLiant Lights-Out 100c Remote Management Card, the ProLiant ML115 G5 is a good choice for remote sites, branch offices, or just managing from home as well.



"The new HP ProLiant ML115 G5 tower server based on AMD Opteron™ processors with DDR2 provides outstanding performance-per-watt."

Randy Allen,
Corporate Vice President,
Server and Workstation Division, AMD

Key features and benefits

Proven HP dependability and support

- HP has built a reputation of dependability by conducting some of the most rigorous and thorough testing in the industry.
- Quality starts with design and is fine-tuned during manufacturing.
- For additional performance and enhanced data security features, the ProLiant ML115 G5 offers Serial ATA (SATA) RAID 0, 1, and 5 from the embedded system board controller.

Expandable to grow with changing business needs

- This powerful, yet simple platform provides all relevant server features in an easy-to-use and easy-to-afford package.
- With Quad-Core AMD Opteron™ processor or Dual-Core and Single-Core AMD Athlon™ processor, DDR II ECC memory, PCI and PCI-Express slots, serial port, four hard disk drive bays, and eight USB 2.0 ports, the ProLiant ML115 G5 delivers both off-the-shelf functionality and easy expandability for your business.

A true server at a desktop price

- The ProLiant ML115 G5 is designed from the ground up as a true server, providing reliability and expandability for your business.
- The optional ProLiant Lights-Out 100c Remote Management Card delivers remote management functionality at a cost-effective price.
- For an enhanced computing solution, the ProLiant ML115 G5 is available with USB DAT tape drives for value-based backup, UPS options for enhanced security, and an optional drive key through front USB or internal USB connectivity for ease of booting.

HP Services

When Technology Works. Business Works

The challenge of virtually every IT organization is similar: To develop and maintain an agile, efficient server infrastructure that delivers the service levels your business needs.

HP Technology Services offer a comprehensive portfolio of HP Care Pack Services to help design, deploy, manage, and support your IT environment, enabling cost-effective upgrades to standard warranty with easy-to-buy, easy-to-use support packages.

Minimum Recommended HP Care Pack offerings

- Three-year, next-business-day response onsite 9-hour x 5-day coverage, hardware support
- Hardware Installation only

Enhanced service level Care Pack offerings

- Three-year same-business-day 4-hour response onsite 13-hour x 5-day coverage, hardware support
- Hardware Installation plus operating system installation and startup

Benefit from HP Care Pack Services helping you:

- Reduce deployment time and manage ProLiant server solutions smoothly and efficiently
- Increase uptime and performance of servers availability to your business
- Detect, diagnose, and repair problems to quickly save time, money, and resources

For more information visit

www.hp.com/services/proliantservices or
www.hp.com/go/proliant/carepack

Financial services

HP Financial Services provides innovative financing and financial asset management programs to help customers cost-effectively acquire, manage, and ultimately retire their HP solutions. For more information on these services, please contact your local HP representative or visit

www.hp.com/go/hpfinancialservices

HP ProLiant ML115 G5 Server



Processor and memory

Number of processors	1
Processors supported	Quad-Core AMD Opteron™ processor: Model 1356, 2.3 GHz, 2 MB Model 1354, 2.2 GHz, 2 MB Model 1352, 2.1 GHz, 2 MB Dual-Core AMD Athlon™ processor: Model 4450B, 2.3 GHz, 1 MB Single-core AMD Athlon™ processor: Model 1640B, 2.7 GHz, 512 KB
Processor cores	Single, dual, and quad core
Cache	2 MB Level 2 cache (AMD Opteron™ 1300 series) 1 MB Level 2 cache (AMD Athlon™ 4450B models) 512 KB Level 2 cache (AMD Athlon™ 1640B models)
Maximum processor speed	2.7 GHz
Memory type	PC2-6400 unbuffered DDR2 ECC 800 MHz
Standard memory	1 GB
Maximum memory	8 GB
Memory protection	ECC
I/O slots	Four total I/O slots: one 3.3V PCI and three PCI Express (1x1, 1x8 and 1x16)

Storage

Storage type	Non-hot plug 3.5-inch SAS Non-hot plug 3.5-inch SATA
Drives supported	Up to 4: Non-hot plug LFF SAS 15K 450/300/146 GB Non-hot plug LFF SATA 7.2K 1 TB/500 GB/250 GB/160 GB
Maximum Internal Storage	1.8 TB SAS; 4.0 TB SATA
Maximum internal drives	4
Removable media bays	2
Expansion slots	4
Storage controller	SATA Models: Integrated 6 ports SATA controller with embedded RAID (4 ports available for Hard Disks) SAS Models: HP SC40Ge Host Bus Adapter with RAID 0, 1 support, FIO

Operating systems

OS choices	Microsoft® Windows® Server 2003 R2 Microsoft® Windows® Small Business Server 2003 Microsoft® Windows® Server 2008 Microsoft® Windows® Small Business Server 2008 Microsoft® Windows® Essential Business Server 2008 Red Hat Enterprise Linux SUSE Linux Enterprise Server
------------	---

For additional OS information, please visit www.hp.com/go/ossupport

Deployment	
Form factor	Tower with rack-mount option kit
Ports	8 total (4 rear, 2 front panel, 2 internal (one for USB Tape connectivity))
Rack height	4U
Networking	Embedded NC105i Express Gigabit Ethernet Server Adapter
Remote management	Standard IPMI 2.0 reporting Lights-Out 100c Remote Management Card (optional)
Redundant power supply	Not available
Redundant fans	1-Non-redundant system fan shipped standard 1-Non-redundant CPU heat sink fan shipped standard
Warranty (parts/labor/onsite)	Standard: 1-year/1-year/1-year Asia Pacific (excluding Japan): 3-year/1-year/1-year

For additional technical specifications and ordering information, please visit the ProLiant ML115 G5 QuickSpecs at http://h18004.www1.hp.com/products/quickspecs/13013_div/13013_div.html

The HP ProLiant ML115 G5 is an affordable, ready-to-grow server, powered by AMD processors—all for the price of a typical desktop computer. To learn more about the ML115 G5 server, visit www.hp.com/servers/ml115-g5

Share with colleagues



Get connected

www.hp.com/go/getconnected

Current HP driver, support, and security alerts
delivered directly to your desktop

© Copyright 2007, 2008, 2010 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

AMD, Athlon, and Opteron are trademarks or registered trademarks of Advanced Micro Devices or its subsidiaries in the United States and other countries. Microsoft and Windows are U.S. registered trademarks of Microsoft Corporation.

4AA1-0483ENW, Created February 2007; Updated March 2010, Rev. 5

