


Lenovo recommends Windows Vista® Business.



THINKCENTRE® M57e:  
**THE NO-HASSLE DESKTOP.**

STABLE, MANAGEABLE AND SECURE



SECURITY

- Disable USB ports in the BIOS for physical data control
- Rescue and Recovery™ for one button recovery if the system crashes
- Computrace Ready for Integrated Asset Management & Recovery

FEATURE FILLED

- Latest Intel® Core™2 Duo and Core™2 Quad processors
- Numerous connectivity ports and expansion bays/slots
- Graphics card support on Tower and Small Form Factors

STABILITY AND MANAGEABILITY

- Easy to manage and maintain without an entire IT department
- ThinkVantage® Technologies help automate critical system tasks
- Award-winning service and support gives you peace of mind

SPEND YOUR TIME MANAGING  
YOUR BUSINESS, NOT YOUR  
COMPUTER.

**lenovo**™

Lenovo recommends Windows Vista® Business.

## THINKCENTRE M57e: COST-EFFECTIVE. SECURE. FULLY LOADED.

The ThinkCentre M Series is the ultimate small business tool. Engineered to meet your computing needs within budget, the M57e ensures you don't settle for less. There is plenty of performance on tap, supporting up to Intel® Core™2 Quad processors and ATI Radeon™ HD graphics solutions tailored to fit your needs.

The ThinkCentre M Series has always combined legendary Think design with Lenovo's engineering in a high value package, and the M57e takes this tradition to a new level. Like the Tower, the M57e Small Form Factor now supports a graphics adapter, and all M57e models are based on a re-designed platform that runs cooler and quieter. Lenovo's unique ThinkVantage® Technologies like Rescue and Recovery™ and Client Security Solution help you make the most of your machine, while our award-winning service and support protects your investment and gives you peace of mind.



Rescue and Recovery™ software combined with a lock slot and padlock loop locking option plus the ability to disable USB ports in BIOS makes the M57e a secure desktop.

Built to perform, the latest M57e models feature Intel® Core™2 Duo and Intel® Core™2 Quad processors backed by the Intel® G31 chipset and high speed DDR2 memory. Dual monitor support is available with the low cost DVI-I Connection Adapter or with ATI Radeon™ HD discrete graphic solutions.

Lower energy consumption means less heat is produced and less noise is generated keeping the system cool.

# Lenovo recommends Windows Vista® Business.

## Tower Machine Types

9948, 9439

## Desktop Machine Types

9949, 9481

## Small Form Factor Machine Types

9952, 9482

### THINKCENTRE M57e SPECIFICATIONS

#### Processors

Intel® Core™2 Quad processor  
Intel® Core™2 Duo processor  
Intel® Pentium® dual-core processor  
Intel® Celeron® processor

#### Preloaded Operating System<sup>3</sup>

Genuine Windows Vista® Ultimate 32  
Genuine Windows Vista® Business 32  
Genuine Windows Vista® Business 64  
Genuine Windows Vista® Home Premium 32  
Genuine Windows Vista® Home Basic 32  
Genuine Windows® XP Professional

#### Serial ATA II Hard Drive<sup>4</sup>

80 GB, 160 GB, 250 GB, 320 GB,  
500 GB 7200 rpm

#### Memory<sup>5</sup>

2 DDR2 667/800 DIMM slots, up to 4 GB

#### Core Chipset

Intel® G31 Express, up to 1333 MHz FSB

#### Optical Drive

DVD-ROM  
CD-RW/DVD-ROM Combo  
Super Multiburner DVD-RW

#### Integrated Communications<sup>2</sup>

Marvell® Giga LAN 8056

#### Ports

8 USB 2.0 (2 front, 4 rear, 2 internal); 2 PS/2® ports; Headphone & microphone on front; Line in, Line out & Microphone on rear; 1 serial (2<sup>nd</sup> serial optional); 1 parallel

#### Expansion Slots/Bays

Tower:

(1) PCI-E x16 slot; (1) PCI-E x1 slot; (2) PCI slot; (2) 5.25" external bay; (1) 3.5" external bay; (2) 3.5" internal bay

Desktop:

(1) PCI-E x16 slot; (1) PCI-E x1 slot; (2) PCI slot; (1) 5.25" external bay; (1) 3.5" external bay; (1) 3.5" internal bay

SFF:

(1) PCI-E x16 slot; (1) PCI slot; (1) 5.25" external bay; (1) 3.5" external bay (slim); (1) 3.5" internal bay; slots are low profile

#### Dimensions<sup>6</sup>

Tower:

Height: 440 mm  
Width: 175 mm  
Depth: 402 mm

Desktop:

Height: 108 mm  
Width: 331 mm  
Depth: 412 mm

SFF:

Height: 99 mm  
Width: 317 mm  
Depth: 355 mm

#### Graphics Solution

Integrated:

Intel® GMA 3100 (all form factors)

Discrete:

ATI Radeon™ HD 2600 XT 512 MB; (2) DVI-I; TV-out (card available on Tower only)  
ATI Radeon HD 2400 XT 256 MB; DMS-59 for dual DVI or VGA; TV-out  
ATI Radeon HD 2400 Pro 128 MB; DMS-59 for dual DVI or VGA; TV-out

Graphic notes:

All form factors support Dual Independent Display. DID is supported via ADD2 card with (1) DVI-D or (1) VGA

#### Keyboard



Preferred Pro USB keyboard  
Preferred Pro USB Fingerprint keyboard

#### Limited Warranty<sup>1</sup>

1 year or 3 years

#### Included Software (Preloaded in Vista)<sup>7</sup>


Adobe® Acrobat Reader  
Diskeeper Lite  
Google™ Picasa™  
Latest ThinkVantage® Technologies Suite  
Microsoft® Office 2007 Trial  
Microsoft® Windows Live Portal  
Norton™ Internet Security (90 days of virus definitions)  
PC Doctor for Windows®



Lenovo recommends Windows Vista® Business.

## MAKE AN AMAZING PC EVEN BETTER.

THINKCENTRE M57e ACCESSORIES



### SYSTEM MEMORY



PC2-5300 memory is designed for current and future DDR2 systems  
– 1 GB PC2-5300 667 MHz DDR2 SDRAM UDIMM (P/N 73P4984)  
– 2 GB PC2-5300 667 MHz DDR2 SDRAM UDIMM (P/N 73P4985)  
Boost System Performance, Enhance Multi-tasking Usability,  
Extend System Useful Life and Ensure Compatibility

### LENOVO LASER MOUSE

(P/N 41U3074)

- 2000 dpi resolution (user selectable to 1600, 800 or 400 dpi)
- Fully programmable tilt wheel and buttons
- Ambidextrous design for both right and left-handed usage



### THINKCENTRE AND LENOVO SUPER MULTIBURNER DRIVE (SERIAL/ATA)

(P/N 41N5620)

- High capacity, read/write removable storage
- Perfect for file sharing, backup, audio CD creation, software installations, DVD Video playback and recording
- Writes both DVDs and CDs



### LENOVO 220X MONITOR AND THE THINKVISION USB SOUNDBAR

LENOVO 220X MONITOR (P/N 4433HB2)

THINKVISION USB SOUNDBAR (P/N 40Y7616)

- Dual speakers provides for full range business audio sound
- Power and audio volume are controlled directly from the soundbar



### LENOVO USB MULTIMEDIA HEADSET

(P/N 40Y8518)

- Detachable USB adapter with integrated sound card
- Virtual 360° sound experience
- Adjustable headband for a perfect fit
- Ear pads that automatically adjust and tilt for maximum comfort



### 1 GB / 2 GB / 4 GB LENOVO USB 2.0 SECURITY MEMORY KEY

- LENOVO USB 2.0 SECURITY MEMORY KEY – 1 GB (P/N 41U5118)
- LENOVO USB 2.0 SECURITY MEMORY KEY – 2 GB (P/N 41U5119)
- LENOVO USB 2.0 SECURITY MEMORY KEY – 4 GB (P/N 41U5120)
- Supported on all notebooks, desktops, docks, and USB hubs under Vista®, Windows® XP & Windows® 2000



### LENOVO ENHANCED PERFORMANCE WIRELESS KEYBOARD AND MOUSE

(P/N 73P40673)

- Programmable hot-keys to instantly launch your favorite applications
- Multimedia Pod for controlling your favorite media player and Internet forward and backward keys
- High definition optical sensor delivers accurate and precise control
- Wireless 2.4 GHz R/F keyboard and mouse with 10-meter range



### THINKVISION RFT RADIAL ARM

(P/N 19K4464)

- The hydraulic cylinder design 'floats' monitors that weight between 8 to 22 pounds
- Adjust monitor height and position with fingertips



### 256 MB ATI HD 2400XT DUAL-VGA OR DUAL-DVI, TV-OUT ADAPTER

(P/N 43R1962)

- Attach two monitors for multi-monitoring environments using Dual-VGA or Dual-DVI
- Supports hardware decode for Blu-Ray via Unified Video Decoder H.264 and VC-1



### KENSINGTON MICROSAVER SECURITY CABLE LOCK FROM LENOVO

(P/N 73P2582)

- Super-strong, steel composite cable with carbon tempered steel core patented T-bar lock provides superior lock strength and theft protection



800 938 838  
lenovo.com/hk

**lenovo**™

**Availability:** Offers, prices, specifications and availability may change without notice. Lenovo is not responsible for photographic or typographic errors. **Pricing:** Does not include tax, shipping and handling, or recycling fees. Reseller prices may vary. **Warranty:** For a copy of applicable warranties, visit [www.lenovo.com/hk/warranty](http://www.lenovo.com/hk/warranty). Lenovo makes no representation or warranty regarding third party products or services. **Footnotes:** [1] **Limited warranty:** Telephone support may be subject to additional charges. [2] **11n Wireless LAN Mini-PCI Express Adapters:** are based on the Draft Release Version 1.0 of the IEEE 802.11n specification, which has not been finalized. [3] **Windows Vista:** Not all Windows Vista features are available for use on all Windows Vista Capable PCs. All Windows Vista Capable PCs will run the core experiences of Windows Vista, such as innovations in organizing and finding information, security, and reliability. Some features available in premium editions of Windows Vista – like the new Windows Aero™ user interface - require advanced or additional hardware. Check [www.windowsvista.com/getready](http://www.windowsvista.com/getready) for details. [4] **Hard Disk drive:** GB = billion bytes. Accessible capacity is less; up to 5.1GB is service partition. [Maximum capacity may require the replacement of installed component with largest supported component available.] [5] **Models with 4GB Memory:** Total accessible memory will be less and will vary depending on the system configuration. [Maximum capacity may require purchase of optional component.] [6] **Thickness:** May vary at certain points on the system. [7] **Included Software:** May differ from its retail version (if available) and may not include user manuals or all program functionality. License agreements may apply. **Energy Star:** As an Energy Star Partner, Lenovo has determined that this product meets the Energy Star guidelines for energy efficiency. **Trademarks:** Lenovo, the Lenovo logo, Access Connections, Active Protection System, Rescue and Recovery, System Migration Assistant, ThinkPad, ThinkVantage, TrackPoint, UltraBay, UltraConnect and UltraNav are trademarks of Lenovo. IBM and the IBM logo are registered trademarks of IBM and are used under license. Celeron, Celeron Inside, Centrino, Centrino Inside, Centrino Logo, Core Inside, Intel, Intel Logo, Intel Core, Intel Inside, Intel Inside Logo, Intel Viiv, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, Viiv Inside, vPro Inside, Xeon and Xeon Inside are trademarks of Intel Corporation in the U.S. and other countries. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Windows Aero is a trademark of Microsoft Corporation. Other company, product and service names may be trademarks or service marks of others. Energy Star is a U.S. registered trademark. c2008 Lenovo. All rights reserved.

Visit [lenovo.com/safecomputing](http://lenovo.com/safecomputing) periodically for the latest information on safe and effective computing.