



# *Personal Systems Reference Lenovo® Consumer Monitors*

*May 2011 - Version 399*




Lenovo L2363d Wide Monitor

Visit [www.lenovo.com/psref](http://www.lenovo.com/psref) for the latest version

<p>Name <b>L2062 Wide Flat Panel Monitor</b>                  Case color <b>High gloss black with metal gray</b>                  Type-model <b>1173-US1</b>                  Panel <b>TFT-LCD, twisted nematic (TN), white LED backlight</b>                  Viewable image size <b>20.0" / 508mm</b> (diagonal)                  Max view area (W x H) <b>17.4" x 9.8" / 443mm x 249mm</b>                  Optimum resolution <b>1600x900</b>                  Max pixel rate <b>153 MHz</b>                  Aspect ratio <b>16:9</b>                  Pixel pitch (mm) <b>0.277mm</b>                  Dot/Pixel per Inch <b>92 dpi</b>                  Brightness <b>250 nits or cd/m<sup>2</sup> (typical)</b>                  Contrast ratio <b>1000:1 (typical)</b>                  Dynamic contrast ratio <b>5,000,000:1</b>                  Pixel response time <b>5ms (typical)</b>                  Color gamut <b>72%</b>                  Anti-reflective <b>Anti-reflective, anti-glare</b>                  Viewing angle at 10:1 CR <b>170° (+/- 85°) horizontal, 160° (+/- 80°) vertical</b>                  Stand <b>Tilt adjustable stand</b>                  Bezel width <b>Sides: 0.63" (16mm);</b>                  Dimensions (HxWxD) <b>14.3" H x 18.9" W x 6.9" D;</b>  <b>362.5mm H x 480.0mm W x 174.8mm D</b>                  Power supply <b>17 watts typical, 22 watts maximum,</b>  <b>&lt;1 watts standby/suspend, universal,</b>  <b>integrated (no external brick-like power supply)</b>                  Weight <b>7.99 lb; 3.63 kg</b>                  Limited warranty<sup>4</sup> <b>1 year</b>                  (includes backlight)                  Available date <b>May 2011</b></p>	<p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Widescreen 20-inch monitor</li> <li>• View images in a 16x9 wide aspect ratio</li> <li>• High-bandwidth Digital Content Protection (HDCP)-compliant</li> <li>• Tilt and cable management stand</li> <li>• Compliance with ENERGY STAR 5.0</li> <li>• Mercury-free and Arsenic-free panel glass</li> <li>• Kensington® lock slot ready for enhanced security</li> <li>• Microsoft® Windows® 7 certified</li> </ul>				
<p>VESA-compliant<sup>2</sup> <b>VESA DDC2B/CI, VESA DPMS-compliant</b>                  Power management <b>ENERGY STAR® 5.0</b>                  Ergonomics <b>ISO 9241-307</b>                  Emission standards <b>FCC Class B</b>                  Environmental <b>TCO (TCO Displays 5.2),</b>  <b>WEEE (EU Directive 2002/95/EC),</b>  <b>RoHS (EU Directive 2002/95/EC)</b></p>	<div style="text-align: center;">  <p><b>Lenovo L2062 Wide Monitor</b></p> </div>				
<p>Preset resolutions <b>VGA: 640x350, 640x480, 720x400</b>  <b>SVGA: 800x600, 832x624</b>  <b>XGA: 1024x768, 1152x864</b>  <b>WXGA: 1366x768</b>  <b>SXGA: 1280x1024</b>  <b>WXGA+: 1440 x 900, 1600x900</b>                  Presets / user settings <b>Standard presets: 24; user settings: 20</b></p>					
<p>Viewing adjustments <b>Tilt: 20° back, -5° forward; detachable stand</b>                  Rotating screen <b>None</b>                  On screen display <b>On screen display with digital user controls (8 languages)</b>                  Control features <b>Direct access (control buttons on front) for automatic image setup</b>                  USB hub <b>None</b>                  Multiple input <b>Dual input (two different PCs attach to two different connectors; one PC shows image; select via button)</b>                  Monitor connectors <b>(1) VGA 15-pin D-shell, analog, blue</b>  <b>(2) Digital Visual Interface (DVI-D) for digital attach [white], <b>HDCP-compliant</b></b>                  Signal cables <b>(1) detachable, VGA 15-pin D-shell at each end, analog, 1.8 meter</b>  <b>(2) detachable, DVI-D at each end (for digital connector), 1.8 meter</b>                  Mounting features <b>Wall or desk mounting using the Radial Arm<sup>9</sup> or third-party accessories meeting the VESA FPMPI<sup>®</sup> (100mm mount)</b>                  Security <b>Security keyhole for attachment of optional cable lock (Kensington® lock-compatible)</b></p>					
<p>Ship group <b>Monitor, attached stand, Setup poster, Safety and Warranty Information, CD with multilingual User's Guide and monitor installation files, analog signal cable, digital signal cable, 1.8m power cord</b></p>					
<p style="text-align: center;"><b>Limited Warranty</b></p> <ul style="list-style-type: none"> <li>⇒ <b>1 year limited warranty<sup>4</sup></b></li> <li>⇒ <b>Advanced Exchange Service at 1-877-453-6686</b></li> <li>⇒ <b>Replacement normally arrives in five business days, excluding holidays</b></li> <li>⇒ <b>Lenovo pays all shipping costs for valid warranty claims<sup>6</sup></b></li> <li>⇒ <b>24x7<sup>8</sup> day toll-free support for warranty issues during the warranty period<sup>4</sup></b></li> </ul>	<p style="text-align: center;"><b>Accessories</b></p> <table border="0"> <tr> <td>Kensington® MicroSaver® Cable Lock</td> <td style="text-align: right;">73P2582</td> </tr> <tr> <td>Kensington Twin Head Cable Lock</td> <td style="text-align: right;">45K1620</td> </tr> </table> <p>See details at <a href="http://www.lenovo.com/support/monitoraccessories">www.lenovo.com/support/monitoraccessories</a>                  See all monitors at <a href="http://www.lenovo.com/support/monitors">www.lenovo.com/support/monitors</a></p>	Kensington® MicroSaver® Cable Lock	73P2582	Kensington Twin Head Cable Lock	45K1620
Kensington® MicroSaver® Cable Lock	73P2582				
Kensington Twin Head Cable Lock	45K1620				

See footnotes for important warranty information  
 US model announced April 19, 2011

<p>Name <b>L2363d Wide Flat Panel Monitor</b>                  Case color <b>High gloss black with metal gray</b>                  Type-model <b>4452-US1</b>                  Panel TFT-LCD, twisted nematic (TN), CCFL backlight                  Viewable image size <b>23.0" (584mm)</b> diagonal                  Max view area (W x H) 20.04" x 11.28" / 509.2mm x 286.4mm                  Optimum resolution <b>1920x1080</b>                  Max pixel rate 290MHz (DVI), 165MHz (HDMI)                  Aspect ratio 16:9                  Pixel pitch (mm) .265mm                  Dot/Pixel per Inch 96 dpi                  Brightness 400 nits or cd/m<sup>2</sup> (typical)                  Contrast ratio 1000:1 (typical)                  Dynamic contrast ratio 20000:1                  Pixel response time 5ms (typical)                  Anti-reflective Anti-reflective, anti-glare                  Viewing angle at 10:1 CR 170° (+/- 85°) horizontal, 160° (+/- 80°) vertical                  Stand Tilt adjustable stand                  Bezel width <i>Sides:</i> 1.13" (28.7mm)                  Dimensions (HxWxD) 16.69" H x 22.40" W x 6.57" D;                  423.8mm H x 569.0mm W x 167.0mm D                  Power supply 55 watts typical, 60 watts maximum,                  &lt;2 watts standby/suspend, universal,                  integrated (no external brick-like power supply)                  Weight 13.2 lb; 6.0kg                  Limited warranty<sup>4</sup> <b>1 year</b> (includes backlight)                  Available date April 2011</p>	<p style="text-align: center;"><b>Features</b></p> <ul style="list-style-type: none"> <li>• Widescreen 23-inch monitor</li> <li>• 1080p full HD support, HDCP-compliant</li> <li>• Lenovo's first 3D monitor, supports NVIDIA® 3D Vision™ (requires selected NVIDIA graphics card configurations)</li> <li>• Supports 120Hz refresh rate</li> <li>• Integrated 3D Web Camera to record 3D images</li> <li>• Built-in DVI and HDMI 1.3 connectors for attachment to two systems concurrently</li> <li>• 10-60 degree easily adjustable stand and VESA mount</li> <li>• Compliance with ENERGY STAR 5.0</li> <li>• Arsenic free glass</li> <li>• Kensington® lock slot ready for enhanced security</li> <li>• Microsoft® Windows 7 certified</li> </ul>				
<p>VESA-compliant<sup>2</sup> VESA DDC2B/CI, EDID 1.3, VESA DPMS-compliant                  Power management ENERGY STAR<sup>®</sup> 5.0                  Ergonomics ISO 9241-307                  Emission standards FCC Class B                  Environmental WEEE (EU Directive 2002/96/EC),                  RoHS (EU Directive 2002/95/EC)</p>	<div style="text-align: center;">  <p><b>L2363d Wide Monitor</b></p> </div>				
<p>Preset resolutions                  VGA: 640x350, 640x480, 720x400                  SVGA: 800x600, 832x624                  XGA: 1024x768, 1152x864                  SXGA: 1280x1024                  WXGA: 1366x768                  WXGA+: 1440x900, 1600x900                  WSXGA+: 1680x1050                  WUXGA: 1920x1080 (support 120Hz refresh rate for 3D display mode)</p> <p>Presets / user settings Presets: 29 (DVI), 24 (HDMI);                  user settings: 20</p>					
<p>Viewing adjustments <i>Tilt:</i> 10°-60° back, 0° forward; adjustable stand                  Rotating screen None                  On screen display On screen display with digital user controls (8 languages)                  Control features Direct access (control buttons on front) for automatic image setup and adjustment for brightness                  USB hub USB 2.0 Hub (1 port into PC, 3 ports for accessories)                  Camera module Integrated camera (3D, 0.3 megapixel) and dual array microphone                  3D Vision kit NVIDIA 3D Vision kit includes GeForce 3D Vision active shutter glasses, 3D Vision USB controller/IR emitter                  Multiple input Dual input (two different PCs attach to two different connectors; one PC shows image; select via button)                  Monitor connectors (1) Digital Visual Interface (DVI-D), digital, white, <b>HDCP-compliant</b>                  (2) HDMI (1.3), digital, black, <b>HDCP-compliant</b>                  Signal cables (1) detachable, dual-link DVI-D at each end, digital, 1.8 meter                  (2) detachable, HDMI at each end, digital, 1.8 meter                  Mounting features Wall or desk mounting using the Radial Arm<sup>3</sup> or third-party accessories meeting the VESA FPMPI<sup>®</sup> (100mm mount)                  Security Security keyhole for attachment of optional cable lock (Kensington® lock-compatible)</p>	<p>Ship group Monitor, attached stand, cable cover, Setup poster, Health and Safety Information and 3D Camera Setup Guide, 2 CDs with multilingual User's Guide, quick setup guide and monitor installation files, NVIDIA 3D vision kit, 1.8 meter dual-link DVI-D cable, 1.8 meter HDMI cable, 1.8 meter USB cable, 1.8 meter black power cord</p>				
<p style="text-align: center;"><b>Limited Warranty</b></p> <ul style="list-style-type: none"> <li>↪ 1 year limited warranty<sup>4</sup></li> <li>↪ Rapid Replacement Service at 1-877-453-6686</li> <li>↪ Replacement normally arrives in two business days, excluding holidays</li> <li>↪ Lenovo pays all shipping costs for valid warranty claims<sup>5</sup></li> <li>↪ 24x7<sup>8</sup> day toll-free support for warranty issues during the warranty period<sup>4</sup></li> </ul>	<p style="text-align: center;"><b>Accessories</b></p> <table border="0"> <tr> <td>Kensington MicroSaver® Cable Lock</td> <td style="text-align: right;">73P2582</td> </tr> <tr> <td>Kensington Twin Head Cable Lock</td> <td style="text-align: right;">45K1620</td> </tr> </table> <p>See details at <a href="http://www.lenovo.com/support/monitoraccessories">www.lenovo.com/support/monitoraccessories</a></p> <p>See all monitors at <a href="http://www.lenovo.com/support/monitors">www.lenovo.com/support/monitors</a></p>	Kensington MicroSaver® Cable Lock	73P2582	Kensington Twin Head Cable Lock	45K1620
Kensington MicroSaver® Cable Lock	73P2582				
Kensington Twin Head Cable Lock	45K1620				

See footnotes for important warranty information  
 US model announced March 22, 2011

**Availability:** All offers subject to availability. Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo is not responsible for photographic or typographic errors.

**Warranty:** For a copy of applicable product warranties, write to: Warranty Information, P.O. Box 12195, RTP, NC, 27709, Attn: Dept ZPYA/B676. Lenovo makes no representation or warranty regarding third party products or services.

- <sup>1</sup> **ISO-compliant:** Compliance with ISO 9241 Part 3, ISO Part 7, ISO Part 8, and/or ISO 13406 Part 2 is dependent on a complete ISO-capable platform of a system unit, monitor, video subsystem, operating system and fonts.
- <sup>2</sup> **VESA:** Requires attachment to suitably configured system with similarly enabled operating system.
- <sup>3</sup> **ENERGY STAR:** As an ENERGY STAR partner, Lenovo has determined that this product meets the ENERGY STAR 4.0 or 4.1 guidelines for energy efficiency. Requires attachment to suitably configured system.
- <sup>4</sup> **Limited warranty:** Support unrelated to a warranty issue may be subject to additional charges.
- <sup>6</sup> **Lenovo pays all shipping costs** for warranty repairs during limited warranty period.
- <sup>8</sup> **Telephone support** may be subject to additional charges, even during the limited warranty period. In the United States call 877-453-6686. Response times may vary. May exclude some holidays.



**Trademarks:** Lenovo, the Lenovo logo, New World. New Thinking., Access Connections, Rescue and Recovery, ThinkCentre, ThinkPad, ThinkStation, ThinkVantage, and ThinkVision are trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, or service names may be trademarks or service marks of others.

This publication was developed for products and services offered in the United States. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to alter specifications and other product information at any time without prior notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions; therefore this disclaimer may not apply to you. This publication was developed in the US.

Visit [www.lenovo.com/safecomputing](http://www.lenovo.com/safecomputing) periodically for the latest information on safe and effective computing.

Visit [www.lenovo.com/psref](http://www.lenovo.com/psref) for the latest version of Personal Systems Reference.

© Lenovo, 2011.  
All rights reserved.

Lenovo  
1009 Think Place  
Morrisville, NC 27560  
U.S.A.

May 2011  
cmbbook.pdf