

## EB200

### 380 TVL Color Camera Module



COLOR NTSC, PAL	ES 1/50 (1/60) ~ 1/100,000	BLC Yes	AGC Yes
POWER 12VDC	AWB Yes	380 TVL	




#### Features

- 1/3" Sony Interline Transfer Super HAD CCD
- Standard resolutions of 380 TVL
- Light sensitivity of 0.3 Lux/F=1.2
- Electronic shutter and AGC allows camera to be operated in environments with various light levels
- Camera module suitable for covert housing
- Small Size: 1.3" x 1.3"
- Standard 3.6mm lens (also available in 2.5mm, 4.3mm, 6mm, 8mm, 12mm and 16mm lens)

#### Specifications

Pickup Device	1/3" Sony Interline Transfer Super HAD CCD
Video Format	NTSC or PAL
Picture Format	510 x 492 (NTSC) / 500 x 582 (PAL)
Horizontal Resolution	380 TVL
Video Output	BNC 1.0 Vp-p, 75 ohm
Sensitivity	0.3 Lux/F=1.2
S/N Ratio	Over 48dB
Electronic Shutter	1/50 (1/60) ~ 1/100,000 sec.
Backlight Comp.	Yes
Auto Gain Control	Yes
Auto White Balance	Yes
Gamma Correction	0.45
Lens	Standard board lens f=3.6mm, F=2.0 (Optional lens: 2.5mm, 4.3mm, 6mm, 8mm, 12mm and 16mm)
Power Source	12VDC +/- 10%, 200mA
Power Consumption	200mA max.
Dimensions (W x H)	33 x 33 mm / 1.3" x 1.3"
Operating Temp.	0°C ~ 50°C / 32°F ~ 122°F
Humidity	20% ~ 80% humidity
Weight	45 g / 0.1 lbs

#### Dimensions



#### Ordering Information

- **EB200/N-3:** 1/3" Color Camera Module, 380 TVL, 3.6mm lens

\*Also available with 2.5mm, 4.3mm, 6mm, 8mm, 12mm and 16mm lens

\*\*To order, replace the last number with the first digit(s) of the desired lens (e.g. 2.5mm lens = EB200/N-2, 6mm = EB200/N-6)

\*Models vary in different countries. Please visit your EverFocus regional website for detailed ordering information.