

1 Port RS232 Serial Ethernet Device Server, PoE Power Over Ethernet, TAA - Replaced by I13P-SERIAL-ETHERNET

**Product ID:** NETRS2321POE



The NETRS2321POE 1 Port RS232 Serial Ethernet Device Server - PoE (Power Over Ethernet) allows you to install your RS232 devices anywhere on your TCP/IP Ethernet WAN/LAN, and access them as if they were right beside you - even over the Internet!

The Serial Device Server is designed to function seamlessly with your other integrated and add-on serial ports as if they were right inside your computer. Perfect for industrial automation, security, Point of Sale, or any long-range serial application, delivering reliable performance in any environment.

The Ethernet/serial device server supports PoE (Power over Ethernet) when connected to a PoE compliant device - eliminating the need for an external power supply and outlet, and making it easier to situate the device server as needed.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- Security (UPS control, access key panels, video cameras, card readers)
- Environmental Control (lighting, temperature, clocks)

- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Hospital (monitoring equipment, nurses' stations)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)

## Features

- Supports standard Ethernet or Power over Ethernet (POE)
- Supports UDP, IP, TCP, ICMP, HTTP, DHCP and ARP-Ping protocols
- Wall mountable
- Integrated 10/100Mbps RJ45 LAN port
- Data transfer rates of up to 115.2 Kbps per port
- Supports Auto Crossover (MDI/MDI-X)
- Support for Windows 2000, XP 32bit, and Vista 32bit

---

### Hardware

Warranty	2 Years
Industry Standards	IEEE 802.3af Power-over-Ethernet

---

### Performance

Maximum Data Transfer Rate	115.2Kbps
Data Bits	6, 7, 8
Stop Bits	1, 2
MTBF	233,403 Hours
Supported Protocols	UDP, IP, TCP, ICMP, HTTP, DHCP, ARP-Ping

---

### Connector(s)

Connector Type(s)	1 - DB-9 (9 pin, D-Sub)
	1 - RJ-45

---

### Software

---

OS Compatibility	Windows Vista (32), XP (32), 2000
------------------	-----------------------------------

---

**Special Notes / Requirements**

Patents and Licenses	<p>The following patents are licensed for this product. This list might not be all inclusive.</p> <ul style="list-style-type: none"> <li>• United States Patent No. 5,406,260 (expired)</li> <li>• United States Patent No. 6,650,622</li> <li>• United States Patent No. 7,457,250</li> <li>• United States Patent No. 8,155,012</li> <li>• United States Patent No. 8,902,760</li> <li>• United States Patent No. 8,942,107</li> <li>• United States Patent No. 9,019,838</li> <li>• United States Patent No. 9,049,019</li> <li>• United States Patent Application No. 14/695,456</li> <li>• United States Patent Application No. 14/726,940</li> </ul>
----------------------	--

---

**Indicators**

LED Indicators	3 - Heartbeat, Link/Activity, 10/100 Mbps
----------------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.3 A
Output Voltage	12V DC
Output Current	0.1A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	1.2

---

**Environmental**

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20C to 85C (-4F to 185F)

Humidity 5~95% RH

---

**Physical Characteristics**

Color	Black
Material	Aluminum
Product Length	4.2 in [10.7 cm]
Product Width	2.6 in [6.6 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	9.1 oz [259.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	11.6 in [29.4 cm]
Package Width	7.6 in [19.2 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	2.1 lb [0.9 kg]

---

**What's in the Box**

Included in Package	1 - Industrial Serial over IP Device Server
	1 - Universal Power Adapter (NA/UK/EU)
	1 - Instruction Manual

---

*\*Product appearance and specifications are subject to change without notice.*

