

WorkCentre®

6400

Letter-size

Color

Multifunction Printer



Xerox® WorkCentre® 6400
Color Multifunction Printer
Full-featured power
in a desktop device

xerox

WorkCentre® 6400 Multifunction Printer

Unleash the productivity of your office. We've taken the office-critical features of our large departmental MFPs and packed them into this ultraproductive letter-sized printer. It seamlessly integrates print, scan, fax and copy functionality, and adds smart management tools to simplify work for busy offices with high-volume color requirements.

A powerhouse made for sharing

From its advanced networking to fast operating speeds (up to 32 ppm color / 37 ppm black-and-white), the WorkCentre 6400 is tailor-made for large workgroups.

- **Multitasking.** Access walk-up copying, scanning or faxing functions when you need them, even while other jobs are printing. Spend your valuable time working, not waiting for your turn.
- **Never wait for a job on hold.** Exclusive Print Around feature detects print jobs waiting for additional resources (such as a special paper size) and prints the next print job in the queue.




WorkCentre® 6400 Quick Facts

- 32 ppm color, 37 ppm black-and-white
- Up to 2400 x 600 dpi
- Standard automatic two-sided color copy/print
- True Adobe® PostScript® 3™, PCL 5c and PCL 6 support



Print / Copy / Scan / Fax

8.5 x 14 in.
32 ppm color



All-in-one simplicity

The WorkCentre 6400 gives your business crucial tools in an easy-to-use package.

- **Walk-up use is intuitive** thanks to the icon-based, 8-inch color touch screen with help screens. It shares the same simplicity our larger Xerox devices are known for.
- **Easy supplies replacement.** Toners come pre-loaded and replacement is simple thanks to the easy-access front door, and email alerts notify you when levels are low.
- **Automatic two-sided** copying, printing and fax receipt reduces office paper use.
- **Regulate use and control costs.** Set limits to users' access to copy and fax functionality and control access to color. Generate usage reports for analysis and billing purposes.
- **Scan routing made easy.** LDAP capability integrates scanning with your network address book.
- **Efficient finisher** (standard on 6400XF) staples your documents or offset stacks jobs for grab-and-go convenience.
- **Annotate, edit and organize** scanned image files with Scan to PC Desktop® SE Personal Edition (standard). Convert scanned documents to editable text formats such as Microsoft® Word® and Excel®.

Your processes simplified

- **Turn a shared multifunction printer into your own personal multifunction printer.** The WorkCentre 6400 is built on the powerful Xerox Extensible Interface Platform™ (EIP), a web- and standards-based technology that lets you add applications for easy access right from the touch screen. For example, Scan to PC Desktop® software (optional Professional version) seamlessly integrates with EIP for customized scanning menus that match your specific workflows.

- **Full-functioned scanning** includes a wide range of document routing capabilities. Store scans in a public or private folder on the hard drive with Scan to Mailbox. Send files to a pre-assigned "home" destination with Scan to Home. Scan files directly to email addresses or store on a central server with network scanning.

- **Automate repetitive job processes** by automatically routing scanned documents to predefined folders on your computer or as attachments to emails with convenient scan templates.

- **Store frequently printed documents** directly on the device for reprinting later.

- **Convert paper documents to text-searchable PDFs** in one step for easy archiving, organizing and searching.



Choose desktop or floor standing models to locate conveniently close to users.

1 Xerox Extensible Interface Platform™ (EIP) is a software platform inside the WorkCentre 6400 that enables personalized solutions you can access right from the touch screen. These applications can leverage your existing databases and meet your specific business challenges.

2 50-sheet Duplex Automatic Document Feeder scans two-sided documents in sizes up to 8.5 x 14 in.

3 Full 8.5 x 14 in. platen glass allows you to scan legal-size documents with ease.

4 80 GB internal hard drive lets you handle more tasks at the device. Use the Save Job feature to keep frequently used documents available for quick printing on the go.

5 100-sheet multipurpose tray.

6 Standard 500-sheet tray.

7 Two additional 500-sheet trays (standard on XF configuration).

8 Stand includes cabinet for toner and media storage (standard on the XF configuration).

9 Finisher collates and staples sets of up to 30 pages. Available for both desktop and floor standing models. Includes 600-sheet output tray.



Convenient walk-up operation. Easy to read and navigate, the large color touch screen guides you through even the most complex operations.

Security built in

Confidential documents stay confidential with advanced security features:

- A print job can be held in the queue until a PIN is entered, releasing it to print.
- Image data in the device's memory can be automatically "shredded" after every job or on request.
- A password can be required before incoming faxes can be printed or removed, and a junk fax barrier protects your privacy.
- Authentication helps prevent unauthorized access to the device and support for 802.1X secures it on the network.
- Supports IPSec for both IPv4 and IPv6 for improved security.
- Secure Access Unified ID System (optional) enables users to log-in at the WorkCentre 6400 with their employee/student ID badge for secure access to functions that need to be tracked for accounting or regulatory requirements.



WorkCentre® 6400 Configurations

WorkCentre 6400S

- Automatic two-sided copy/print/scan
- 600-sheet input capacity
- Color Scan to Email, Scan to Network

WorkCentre 6400X

- 6400S plus:**
- Embedded Fax, LAN Fax, Internet Fax and support for Server Fax

WorkCentre 6400XF

- 6400X plus:**
- 1,600-sheet total input capacity
- 600-sheet finisher for 30-sheet stapling capability
- Stand with storage cabinet

Options

- Additional 500-sheet trays
- Finisher for 30-sheet stapling
- Stand with storage cabinet
- Wireless network adaptor
- Foreign device interface

WorkCentre® 6400



	WorkCentre 6400S	WorkCentre 6400X	WorkCentre 6400XF		
Speed	Up to 32 ppm color / 37 ppm black-and-white (Letter)				
Duty Cycle	Up to 120,000 pages / month*				
Paper Handling Paper input	Standard	Duplex Automatic Document Feeder: 50 sheets; Custom Sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm; Weight: 12.5 to 28 lb / 50 to 105 gsm Multipurpose Tray 1: 100 sheets; Custom sizes: 3.6 x 5.8 in. to 8.5 x 14 in. / 97 x 147 mm to 216 x 356 mm Tray 2: 500 sheets; Sizes: 8.5 x 11 in. / A4 (210 x 297 mm)			
	Optional	Tray 3 and Tray 4: 500 sheets; Sizes: Letter, Legal, Executive, US Folio, A4, B5 JIS	Standard		
Paper output	500 sheets, automatic two-sided				
Finishing	Optional	Finisher: 600-sheet tray, 30-sheet stapling	Standard		
Print First-page-out-time	As fast as 16 seconds				
Print resolution	Up to 2400 x 600 dpi				
Processor / Memory	800 MHz / 1 GB plus 80 GB hard drive				
Page Description Languages	PCL® 5c, PCL 6, Adobe® PostScript® 3™, PDF 1.6, TIFF, JPEG				
Connectivity	USB 2.0 (for print only), 10/100/1000 Base-TX Ethernet, IPv4 and IPv6				
Print features	Automatic two-sided, Custom page size, N-Up, Banner sheet, Inserts, Covers, Booklet creation, Mirror image, Collation, Watermarks, Scaling, Print Around, Sample set, Secure print, Delayed print, Saved Job				
Copy Copy resolution	600 x 600 dpi				
Copy features	Automatic two-sided, Collation, Reduce/Enlarge 25 to 400 %, Lighten/darken, Booklet creation, covers, Inserts, Annotations, Bates Stamping, Transparency separators, Multiple-up, Build Job, Sample copy, Save copy settings				
Fax	NA	Embedded Fax, LAN Fax, Internet Fax, Network Server Fax enablement			
Fax features		Up to 600 x 600 dpi (Super Fine) resolution, Junk fax filter, Mailboxes and Polling, Secure Fax, Delayed Send, Speed dials (up to 200), Group dials			
Scan Scan destinations	Scan to Mailbox, Scan to Email, Scan to File, Scan to Home				
Scan features	Up to 600 x 600 dpi, File formats: PDF, Searchable PDF, TIFF, Multi-page TIFF, JPEG; Scan to PC Desktop® SE Personal Edition (includes 1 seat of PaperPort® SE, OmniPage® SE, Image Retriever)				
Accounting	Job-based Accounting, Xerox Standard Accounting, Network Accounting enablement				
Security	Disk Overwrite, Job Overwrite, Disk Encryption, 802.1X, Secure Print, Authentication, Secure Fax				
Warranty	One-year on-site warranty, Xerox Total Satisfaction Guarantee				

* Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis.

Device Management

CentreWare® Internet Services, CentreWare Web

Print Drivers

Windows® 2003/XP/Vista, Mac OS® X version 10.3 and higher, Linux® Turbolinux® 10 Desktop, SUSE™, Red Hat®, Xerox Global Print Driver, Xerox Mobile Express Driver

Font Support

141 PostScript fonts, 81 PCL fonts

Media Handling

Multipurpose Tray 1: 16 lb. bond to 80 lb. cover / 60 – 210 gsm; Trays 2, 3, 4: 16 – 24 lb. bond / 60 – 90 gsm; Two-sided printing: 16 – 40 lb. bond / 60 – 150 gsm; Media types: Plain paper, transparencies, card/cover, glossy, labels, envelopes

Color Standards

PANTONE® Color approved solid-color simulations, Xerox Color Correction

Operating Environment

Operating: 50° to 90° F / 10° to 32° C; Storage: -4° to 104° F / -20° to 40° C; Relative humidity: 15 to 85 %; Storage: 10 to 95 %; Noise Level: Sound pressure: Printing: 56.8 dB(A), Standby: 37.3 dB(A); Sound power: Printing: 7.294 B, Standby: 5.106 B

Electrical

Power: 110-127 VAC, 50/60 Hz; Power consumption: Standby: 165 W; Printing: 854 W; Power save: 24 W; 220-240 VAC, 50/60 Hz; Power consumption: Standby: 161 W; Printing: 802 W; Power save: 26 W; ENERGY STAR® qualified

Dimensions (WxDxH)

6400S/6400X: 20.8 x 23.1 x 24.7 in. / 530 x 588 x 627 mm; Weight: 130 lbs. / 59 kg; 6400XF: 39.7 x 26.5 x 46 in. / 1008 x 673 x 1169 mm; Weight: 243 lbs. / 110 kg

Package Dimensions (WxDxH):

6400S/6400X: 29.9 x 25.6 x 34.8 in. / 760 x 650 x 883 mm; 6400XF: 44 x 30.3 x 57.4 in. / 1118 x 770 x 1458 mm

Certifications

FCC Part 15, Class A, FCC Part 68, CE Mark applicable to Directives 2006/95/EC, 2004/108/EC and 1999/5/EC, Listed UL 60950-1/CSA 60950-1-03

What Comes In The Box

The WorkCentre 6400 includes Toner Cartridges installed (standard-capacity for CMY and high-capacity for Black).

Supplies and Options

Print cartridges: ¹	
Cyan standard-capacity: 8,000 pages	106R01320
Magenta standard-capacity: 8,000 pages	106R01321
Yellow standard-capacity: 8,000 pages	106R01322
Black high-capacity: 12,000 pages	106R01316
Cyan high-capacity: 16,500 pages	106R01317
Magenta high-capacity: 16,500 pages	106R01318
Yellow high-capacity: 16,500 pages	106R01319
Imaging Units: ²	
Cyan Imaging Unit: 30,000 pages	108R00775
Magenta Imaging Unit: 30,000 pages	108R00776
Yellow Imaging Unit: 30,000 pages	108R00777
Black Imaging Unit: 30,000 pages	108R00774
Waste Cartridge: 22,000 pages each (Qty 2)	108R01368
110V Fuser: 150,000 pages	115R00059
Foreign Device Interface	097S03872
Stand	097S03873
500-Sheet Feeder	097S03874
Finisher	097S03875
Wireless Network Adapter	097S03740
Scan to PC Desktop	
- Professional Small Business Edition (5 seats)	097S03910



For more information, call 1-877-362-6567 or visit us at www.xerox.com/office

¹ Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

² Approximate pages. Declared Yield based on an average job size of 5 pages letter/A4 size. Yield will vary based on job run length, media size and orientation.

© 2010 Xerox Corporation. All rights reserved. Contents of this publication may not be reproduced in any form without permission of Xerox Corporation. XEROX®, CentreWare®, WorkCentre® and the sphere of connectivity design are trademarks of Xerox Corporation in the U.S. and/or other countries. Adobe® and PostScript® 3™ are registered trademarks or trademarks of Adobe Systems, Incorporated. PCL® is a registered trademark of Hewlett-Packard. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. All other trademarks are the property of their respective manufacturers. The information in this brochure is subject to change without notice. 2/10 610P729867G

