





Antec's EarthWatts Platinum is one of the most efficient PSU series ever created. With an 80 PLUS® PLATINUM rating, the highest efficiency mark for power supplies, this PSU achieves up to 93% efficiency and gives you savings unheard of from other power supplies. By using the EA-550 Platinum, you can reduce your electricity bill up to 25%. A 3 year Antec Quality warranty, a whisper-quiet 120mm DBB fan controlled by Antec's renowned Thermal Manager and CircuitShield™'s industry-leading 7 levels of protection make the EA-550 Platinum one of the best choices available. Get the power you need, save money and help protect the environment with Antec's EA-550 Platinum!



SPECIFICATIONS:

- 550W Continuous Power - Guaranteed 550W of Continuous Power from Antec
- 80 PLUS® PLATINUM certified - Up to 93% efficient, to reduce your electricity bill
- Save Energy and Money - Reduce your electricity bill by up to 25%!
- AQ3 - Antec Quality 3 year warranty and lifetime global 24/7 support
- 120 mm DBB Silence - Whisper-quiet high-quality double ball bearing fan with long lifetime
- Thermal Manager - An advanced low voltage fan control for optimal heat & noise management
- High Current Rails - 4 fully-protected High Current +12V rails with high load capabilities ensure maximum CPU & GPU compatibility
- Multi PCI-E - 2 PCI-E connectors for multiple GPU support
- CircuitShield™ - Over Current Protection (OCP), Over Voltage Protection (OVP), Under Voltage Protection (UVP), Short Circuit Protection (SCP), Over Power Protection (OPP), Surge & Inrush Protection (SIP), No Load Operation (NLO) & Brown-Out Protection (BOP)
- Japanese heavy-duty caps - High-performance Japanese capacitors ensure tightest DC stability and regulation

POWER SUPPLY CONNECTORS ASSORTMENT



INPUT

Voltage	100 - 240VAC ± 10%							
Frequency Range	50Hz - 60Hz							
Current	8 - 4A							
Efficiency	Up to 93%							

OUTPUT

Voltage	+5V	+3.3V	+12V1	+12V2	+12V3	+12V4	-12V	+5VSB
Max. Load	16A	16A	30A	30A	30A	30A	0.3A	3A
+12V1-4 maximum combined output: 516W +3.3V and +5V Maximum combined output: 95W								

ENVIRONMENT

Operating Temperature	0°C - 50°C							
Safety Approvals	UL, cUL, CB, CE, FCC, TÜV, BSMI, CCC, C-Tick, GOST-R, KCC							
Net Weight	4.2 lbs / 1.9 kg							
Size	86 mm (H) x 150 mm (W) x 140 mm (D) 3.4" (H) x 5.9" (W) x 5.5" (D)							

UPC#

0-761345-27520-0	0-761345-10678-8	JP
0-761345-04750-0	0-761345-10679-5	TW
0-761345-04751-7	0-761345-10680-1	KR
0-761345-10676-4	0-761345-10681-8	HK
0-761345-10677-1	0-761345-10688-7	NC

