


12U 19in Hinged Wall Mount Server Rack Cabinet w/ Steel Mesh Door

Product ID: RK1219WALHM



This 12U Server Rack/Cabinet offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle.

The sturdy 12U rack cabinet features a high quality steel design and a vented, steel mesh door to help keep rack mounted equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack cabinet accommodates 19in wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

Our 12U Rack Cabinet is designed for guaranteed reliability to ensure a stable rack mount platform for valuable equipment and backed by Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Mounting standard 19 in. networking equipment in exposed or unsecure locations

Features

- Unique hinged design swings open for easy access to your equipment
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Steel mesh door for added security

Hardware	Warranty	Lifetime
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel Mesh
	Front Door Features	Secure Key Lock with Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Rear Door Construction	Steel
	Side Panel Construction	Steel
	Side Panel Features	Secure Key Lock with Removable Side Panels
	Special Features	Adjustable Mounting Rails
		Grounding Lug(s)
	Ships Fully Assembled	
	Wall-Mountable	
	U Height	12U
	Wallmountable	Yes
Performance	Weight Capacity	132.6 lb [60 kg]
Physical Characteristics	Color	Black
	Rear Door Features	Secure Key Lock
Product Measurements	Internal Depth	20.6 in [52.2 cm]
	Internal Width	22 in [56 cm]
	Maximum Mounting Depth	15.4 in [39.2 cm]
	Minimum Mounting Depth	2.7 in [6.8 cm]
	Product Height	25 in [63.5 cm]
	Product Length	21.7 in [55 cm]
	Product Width	23.5 in [59.7 cm]
	Weight of Product	55.5 lb [25.1 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	26.1 in [66.2 cm]

	Package Length	27.6 in [70 cm]
	Package Width	26.2 in [66.5 cm]
	Shipping (Package) Weight	62.2 lb [28.1 kg]
What's in the Box	Included in Package	1 - Black Hinged Cabinet 1 - Set of Keys 10 - M6 Screws 10 - M6 Cage Nuts

Product appearance and specifications are subject to change without notice.