



Antec's EarthWatts Platinum is one of the most efficient PSU series ever created. With an 80 PLUS® PLATINUM rating, the highest efficiency mark for power supplies, this PSU achieves up to 93% efficiency and gives you savings unheard of from other power supplies. By using the EA-650 Platinum, you can reduce your electricity bill up to 25%. A 3 year Antec Quality warranty, a whisper-quiet 120mm DBB fan controlled by Antec's renowned Thermal Manager and CircuitShield™'s industry-leading 7 levels of protection make the EA-650 Platinum one of the best choices available. Get the power you need, save money and help protect the environment with Antec's EA-650 Platinum!



SPECIFICATIONS:

- **650W Continuous Power** - Guaranteed 650W of Continuous Power from Antec
- **80 PLUS® PLATINUM certified** - Up to 93% efficient, to reduce your electricity bill
- **Save Energy and Money** - Reduce your electricity bill by up to 25%
- **AQ3** - Antec Quality 3 year warranty and lifetime global 24/7 support
- **120 mm DBB Silence** - Whisper-quiet high-quality double ball bearing fan with long lifetime
- **Thermal Manager** - An advanced low voltage fan control for optimal heat & noise management
- **High Current Rails** - 4 fully-protected High Current +12V rails with high load capabilities ensure maximum CPU & GPU compatibility
- **Multi PCI-E** - 2 PCI-E connectors for multiple GPU support
- **CircuitShield™** - Over Current Protection (OCP), Over Voltage Protection (OVP), Under Voltage Protection (UVP), Short Circuit Protection (SCP), Over Power Protection (OPP), Surge & Inrush Protection (SIP), No Load Operation (NLO) & Brown-Out Protection (BOP)
- **Japanese heavy-duty caps** - High-performance Japanese capacitors ensure tightest DC stability and regulation

POWER SUPPLY CONNECTORS ASSORTMENT



INPUT

Voltage	100 - 240VAC ± 10%							
Frequency Range	50Hz - 60Hz							
Current	10 - 5A							
Efficiency	Up to 93%							

OUTPUT

Voltage	+5V	+3.3V	+12V1	+12V2	+12V3	+12V4	-12V	+5VSB
Max. Load	18A	20A	30A	30A	30A	30A	0.3A	3A
+12V1-4 maximum combined output: 576W								
+3.3V and +5V Maximum combined output: 105W								

ENVIRONMENT

Operating Temperature	0°C - 50°C							
Safety Approvals	UL, cUL, CB, CE, FCC, TÜV, BSMI, CCC, C-Tick, GOST-R, KCC							
Net Weight	4.4 lbs / 2.0 kg							
Size	86 mm (H) x 150 mm (W) x 140 mm (D) 3.4" (H) x 5.9" (W) x 5.5" (D)							

UPC#

0-761345-27670-2	0-761345-10684-9
0-761345-04760-9	0-761345-10685-6
0-761345-04761-6	0-761345-10686-3
0-761345-10682-5	0-761345-10687-0
0-761345-10683-2	0-761345-10689-4