

Panasonic

ideas for life

14 PPM High Speed Printing and Copying

600 DPI High Quality Laser Printing and Copying

170-Page Document Memory*¹⁺²

KX-FL611E

Laser Fax



LASER PRINTING / LASER COPIER / INTEGRATED TELEPHONE

HIGH SPEED
14PPM
LASER PRINTING

Dual Access



Document
Memory*¹⁺²



14.4 kbps

TELECOMMUNICATIONS

KX-FL611E

Advanced
Communication
System with Laser
Print Quality



Advanced Features



Convenient Laser Copier Function

The laser fax performs a range of advanced laser copier functions in 600 dpi at 14 PPM: Enlarge, Reduce, Collate (sort) and Multiple Copy up to 99 copies from one original.



High Speed Fax Transmission (14.4 kbps)

This system is designed for fast, efficient fax transmission at speeds up to 14.4 kbps. This minimizes costs when you're sending a long-distance fax.



Laser Technology for Quality Printing

The Panasonic laser fax lets you enjoy the professional look of laser printing. The laser copier function helps assure high quality reproduction in every document and drawing you want to copy.



14 PPM Laser Printing

Whether you're printing or copying faxes or original documents, the laser fax delivers crisp 600 dpi laser output at an incredibly fast rate of 14 pages per minute.



170-Page Document Memory*1*2

This unit can store up to 120 pages in its built-in memory. Ideal for broadcasting multi-page documents to multiple locations. This feature also enables out-of-paper reception for up to 170 pages.

Other Features

- 14 PPM high-speed laser printing
- Transmission speed: up to 8 seconds per page*
- Caller ID list printout*4
- Sequential broadcasting (20 locations)
- Junk fax prohibitor (up to 10 numbers)
- Delayed transmission
- Error correction mode (ECM)
- 64-level halftone resolution
- Friendly fax reception
- 20-page document feeder
- 250-sheet paper cassette
- Telephone directory for up to 122 names and numbers
- Electronic volume control
- Help function
- Handset mute function
- Toner near-end and empty indication

KX-FL611E Specifications

Facsimile

Compatibility:	ITU-T G3
Paper Handling:	A4
Scanning Width:	208 mm
Resolution:	Standard/fine/super fine/photo/photo with text
Halftone:	64 levels
Modem Speed:	14.4 kbps with automatic fallback
Transmission Speed:	Approx. 8 seconds per page*1 in ECM-MMR mode
Compression System:	MH/MR/MMR
Document Memory*1*2:	Max. 170 pages for memory reception. Max. 120 pages for memory transfer
Paper Cassette:	Max. 250 sheets
Document Feeder:	Max. 20 sheets
Printing Method:	Laser printing on plain paper
Resolution:	600 dpi
Printing Speed:	up to 14 PPM
Copier Function:	Enlarge (up to 200% in 5% steps), Reduce (to 50% in 5% steps), multiple copy (up to 99 copies)

Integrated Telephone System

Dial Mode:	Tone
Dialing Memory:	122 30-digit telephone numbers
Caller ID*1:	FSK compatible
Power Source:	AC 220-240V, 50 Hz
Dimensions (W x D x H):	430 mm x 480 mm x 370 mm
Weight:	9.2 kg

*1 Based on ITU-T No.1 test chart.

*2 Max. 170 pages for out-of-paper reception. Max. 120 pages for memory transmission.

*3 5% page coverage.

*4 Requires subscription to fee-based telephone company service. See dealer for detail.

Consumables

KX-FA83X Toner Cartridge (2,500 pages*3)
KX-FA84X Drum Unit (10,000 pages)

Panasonic®

Global Web Sites: <http://www.panasonic.co.jp/global>

Design and specifications are subject to change without notice. 0M0305SK-KX-FL611-LTE