

10 ft Coax High Resolution 90° Upward Angled VGA Monitor Cable - HD15 M/M

StarTech ID: MXT101MMHU10



This 10ft upward-angle VGA cable is designed to support the highest resolutions and highest video quality possible through VGA while fitting perfectly in tight connection spaces. The cable features one standard VGA connector (HD15) and one VGA connector (HD15) that is situated on an upward angle relative to the shaft of the cable, requiring only 32.4mm of space at the connection point.

Suited for high resolution VGA applications (1280x1024 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Applications and Solutions

- Connecting Multimedia Servers
- POS Displays

Features

- 90° Upward Angled connector with a 32.4mm depth
- Ferrite core eliminates EMI interference
- Ideal for high resolution monitors (1280x1024 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Technical Specifications

- Warranty: Lifetime warranty
- Carton Quantity: 50
- Shipping (Package) Weight: 0.75 lb [0.34 kg]
- Product Weight: 11.79 oz [334 g]
- Color: Black
- Connector A: 1 - High Density DB15 (VGA) Male
- Connector B: 1 - High Density DB15 (VGA) Male
- Cable Length: 10 ft [3.05 m]
- Cable Jacket Type: PVC - Polyvinyl Chloride
- Wire Guage: 28 AWG
- Number of Ferrites: 1
- Packaging Style: Bagged

