

- The B123-001-60 has been designed for use with Tripp Lite P568-Series HDMI cables. To ensure maximum distance and performance, it is recommended that you use Tripp Lite P568-Series HDMI cabling. For distances over 75-ft, 24AWG cable such as Tripp Lite's P568-100-HD is required.
- Although most installations will not require power, a Micro USB port is provided in the event power is needed. Using a Micro USB cable (such as Tripp Lite's UR05C-Series), connect the Micro USB port to a USB wall charger, the USB port on your monitor, or the USB port on a computer.

## HDMI Signal Booster / Extender Cable, 1920 x 1200 (1080p) 60Hz, Up to 125 ft. (38 m), (HDMI M/F), 1 ft, TAA

MODEL NUMBER: **B123-001-60**



Extend a 1080p @ 60Hz (or 1920 x 1200) signal up to 125ft

### Description

Tripp Lite's B123-001-60 HDMI Signal Extender increases the distance a 1080p @ 60Hz (or 1920 x 1200) signal can be transmitted beyond the recommended 16-ft. (4.88 m). It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz, at a maximum distance of 125-ft. (38.1 m) from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p @ 60Hz (or 1920 x 1200) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable. Simply connect the longer cable between the source and the B123-001-60, and the built-in cable between the adapter and the monitor/TV. The built-in HDMI cable features a latching connector for a more secure connection. Software or drivers are not required. HDCP compliant. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Extend a 1080p @ 60Hz (or 1920 x 1200) HDMI signal up to 125-ft. (38.1 m) from the source
- Use P568-Series HDMI cables in most applications

### Highlights

- Extend a 1080p @ 60Hz (or 1920 x 1200) HDMI signal up to 125-ft. (38.1 m) from the source
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- No external power required in most installations
- Built-in HDMI cable features a latching connector for a more secure connection
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B123-001-60 HDMI Active Extender



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Built-in HDMI cable features a latching connector for a more secure connection
- When extending a 1080p @ 60Hz (or 1920 x 1200) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD.
- Lengths over 100-ft. (30.5 m) are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- No external power required in most installations
- HDCP compliant
- No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332171184
Product Type	Signal Booster
Technology	HDMI; Cat5/5e; Cat6
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (MALE)
Max Supported Video Resolution	1920x1200 @ 60Hz
Max 720P Range (ft)	125
Max 1080P Range (ft)	125
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Max 1920 x 1200 Range (ft)	125
Signal Range (ft)	125
Signal Range (m)	38
Recommended Cabling	24 AWG
Max Supported Color Depth	24-bit True Color
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
AUDIO	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Pass-through audio
<b>POWER</b>	
Power Source	Unit (Optional)
Power Source Type	USB
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.3
Number of Displays	1
Form Factor/Mounting Options	Pigtail
Shipping Dimensions (hwd / cm)	3.30 x 15.60 x 12.19
Shipping Dimensions (hwd / in.)	1.30 x 6.14 x 4.80
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.6 x 1.02 x 8.36
Unit Packaging Type	Box
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.05
Housing	Plastic
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	125
Max 480P Range (ft)	125
Max 1440 x 900 Range (ft)	125
Max 1080i Range (ft)	125
Max 480i Range (ft)	125
Max 640 x 480 Range (ft)	125
Max 800 x 600 Range (ft)	125



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max 1600 x 1200 Range (ft)	125
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	MICRO-USB B (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
Built-In Equalizer	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>