

you can
Canon

**imageFORMULA
DR-X10C**

A3 High Speed Production Scanner

High speed scanning
you can depend on

DR-X10C



imageFORMULA



The paper tray can be configured with 3 different height positions according to the volume of paper being scanned



If your business is serious about scanning, there's an outstanding mid-volume document scanner that delivers high-end performance. Introducing the DR-X10C: bringing you deadline-beating speeds, assured reliability and the highest quality scans time after time.

Great performance with maximum efficiency

The ultimate in productivity

Whatever the nature of your scanning requirements, the DR-X10C is designed to process them with maximum efficiency. That means the DR-X10C is an A3 scanner capable of 100 pages per minute* – whether scanning black & white, greyscale or colour or scanning at 200dpi or 300dpi. These incredible productivity levels are achievable because the bulk of image processing is carried out by a dedicated chip in the device's firmware, and independently of your PC.

Image Conscious

When the quality of the image is paramount, the DR-X10C comes into its own. It provides performance at optical resolution of 600dpi with numerous image enhancement capabilities. Furthermore, a High Speed Mode allows 300dpi images to be scanned and upgraded into 400dpi and 600dpi images. And to avoid dust accumulation and image deterioration, the DR-X10C uses an automatic blower, wiper, and shading mechanism to keep the sensor clean and the image quality high.

Renowned Reliability

Operators need to feel comfortable that productivity will be maintained in order for them to focus their time on other things and the DR-X10C delivers in abundance. Providing the highest standards of reliability, the DR-X10C comes equipped with a host of innovative features to ensure optimum feed reliability, outstanding double feed detection and minimal user intervention for the very highest levels of productivity.

Same speed scanning



High performance scanning and exceptional image quality.

*A4 portrait, 200/300dpi simplex

Whatever you plan to scan, it's more than likely that no two documents will be the same. The DR-X10C had been designed so that the burden of correctly feeding, handling and processing your documents is effortlessly dealt with by the device and not by you.

Designed to deliver unbeatable results

Effortless feeding

The paper tray can be configured with 3 different height positions with manual feed and bypass mode and also offset feeding (lockable side guides). This ensures there's no waiting around for scanning to begin.

Active Separation Torque Control

Batches of documents are rarely the same, with differences in paper texture, thickness and size, which is why the DRX-10C's feeder has been created to be as nimble as possible. This innovative feature provides the capability to handle a wide range of media by allowing for 5 electronically controlled torque settings. Particular benefits are found when scanning thin fragile documents where you can achieve the necessary separation without the risk of document damage occurring from over aggressive separation. This ensures the best possible levels of document separation and therefore feed reliability.

Instant size and skew detection

A dedicated image sensor, located inside the scanner, automatically and instantly detects the size and skew angle of the physical document passing through the scanner, ensuring most accurate reliable results and heightened productivity.

Ultrasonic double feed detection

Equipped with 3 independently controlled Ultrasonic Sensors, the DR-X10C offers accurate double feed detection and reliability. Additionally the sensors can be setup to trigger either ON or OFF according to a set distance from the leading edge of the scanned page - making scanning documents with sticky notes and/or labels convenient and easy - ensuring maximum productivity.

Double feed retry

This unique feature automatically reverses the documents in the feeder when a double feed is detected and tries to re-feed them again. Scanning the occasional envelope is simple too - after detection just accept the image by pressing a button on the control panel and scanning automatically continues - boosting overall productivity.

Staple detection


Canon's innovative staple detection stops feeding instantly whenever a staple is detected so that no damage occurs to the device or document.



The DR-X10C is able to handle a wide range of document sizes in one single batch



Unbeatable levels of reliability for all your document needs.



CapturePerfect software is bundled with the DR-X10C



The DR-X10C makes light work of your heaviest workloads. As well as being incredibly simple to operate it comes equipped with a range of powerful image enhancement features, Canon's CapturePerfect software, and a number of accessories: designed to help you deal with every eventuality.

Added control whenever you need it

Additional features

For added power and ease of operation, the DR-X10C comes with a suite of additional capabilities. These include auto colour detection, prevent bleed through, moiré reduction, black border removal and punch hole removal. Furthermore, text enhancement features can actually improve the legibility of your scanned documents - for example where characters are affected by deep coloured or patterned backgrounds.

CapturePerfect

For total control over scanning, from start to finish, the DR-X10C is bundled with CapturePerfect software. It offers a user-friendly interface where multiple jobs or applications can be simply setup with predefined job settings. Daily routine scanning applications can be launched quickly and easily without the need to adjust any device or output settings. Capture Perfect also has many flexible file saving options such as appending to files, saving files as searchable and encrypted PDF and much more. So you gain in every aspect of your work.

Available accessories

- Pre and Post imprinter - prints up to 32 characters - position is electronically controlled
- Patchcode Decoder (Software)
- Barcode Module III (Software)
- Kofax Hardware VRS Card (available Q3 2008)

Ideal for your business

Ideal for Specialist bureau and scanning service providers

Exceptional reliability whilst running at 100 pages per minute and with a duty cycle of 60,000 scans per day ensures the DR-X10C is the scanner you can always depend on.

Ideal for process improvement in demanding offices

Unbeatable productivity combines with effortless operation to make the DR-X10C the perfect scanner to place at the heart of your business-critical scanning processes, such as invoicing and record retention.

Everything you need for the most outstanding results.

Specifications DR-X10C

Type	Desktop Type Sheet Fed Scanner		
Document Reading Sensor	CMOS CIS 3 Line Sensor		
Optical Resolution	600dpi		
Light Source	RGB LED		
Reading Side	Front / Back / Duplex		
Interface	Dual Interface (High Speed USB 2.0 & SCSI-3)		
	Optional Kofax Hardware VRS (CGA) Card - available Q3 2008		
Dimensions	Tray closed: 528 (W) x 563 (D) x 375 (H) mm		
	Tray opened: 528 (W) x 861 (D) x 432 (H) mm		
Weight	Approx. 39 kg		
Power Requirements	AC220 - 240V (50/60Hz)		
Power Consumption	Scanning: 125W, Sleep mode: 4.5W (AC 220-240V)		
	Power Turned Off: 0W		
Operating Environment	10 - 32.5°C (50 - 90.5°F), Humidity: 20 - 80% RH		
Environmental Compliance	RoHS and ENERGY STAR		
READING SPEED¹		Simplex	Duplex
Portrait (A4)	B & W / Grayscale	200/300dpi	100ppm
	Colour	200dpi	100ppm
	Colour	300dpi	100ppm
Landscape (A4)	B & W / Grayscale	200/300dpi	128ppm
	Colour	200dpi	128ppm
	Colour	300dpi	128ppm
DOCUMENT SPECIFICATIONS			
Size	Width	50.8 - 305mm	
	Length	70 - 432mm	
Thickness	Automatic Feeding	52 - 123g/m ² (0.06 - 0.15mm)	
	Bypass Mode	42 - 255g/m ² (0.05 - 0.30mm)	
Long Document Mode	1000mm max. (Can be set on operation panel)		
	(Thickness less than 0.2mm and image data less than 348MB)		
Paper separation	Retard Roller		
	500 sheets (80 g/m ²)		
Feeder Capacity	Selectable 500, 300, 100 sheets & MANUAL / BYPASS Feeding Mode		
	Offset Feeding with lockable side guides		
Output Resolution	100 x 100dpi, 150 x 150dpi, 200 x 200dpi, 240 x 240dpi,		
	300 x 300dpi, 400 x 400dpi, 600 x 600dpi		
Output Mode	B&W / Error Diffusion / Advanced Text Enhancement I & II		
	8bit (256 level) Grayscale		
Binary	24bit color		
Grayscale			
Colour			

PRODUCT FEATURES	
Image Processing	Auto Page Size Detection & Deskew Skip Blank Page Text Orientation Recognition Auto Colour Detection Colour Dropout / Enhancement (R/G/B/Custom) Colour Enhancement (R/G/B/Custom) Advanced Text Enhancement (I & II) Moire Reduction Prevent Bleed Through / Remove Background Batch Separation Punch Hole Removal Scan Area Setting MultiStream
Device	Auto Power ON/OFF (via USB) Rapid Recovery System Ultrasonic Double Feed Detection (Sensors independently adjustable) Manual / Bypass Feeding Active Separation Torque Control Double Feed Re-Try Mechanism Job / User Registration Buttons Verify Scan / Count Only Mode Buzzer Alarm Selectable Background (White/Black)
BUNDLED SOFTWARE	ISIS / TWAIN Drivers (Windows 2000/XP Pro/ XP Home/Vista) Capture Perfect 3.0
Options	Pre-Imprinter Post-Imprinter PatchCode Decoder Barcode Model III Kofax Hardware VRS (CGA) Card - available Q3 2008
Consumables	Exchange Roller Kit Cleaning Sheets Ink Cartridges
Daily Duty Cycle	Approx. 60,000 scans / day
¹ The scanning speed depends on the specification of PC and the setting of functions.	
Canon recommends you use Canon Media for the best results. Please check media (paper) compatibility list to see which variety of paper/media is recommended.	
Some images are simulated for clarity of reproduction. All data is based on Canon's standard testing methods. This leaflet and the specifications of the product have been developed prior to the date of product launch. Final specifications are subject to change without notice. ™ and ©: All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.	



Partner Programme



imageFORMULA

you can
Canon

Canon Electronics Inc.
www.canon.com

Canon Europa N.V.
www.canon-europe.com

English-UK Edition 0120W735
© Canon Europa N.V., 2008 (0308)

Canon (UK) Ltd
Woodhatch, Reigate
Surrey RH2 8BF
Telephone No: 01737 220000
Facsimile No: 01737 220022
www.canon.co.uk

Canon Ireland
Arena Road, Sandyford Industrial Estate
Dublin 18, Ireland
Telephone No: 01-2052400
Facsimile No: 01-2958141
www.canon.ie