

47" CLASS (46.9" MEASURED DIAGONALLY)

42" CLASS (42.0" MEASURED DIAGONALLY)

47WS50MS-B

42WS50MS-B

LED Widescreen



Full HD Capable Monitor

NATIVE DISPLAY RESOLUTION
1920 x 1080 (FHD)HIGH BRIGHTNESS
700 cd/m²CONTRAST RATIO
1,300:1 (Typ.), 500,000:1 (DCR)

178° VIEWING ANGLE

VIEWING ANGLE and LIFE EXPECTANCY
Portrait and Landscape Mode

RJ-45 LAN CONTROL

DISPLAY PORT, HDMI AND DVI CONNECTION

RS-232C CONTROL

CONVENIENT EXTERNAL SPEAKER-OUT



ENERGY STAR® 5.1 COMPLIANT

SPLIT ZOOM (self video wall)
Up to 5 x 5 matrix - adjusts for bezel widthBEZEL WIDTH
(11.5mm)

USB PLAYBACK

USB PORT

TEMPERATURE SENSOR


PIP/PBP

3-YEAR LIMITED WARRANTY
(parts/labor/backlight)



DIMENSIONS

47WS50MS-B
42WS50MS-B47" CLASS (46.9" MEASURED DIAGONALLY)
42" CLASS (42.0" MEASURED DIAGONALLY)

47WS50MS-B



42WS50MS-B



Rear Jack Pack Panel



PANEL

Screen Size	47" class (46.9" measured diagonally) 42" class (42.0" measured diagonally)
Panel Technology	IPS (LED BLU)
Aspect Ratio	16:9
Native Resolution	1920 x 1080 (FHD)
Brightness	700 cd/m ²
Contrast Ratio	1,300:1 (Typ.), 500,000 (DCR)
Viewing Angle	178° / 178°
Response Time	12ms (G to G)

INPUT (REAR)

Digital	HDMI (1), DVI-D (1), Display Port (1) with HDCP for all input
Analog	Component (1), Composite (1), RGB (1) (Shared with D-Sub)
Audio	RGB/DVI-D/AV/Component (3.5φ 1)
External Control	RS232C (1), RJ45 (1)
USB	Yes (1)

OUTPUT (REAR)

Digital	DVI-D (1)
Analog	Component(1), Composite(1), RGB(1) (Shared with D-Sub)
Audio	External speaker
External Control	RS232C (1), IR (1)

AUDIO

Balance	Yes
Audio Power	20W (10W x 2)
Speaker On/off	Yes
Clear Voice II	Yes
Sound mode	Standard, Music, Cinema, Sports, Game

CABINET

Bezel Width	11.5mm
Monitor Dimensions (W x H x D)	42.2" x 24.3" x 1.2" (47") 37.9" x 21.8" x 1.3" (42")
Monitor Weight	34.6 lbs. (47"), 30.0 lbs. (42")
Carton Dimensions (W x H x D)	47.1" x 30.3" x 5.5" (47") 42.7" x 29.1" x 4.9" (42")
(Head Only)	Packed Weight (Head Only) 42.8 lbs. (47"), 36.4 lbs. (42")
VESA™ Standard Mount Interface	400mm x 400mm

SPECIAL FEATURES

Smart Energy Saving	Yes
Multimedia playback	Yes
PIP/PBP	Yes
Temperature Sensor	Yes
Tile mode (Up to 5x5)	Yes
ISM Method	Yes
Key Lock	Yes

ENVIRONMENT CONDITIONS

Operation Temperature	0°C ~ 40°C
Operation Humidity	10% ~ 80%

POWER

Power Supply	100-240V~, 50/60Hz
Power Consumption	Typical/Smart Energy Saving on 120W (Max), 85W (SES) (47") 115W (Max), 75W (SES) (42")
DPMS	1W (Set Only)/2W (With External Device)
Power Off	0.5W

STANDARD (CERTIFICATIONS)

Safety	UL, cUL, CB scheme, TUV
EMC	FCC Class "A" / VCCI / C-tick / CE / KCC
ErP/Energy Star 5.1	Yes / Yes

MEDIA PLAYER COMPATIBILITY

Slot PC compatible (optional)	Yes (MP500)
-------------------------------	-------------

SOFTWARE COMPATIBILITY

Supersign Compatibility	Elite-W / Elite-W lite
LIMITED WARRANTY	3 Years (parts/labor/backlight)

UPC CODE

42WS50MS-B	7 19192 19080 1
47WS50MS-B	7 19192 19031 3

ACCESSORIES

Accessory	Remote Controller, Power Cable, RGB Cable, Manual, ESG, IR Receiver
-----------	---

OPTIONAL ACCESSORIES

Hidden Speakers SP-2000	Black
Speaker Dimensions (W x H x D)	1.6" x 12.9" x 2.2"
Speaker Weight (each)	0.8 lbs
Optional stand (ST-200T)	
Stand Dimensions (W x H x D)	3.4" x 6.2" x 11.7"
Weight	3.1 lbs
Packaging Dimensions (W x H x D)	13" x 4.5" x 12.8"
Packed Weight	4.2 lbs

All screen images are simulated. Dimensions and weights are approximate. Design, specifications, and features subject to change without notice.

© Copyright 2012 LG Electronics USA, Inc. All Rights Reserved. "LG Life's Good" is a registered trademark of LG Corp.

ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. In Plane Switching is a trademark of LG Philips LCD Ltd. VESA is a trademark of Video Electronics Standards Association. HDMI, the HDMI logo and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing LLC. All other product and brand names are trademarks or registered trademarks of their respective companies.

Printed in the USA. September 2012

LGsolutions.com



LG

Life's Good

SPEC_42_47WS50MS_091210_PR

47WS50MS-B

42WS50MS-B

47WS50MS-B

42WS50MS-B