

Cisco Video Surveillance 6030 IP Camera

Product Overview

The Cisco® Video Surveillance 6030 IP Camera is an outdoor, high-definition, full-functioned video endpoint with industry-leading image quality and processing power. The camera is capable of full 1080p resolution at 30 frames per second (fps) while optimizing network usage with either H.264 or MJPEG compression. Contact closures allow integration with access control systems. With its open, standards-based design, the camera provides an ideal platform for integration and operation as an independent device or as part of a Cisco Video Surveillance Network.

Figure 1. Cisco Video Surveillance 6030 IP Camera



The Cisco Video Surveillance 6030 IP Camera offers a variety of benefits, including:

- **True high-definition video:** The camera streams crisp and clear 1080p (1920 x 1080) (2.1 MP) video at 30 fps while maintaining low network bandwidth.
- **Motorized focus and zoom:** The lens on the 6030 IP Dome allows the focus and zoom to be controlled remotely, greatly simplifying installations and field of view adjustments.
- **Outdoor Ready:** An IP66 rated enclosure enables outdoor mounting.
- **Dual streaming:** The camera can stream H.264 and MJPEG video simultaneously. Each video stream can be configured with individual resolution, quality, and frame-rate settings.
- **Day/night operation:** The camera provides true day/night functionality, and includes an infrared (IR) filter that automatically switches to night mode in low-light scenes. This function can be set to manual, automatic, or scheduled control.
- **Flexible power options:** The camera supports Power over Ethernet (PoE) 802.3af, 12 VDC, or 24 VAC power through an optional external power supply.

- **Medianet support:** The camera supports the Medianet interface. When connected to a Cisco switch that also supports medianet, the switch recognizes the camera as a video endpoint, and then uses SmartPort macros to set the right network parameters for the video stream on the network. In addition, the camera can be automatically discovered and configured when connected to VSM 7.0, thereby minimizing installation time and cost.

Features

Table 1 describes the features of the Cisco Video Surveillance 6030 IP Camera.

Table 1. Cisco Video Surveillance 6030 IP Camera Features

Item	Specification
Imaging device	1/2.7-in. progressive-scan CMOS
Image control	Automatic white balance (AWB), automatic gain control (AGC), automatic exposure shutter (AES), and auto and manual iris
Dynamic range	69 dB
Minimum illumination	<ul style="list-style-type: none"> • Color mode: F1.2 @ 0.4 lux • Black and white mode: F1.2 @ 0.2 lux
Lens	<ul style="list-style-type: none"> 3-9 mm DC-Iris Remote focus and zoom
Field of view	<ul style="list-style-type: none"> 37.5°~ 103.7°(horizontal) 21.6°~ 71.2°(vertical) 42.6°~111.21°(diagonal)
Camera angle adjustment	<ul style="list-style-type: none"> Pan: 350° Tilt: 80° Rotate: 350°
Shutter speed	1/5 to 1/32,000 sec
Video compression	H.264 and MJPEG
Resolution and frame rate (H.264)	<ul style="list-style-type: none"> • 1920 x 1080 @ 30 fps (1080p) • 1280 x 720 @ 30 fps (720p) • 1024 x 576 @ 30 fps • 960 x 544 @ 30 fps • 704 x 480 or 576 @ 30 or 25 fps (4CIF) • 640 x 368 @ 30 fps • 352 x 240 or 288 @ 30 or 25 fps (CIF)
Resolution and frame rate (MJPEG)	<ul style="list-style-type: none"> • 1280 x 720 @ 30 fps (720p) • 1024 x 576 @ 30 fps • 960 x 544 @ 30 fps • 704 x 480 or 576 @ 30 or 25 fps (4CIF) • 640 x 368 @ 30 fps • 352 x 240 or 288 @ 30 or 25 fps (CIF)
Video streaming	<ul style="list-style-type: none"> • Single-stream H.264 up to 1080p (1920 x 1080) @ 30 fps • Dual-stream H.264 and MJPEG • H.264: Primary stream programmable up to 1280 x 720 @ 30 fps • MJPEG: Secondary stream programmable up to 960 x 544 @ 15 fps
Protocols	Dynamic Host Control Protocol (DHCP), Hypertext Transfer Protocol (HTTP), Secure HTTP (HTTPS), Network Time Protocol (NTP), Real-Time Transport Protocol (RTP), Real-Time Streaming Protocol (RTSP), Simple Mail Transfer Protocol (SMTP), Secure Sockets Layer/Transport Layer Security (SSL/TLS), TCP/IP, Cisco Discovery Protocol, Bonjour, Simple Network Management Protocol (SNMP), and Secure Shell (SSH) Protocol
Quality of service (QoS)	Differentiated-services-code-point (DSCP) marking and class-of-service (CoS) marking

Item	Specification
Power	12 VDC or 24 VAC through optional external power supply, available separately PoE (802.3af)
Power consumption (max)	DC: 9.5W AC: 13.1W PoE: 12.72W

Table 2 lists the video stream support for the Cisco Video Surveillance 6030 IP Camera for 16:9 Aspect Ratios.

Table 2. Cisco Video Surveillance 6030 IP Camera Video Stream Support for 16:9 Aspect Ratios

Primary (H.264)	Maximum fps	Secondary (H.264 or MJPEG)	Maximum fps
1920 x 1080	30	-	-
1920 x 1080	15	1024 x 576 960 x 544 640 x 368	15
1280 x 720	30	1024 x 576 960 x 544 640 x 368	15
1024 x 576	30	1024 x 576 960 x 544 640 x 368	15
960 x 544	30	960 x 544 640 x 368	15
640 x 368	30	640 x 368	15

Table 3 lists the video stream support for the Cisco Video Surveillance 6030 IP Camera for 4:3 Aspect Ratios.

Table 3. Cisco Video Surveillance 6030 IP Camera Video Stream Support for 4:3 Aspect Ratios

Primary (H.264)	Maximum fps	Secondary (H.264 or MJPEG)	Maximum fps
720 x 480/576	30/25	720 x 480/576 704 x 480/576 352 x 240/288	15
704 x 480/576	30/25	704 x 480/576 352 x 240/288	15
352 x 240/288	30/25	352 x 240/288	15

Connectors

Table 4 describes the connectivity and connectors of the Cisco Video Surveillance 6030 IP Camera.

Table 4. Cisco Video Surveillance 6030 IP Camera Connectors

Item	Specification
Network connectivity	100 BASE-TX Ethernet with RJ-45 connector
Alarm input	One logic level programmable
Alarm output*	One logic level programmable
Power input	Terminal block

* Not supported when the camera is used with Cisco Video Surveillance Manager.

Software

Table 5 describes the primary features of the Cisco Video Surveillance 6030 IP Camera software.

Table 5. Cisco Video Surveillance 6030 IP Camera Primary Software Features

Item	Specification
Activity detection	User-definable alerts with configurable sensitivities and thresholds, email alert, and HTTP notifications
Video format	NTSC and PAL
Image settings	Configurable brightness, sharpness, contrast, saturation, hue, and white balance
Overlay capabilities	Time, date, and text
Selectable bit rate	Support for constant bit rate or variable bit rate
IP filtering	Ability for users to enter a list of allowed or blocked IP addresses for viewing video and configuring camera settings
Discovery	Cisco Discovery Protocol and Bonjour Zero-Configuration discovery
Configuration	<ul style="list-style-type: none">• Browser-based using Internet Explorer 8 and later• Two levels of user access with password protection
Security	Support for IEEE 802.1X authentication

Specifications


Table 6 provides specifications of the Cisco Video Surveillance 6030 IP Camera.

Table 6. Cisco Video Surveillance 6030 IP Camera Mechanical Specifications

Item	Specification	
Housing	Aluminum	
LEDs	Power and activity	
Dimensions (D x H)	6.9 x 4.5 inches (174 x 115 mm)	
Weight	1296g	
Certifications	Safety: UL60950-1 2 nd edition CSA22.2-No.60950-1 IEC/EN60950-1 2 nd edition IEC/EN60825	EMC Requirements: CISPR22 Class B ICES-003 EN55022 EN55024 EN61000-3-2/-3-3 Class A VCCI Class B KN22 Class B KN24
Operating temperature	-40 to 131°F (-40 to 55°C) Cold startup: -40°C	

Figure 2 shows the dimensions of the Cisco Video Surveillance 6030 IP Cameras. Note that all dimensions are in millimeters.

Figure 2. Cisco Video Surveillance 6030 IP Camera Dimensions



Package Contents

Table 7 describes the items that ship with the Cisco Video Surveillance 6030 IP Camera.

Table 7. Package Contents

Item
Cisco Video Surveillance 6030 IP Camera
Installation template and alignment sticker
Bushing and connectors
L type hex wrench
Screws and nuts
Desiccant pack
Documentation reference card
Regulatory documentation

Availability

The Cisco Video Surveillance 6030 IP Camera is available through Cisco Authorized Technology Provider (ATP) Partners.

Ordering Information

Table 8 lists the part numbers for the Cisco Video Surveillance 6030 IP Camera and for the lenses that the camera supports.

Table 8. Ordering Information

Part Number	Description
CIVS-IPC-6030	Cisco Video Surveillance IP Camera, Outdoor VR HD Dome Body
CIVS-IPCA-PWR12V	12 VDC Power Supply

Using the Camera with Cisco Video Surveillance Manager

Features that are marked with an asterisk (*) are not supported when using the camera with Cisco Video Surveillance Manager. Please refer to the release notes for Cisco Video Surveillance Manager 6.3 for more information:

http://www.cisco.com/en/US/docs/security/physical_security/video_surveillance/network/vsm/release_notes/6_3/vsm_rn_63.html.

Services and Support

Cisco and our certified partners can help you accelerate success and improve the return on your investment in a Cisco Physical Security solution. The Cisco lifecycle approach to services defines the requisite activities at each phase of the solution lifecycle. This approach allows you to:

- Reduce deployment costs by identifying the features that will best meet your business requirements
- Accelerate migration by assessing the readiness of your network to support the system and by developing a sound design
- Support smooth implementation through effective planning and expert installation, configuration, and integration
- Increase operational efficiency and extend the value of your investment with award-winning technical support

For more information about Cisco Services, please visit <http://www.cisco.com/go/services>.

For More Information

For more information about the Cisco Video Surveillance 6030 IP Camera, please visit <http://www.cisco.com/go/physec> or contact your local Cisco account representative.



Americas Headquarters
Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters
Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters
Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at www.cisco.com/go/offices.

 Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: www.cisco.com/go/trademarks. Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)