



HP Pavilion 25xi 25-inch IPS LED Backlit Monitor

Multi-tasking just got better. Stunning visuals, Full-HD¹ resolution, and IPS widescreen technology in a bold new micro-thin, bezel-less design.



Share photos, videos, and games with everyone in the room and experience the same great views from almost any angle on the all new HP Pavilion 25xi 25-inch IPS LED Backlit Monitor. Incredible performance, vivid colors, and smart HP My Display software sweeten the deal.

Less distortion. Less blurring. Happy spectators.

In-plane Switching (IPS), the color-rich technology you know and love in tablets, mobile devices, and televisions, is now available in a micro-thin display designed for the home. That means image and color consistency from almost anywhere in the room.

Beauty and brains

Modernize your home desktop with a contemporary, bezel-less design that delivers maximum views of all your favorite images and on-screen content. Save space in style, too. The unique, micro-thin profile fits virtually anywhere without taking up valuable space. Do more with a dual-monitor setup enabled by the smart, plug-and-play design. Stay connected to current and evolving devices with built-in VGA, DVI, and HDMI inputs (with HDCP).

Smooth Surface panel

BrightView panels reduce glare by reflecting light away from you with no loss of contrast.

Jaw-dropping details

Bring your memories to life with eye-popping details. HP Enhance+ delivers super-crisp images and advanced noise reduction. Enjoy a crisp, detailed view with Full HD¹ 1920 x 1080 resolution and 10,000,000:1 dynamic contrast ratio.² Give your photos, videos, and online games³ more depth and see the difference with deeper blacks and whiter whites.

Software that simplifies

Control power-saving modes and customize screen settings with integrated HP My Display software, which also lets you partition your screen so you can work with multiple open application windows at the same time.

HP on your side

Help reduce your power consumption and cut back on energy costs with an intelligent, energy-efficient design built with the environment in mind. Mercury-free LED backlighting, a BFR/PVC-free design⁴, arsenic-free display⁵ glass, and recyclable packaging are just a few of the responsible details built right into your display.

Gain peace of mind from HP's award-winning service and support and relax with a standard, one-year limited warranty.

HP Pavilion 25xi 25-inch IPS LED Backlit Monitor

Part number	B7B82AA#ABA
Panel type	IPS with Brightview technology
Viewable image area	63.5 cm (25 in) diagonally measured
Viewing angle	Up to 178° horizontal/178° vertical
Brightness²	250 nits (cd/m ²)
Contrast ratio²	1,000:1 (typical); 10,000,000:1 (dynamic)
Response rate²	7 ms (GtG)
Frequency	Horizontal: 24 to 94 kHz Vertical: 50 to 76 Hz
Aspect ratio	16:9
Native resolution	1920 x 1080 @ 60 Hz (Full HD) ¹
Resolutions supported	1920 x 1080 @ 60 Hz, 1680 x 1050 @ 60 Hz, 1600 x 900 @ 60 Hz, 1440 x 900 @ 60 Hz, 1280 x 1024 @ 60 Hz, 1280 x 720 @ 60 Hz, 1024 x 768 @ 60 Hz, 800 x 600 @ 60 Hz, 720 x 400 @ 70 Hz, 640 x 480 @ 60 Hz
Input signal	(1) VGA, (1) HDMI, and (1) DVI-D, HDCP support; 1.8 m (5.9 ft) DVI-D cable included; VGA and HDMI cables also included in select regions.
User controls (on-screen display)	Brightness, contrast, color, image control, OSD control, management, language, information, factory reset, source control, exit
External Speakers	One pair of two (2) watt speakers. USB powered. Frequency Response 180Hz~20KHz, S/N Ratio >75dB, Separation >40dB (available in Singapore, Taiwan, India, Australia, Japan) (Korea TBD)
Power consumption	Maximum: 30 watts Typical: 28 watts Power saving: <0.5 watts
Dimensions (w x d x h)	Unpacked: 577.7 x192.3 x 429.4 mm (22.74 x 7.57 x 16.91 in) Head only: 577.7 x 35 x 358 mm (22.74 x 1.38 x 14.09 in)
Weight	Unpacked: 4.4 kg (9.71 lb) Head only: 3.4 kg (7.57 lb)
Base features	Tilt: -5° to +25° vertical
Environmental	Operating: 5° to 35° C (41° to 95° F) Non-operating: -20° to 60° C (-34° to 140° F)
Certification and compliance	CB, CE, FCC marking, ES 5.2, ErP, CSA/C-UL/C-ETL Mark, UL/CSA-NTRL/ETL-NRTL Mark, ICES, Argentina S-Mark, Japan VCCI, CCC, China CEL, Taiwan BSMI, Bauart, CECP, ISO9241-307, GOST 25861, HRN N N.201, GOST R 50377-1992, GOST 25861, EEI certificate, IS 1121, SASO, SABS IEC 60950-1, NOM-019-SCFI-1998, KC Mark, KCC Mark, PSB mark, ISC mark, C-Tick
Limited warranty	Protected by an HP standard limited warranty (1-1-0). Certain restrictions and exclusions apply.

1. High definition (HD) content is required to view HD images.

2. All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

3. Internet access required and sold separately.

4. Meeting the industry definition of 'BFR/PVC-free' per the iNEMI Position Statement on "Low Halogen" Electronics. Plastic parts incorporated into the chassis generally contain < 1000 ppm (0.1%) of bromine or chlorine. Printed circuit board and substrate laminates generally contain < 1500 ppm (0.15%) of total bromine and chlorine. Service parts after purchase may not be BFR/PVC-free. External accessories, including power supplies, power cords, and peripherals are not BFR/PVC-free.

5. Arsenic and its compounds were not detected using U.S. EPA test methods 3052/6010b by ICP-AES with a MDL 10 ppm.

© Copyright 2012 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. September 2012

