

SmartPro 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS, 2U Rack/Tower, WEBCARDLX Network Interface, LCD, USB, 8 Outlets

MODEL NUMBER: **SMART1500RM2UN**



Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Pre-installed WEBCARDLX network interface permits remote UPS management 24/7.

Description

The SMART1500RM2UN SmartPro® 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up servers and network storage devices, the SMART1500RM2UN switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Featuring eight NEMA 5-15R outlets (four switchable) and a 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input, the SMART1500RM2UN has an internal battery that provides 13 minutes of support at half load and 4.5 minutes at full load.

The Java-free HTML5-based WEBCARDLX interface enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities. Protocols supported include IPv4, IPv6, HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP.

Automatic voltage regulation (AVR) maintains 120V nominal output over an input range of 83V to 147V without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage.

Highlights

- Corrects under- and overvoltages from 83V to 147V
- 8 NEMA 5-15R outlets—4 switchable via network interface
- Pre-installed WEBCARDLX network interface for remote management
- Interactive LCD monitoring screen
- 13 min. runtime at half load; 4.5 min. at full load
- To enable the Auto Probe feature, this product requires LX firmware update 15.5.2 or later to be installed

Package Includes

- SMART1500RM2UN SmartPro 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS
- Pre-installed WEBCARDLX network interface
- USB-B to USB-A cable
- Micro-USB to USB-A configuration/console cable
- DB9 cable
- EPO cable
- 4-Post rack mounting hardware
- Owner's manual



Features

Protects Mission-Critical Rack-Mounted Equipment Provides fully regulated sine wave AC output for servers, network storage devices and telecom hardware Audible alarm signals loss of utility power, overload, low battery and fault conditions 8 NEMA 5-15R outlets (4 are switchable) 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input 0.9 power factor rating 570-joule surge suppression rating

Reliable Battery Backup Supports half load up to 13 min. and full load up to 4.5 min. Internal batteries designed for hot-swap field replacement 95% line-power efficiency rating saves money in energy costs

Pre-Installed WEBCARDLX Network Interface Network interface supports simultaneous communications via built-in USB, DB9 serial/contact-closure and pre-installed WEBCARDLX network management card Allows full remote access for power monitoring, configuration, control and email notifications via secure web browser, SNMP, Telnet, SSH, or Command Line. Supports 10/100 Mbps auto-sensing for communication with an Ethernet network. Optional EnviroSense2 sensors (sold separately) enable site monitoring of temperature, humidity and contact-closure status Reduce Service Calls with Auto Probe Autonomous Device Management. The Auto Probe feature (Firmware 15.5.2 and greater) checks the connectivity status of any networked device and automatically takes one or more user-configured actions if the device fails to respond; actions include outlet reboot, set SNMP traps, SNMP OID sets, and even script execution when used in conjunction with the Tripp Lite PowerAlert Network Shutdown Agent (PANSA)

2 Load Banks with Switchable Outlets Can control 4 outlets remotely to reboot equipment or shed nonessential loads

Automatic Voltage Regulation (AVR) Maintains 120V nominal output over input range of 83V-147V without using battery power

EMI/RFI Line Noise Filtering Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

Interactive LCD Screen Front-panel LCD signals operating mode, load level, voltage, battery charge and estimated runtimes Rotates for easy viewing in rack-mount or tower configurations

Communications Ports USB and DB9 ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software (available via free download from www.tripplite.com/poweralert) EPO port supports emergency shutdown in large facilities

Versatile Installation Options Hardware included for 4-post mounting in 2U of EIA-standard 19 in. rack Mounts on wall or 2-post rack with optional 2POSTRMKITWMM accessory Mounts in upright tower position with optional 2-9USTAND accessory

Specifications

OVERVIEW	
UPC Code	037332178237
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	



Output Volt Amp Capacity (VA)	1500
Output kVA Capacity (kVA)	1.5
Output Watt Capacity (Watts)	1350
Output kW Capacity (kW)	1.35
Power Factor	0.9
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-21%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable two-outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	4.5 min. (1350w)
Half Load Runtime (min.)	13 min. (675w)
Expandable Runtime	No
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	 RBC93-2U
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 83 and 107 are boosted by 14%
USER INTERFACE, ALERTS & CONTROLS	



Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions. LX Platform Interface: Recessed reset switch for interface reboot and factory reset.
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	Network Link/Activity (Green): Flashes for network activity. Network Speed (Yellow): 10 Mbps (Flashing), 100 Mbps (On steady). LX Platform Interface Status: Normal Operation (Solid Green); Software Update (Alternating Green/Orange ~1/sec); Factory Reset (Alternating Green/Orange ~2/sec).
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 2-4 post front rail rackmount (UPSHDEARKIT); 4 post rackmount short-depth (4POSTRAILKITWM); Tower (2-9USTAND); Wallmount (2POSTRMKITWM);
Minimum Required Rack Depth (cm)	41.91
Minimum Required Rack Depth (inches)	16.5
Optional Mounting Accessory Notes	Optional 2-9USTAND enables upright tower UPS placement; 2POSTRMKITWM enables wall-mount and 2-post rackmount installation; 4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); UPSHDEARKIT enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	342
Primary UPS Height (mm)	88
Primary UPS Width (mm)	439
Rack Height	2U



Shipping Dimensions (hwd / cm)	21.59 x 59.18 x 49.78
Shipping Dimensions (hwd / in.)	8.50 x 23.30 x 19.60
Shipping Weight (kg)	26.76
Shipping Weight (lbs.)	59.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.76 x 43.94 x 34.16
UPS Power Module Dimensions (hwd, in.)	3.45 x 17.3 x 13.45
UPS Power Module Weight (kg)	21.09
UPS Power Module Weight (lbs.)	46.5
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	267
Battery Mode BTU / Hr. (Full Load)	1012
AC Mode Efficiency Rating (100% Load)	95%
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Monitoring Port Description	Includes Pre-installed WEBCARDLX Network Management interface card. RJ45 Network port, Micro-USB Configuration/Console port, USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules.
PowerAlert Software	For local monitoring via the UPS's built-in Serial or USB communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	Micro-USB, USB, and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
EPO Port	RJ11 interface jack with 4 meter cable included. Supports normally open and normally closed EPO systems
SNMP Compatibility	SNMPv1, V2c, V3
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
Network Speed	10/100 Mbps
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds



Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (included); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>