

HSM® shredstar

BS10Cs document shredder



- Continuous Duty Operation
- Casters for mobility and shared use
- 430 particles per page
- Manual reversing function
- Full bag indicator
- Overload protection
- Automatic start/stop
- Anti-Jam Technology with automatic reversing function designed to quickly and easily reverse out paper in the event the machine is overloaded
- Level indicator of waste container through inspection window
- Equipped with an Energy Management Control System (EMCS) putting shredder into energy saving standby mode after 30 minutes of being idle
- 2 year warranty on parts
- Lifetime warranty on cutting heads
- Optional: Uses a 11 gallon capacity shred bag; Part #HSM1310



HSM part#	HSM1053
Cutting type	Cross cut
Cutting size	5/32" x 1 3/8"
Security level DIN 32757-1	3
Security level DIN 66399	P-4 / F-1
Cutting capacity per run in sheets	10
Cutting Speed	7.2 ft / min
Throat opening	8.9"
Motor at maximum no of sheets	250W
Motor power (horsepower)	0.27
Voltage	115 V / 60Hz
Dimensions (H x W x D)	16.75" x 18.25" x 8.6"
Weight	17 lbs
Shred-bin volume	5 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downington, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®