

Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/MTRJ - 1 m

StarTech ID: 50FIBLCMT1



The 50FIBLCMT1 1m LSZH LC to MTRJ Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-MTRJ patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

Applications

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- Immune to electrical interference
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM2
Fiber Type	Multi Mode
Connector A	2 - Fiber Optic LC Duplex Male
Connector B	1 - Fiber Optic MT-RJ Male
Cable Length	3.3 ft [1 m]
Color	Orange
Product Length	3.3 ft [1 m]
Shipping (Package) Weight	0 lb [0 kg]