

960H Diamond Dome™ Series Miniature Indoor Camera

CDD11HW 3.6mm fixed lens

Features

- 1/3" 960H Sony Super-HAD II™ CCD
- 700 TV lines of resolution
- Unique and stylish housing for attractive indoor installation
- Small form factor for an unobtrusive look
- 3-axis wall or ceiling mount
- Full OSD operation
- 5 year warranty

Specifications

Image Sensor	1/3" 960H Sony Super-HAD II™ CCD
Resolution	700 TV lines
Minimum Illumination	Color: 0.1 lux, BW: 0.01 lux
Total Pixels	1028 (H) x 508 (V)
Effective Pixels	976 (H) x 494 (V)
Scanning System	2:1 interlace
Synchronization	Internal
OSD	Available
Backlight Compensation	BLC / HLC
S/N (Y signal)	52dB (AGC Off)
White Balance	ATW1 / ATW2 / ATW / Manual
Electronic Shutter Speed	Auto (1/60 sec. - 1/100,000 sec.)
2D-DNR	On / Off



WDR	DWDR
DPC	Auto / Manual / Off
Motion Detection	On / Off (4 zone)
Privacy	On / Off (8 zone)
Mirror	On / Off
Parking Line	Available
Sharpness	0 - 31 (level adjustable)
Day/Night	Auto / Color / BW / Ext
Power Supply	12VDC (power supply not included)
Power Consumption	200mA
Operating Temperature	14° F – 122° F
Dimensions	2.52" (H) x 2.87" (D)
Weight	4 oz.

Optional Accessory



Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.



Rev. 2/18/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com