

High performance LCD projector captures attention in classrooms or conference rooms with dynamic images and 3,000 ANSI lumens.



## Key Features

- WXGA 1280 x 800 resolution
- 3,000 ANSI lumens white/color output
- 16 watt audio output
- 4000:1 contrast ratio
- HDMI 1 input
- 5,000 hours hybrid filter\*
- 5,000 hours lamp life (Standard mode) and 6,000 hours lamp life (Eco mode)\*\*
- Power saving standby mode less than 0.5W



From the classroom to the conference room, Hitachi's CP-WX3030WN LCD projector combines superior image clarity, high quality value, and long-life reliability. Bright, vivid colors with razor-sharp text and bold graphics will truly enhance any lesson or meeting and make it more memorable. For greater installation convenience, the CP-WX3030WN has a cloning function which enables you to copy configuration settings from one projector to others of the same model via USB memory. The CP-WX3030WN also includes our iOS application Projector Quick Connection App which offers simple control options including sending photo and document files and web site contents to the projector. Plus, Hitachi's Intelligent Eco Mode with ImageCare combines optimal picture performance with maximum energy savings for a lower total cost of ownership. For added peace of mind, Hitachi's CP-WX3030WN is also backed by a generous warranty and our world-class service and support programs.

# CP-WX3030WN

## UNIQUE FEATURES

### Cloning Function



Copy configuration settings from one projector to others of the same model via USB memory. Cloning can save almost all PJ settings such as gamma and keystone via USB memory.

### Drawing Function with Optional Tablet (TB-1)



The optional Hitachi wireless tablet and pen allows you to engage your audience by annotating over images shown on the projector.

### ImageCare Technology



ImageCare is a lamp power control function that combines optimal picture performance with maximum energy savings by decreasing energy usage, improving contrast ratio and lengthening lamp life. The result is a lower total cost of ownership and decreased maintenance cost.

### Intelligent Eco and Saver Modes



Automatically changes the brightness of the lamp according to the brightness level of the screen. Also, automatically changes the brightness of the lamp if there is no change in the screen image. Using ImageCare technology, these features give optimal picture performance with maximum energy savings.

### Projector Quick Connection iPad App



Our iOS application offers full projector control and also provides the capability to display photos, document files and web site contents. Available for iPad® and iPhone® devices. Works over your LAN via your RJ-45 port or via an optional USBWL11N wireless adapter.

### Wired and Wireless Switcher Solutions



Multifunctional switcher operates in conjunction with the receiver to provide expanded source selection and switching options for connected devices. The switcher is sold as an optional accessory that can provide 1080p 30 fps wireless via WHDI for both video and audio.

## STANDARD FEATURES

### Display via USB



Simply plug and play using the USB port instead of the 15-pin D-sub VGA cable.

### Input Source Naming



Users can rename input sources in more descriptive terms instead of the factory default names. **Exclusive to Hitachi.**

### Microphone Input



A microphone can be used via the jack located on the input panel. Allows for more dynamic presentations even in standby mode.

### Network Control, Maintenance and Security



Embedded networking gives you the ability to manage and control multiple projectors over your LAN. Features include scheduling of events, centralized reporting, image transfer and e-mail alerts for reactive and routine maintenance.

### PC-Less Presentation



By using a USB memory stick or other storage device, you can use the projector without a computer. Menus are easy to see with a thumbnail display. There is also a slideshow function. This feature also supports the following file types: JPG, PNG, BMP, GIF, AVI, and MOV — frame rate is under 12fps 640 x 480.

### PIN Lock / MyScreen / MyText



PIN lock protection can limit projector users. MyScreen PIN lock keeps captured images on the startup screen. Users can set any name logo to MyScreen, clearly identifying ownership. MyText provides the ability to write text on the startup screen such as model name, serial number or location.

### PJMessenger



PJMessenger function allows you to send and display text messages and audio alerts on your networked projectors. It is an easy and efficient way to send announcements out to multiple units.

### Present Content via LAN



Hitachi's suite of networking software allows you to easily send content directly from your PC to the projector via your LAN connection.

### Serial Number and Media Access Control Label



A label is affixed to side of projector to more easily access and read the model name, serial number and MAC address while mounted in ceiling use. This is a convenience for installers, end users and auditors for instant accessibility.

### Wireless Presentation Compatible



Connect the projector to a computer or your network using the optional USB wireless adapter (part number USBWL11N). The adapter supports IEEE802.11b/g and the latest 11n.



# CP-WX3030WN LCD Projector

**HITACHI**  
Inspire the Next

## Long-life reliability with a lower total cost of ownership.

From classrooms to conference rooms, Hitachi's CP-WX3030WN can make a big impact on your audience. With 3,000 ANSI lumens brightness and WXGA 1280 x 800 resolution, the CP-WX3030WN is designed to make any message more memorable with colorful images, crisp text, and powerfully



clear audio. Incorporating Hitachi's leading-edge technology, the CP-WX3030WN features high contrast ratio, long lamp life, cloning function enabling you to copy configuration settings from one projector to others of the same model, and is wireless presentation compatible. Plus, embedded networking gives you the ability to manage and control multiple projectors over your LAN (scheduling of events, centralized reporting, image transfer, and e-mail alerts). Even with the the array of advanced features, Hitachi's CP-WX3030WN is designed for user-friendly operation and installation convenience.



Front View



Top View




Left Profile



Right Profile



## Input/Outputs



- |                    |                      |                      |
|--------------------|----------------------|----------------------|
| 1. USB Type A x 2  | 7. Control (RS-232C) | 13. Audio in 1 and 2 |
| 2. USB Type B      | 8. Kensington Lock   | 14. Monitor Out      |
| 3. HDMI            | 9. Microphone Input  | 15. AC               |
| 4. Computer in 1   | 10. S-Video          | 16. Security Bar     |
| 5. Computer in 2   | 11. Audio Out        | 17. LAN              |
| 6. Composite Video | 12. Audio in 3       |                      |



3LCD Technology



Closed Captioning



Crestron  
Integrated Partner



AMX Device  
Discovery



Hitachi Trade-Up  
Program



3 Year Warranty

**HDMI** HDMI

HI0187-04/13 WEB  
All specifications subject to change without notice.  
3LCD and the 3LCD logo are registered trademarks of the Seiko Epson Corporation.  
©2013 Hitachi America, Ltd. All Rights Reserved.

### Hitachi America, Ltd.

900 Hitachi Way, Chula Vista, CA 91914  
Toll Free: 1.800.HITACHI • Email: dmd.info@hal.hitachi.com  
Web: hitachi-america.us/projectors

# CP-WX3030WN



# CP-WX3030WN LCD Projector

**HITACHI**  
Inspire the Next




Accessories and Lenses	
<b>Supplied Accessories</b>	Remote control, power cord, computer cable, user's manual, security label, application CD, adapter cover
<b>Optional Accessories</b>	USBWL11N USB wireless adapter, TB-1 (wireless USB tablet), MS-1 switcher, MS-1WL wireless multifunction switcher, LCDSC2000 soft sided case
<b>Optional Lenses</b>	NA
Replacement Parts	
<b>Lamp</b>	DT01481
<b>Remote Control</b>	HL02881
<b>Filter</b>	UX38841

**Projection Throw Chart**

Screen Size 16:10		Throw Distance	
Diagonal	Width	Min	Max
30	25	36	44
60	51	74	89
80	68	99	120
100	85	125	150
200	170	251	302
300	254	378	454

Throw Ratio: 1.5 - 1.8 : 1 (distance : width)  
Screen size and throw distance are measured in inches.

Specifications			
Display	Projection Technology		3LCD, 3 chip technology
	Resolution		WXGA - 1280 x 800
	White Light Output		3,000 ANSI lumens
	Color Light Output		3,000 ANSI lumens
	Colors		1074 million colors
	Aspect Ratio		Native 16:10 and 4:3 / 16:9 compatible
	Contrast Ratio		4000 : 1 (using active IRIS)
	Throw Ratio (distance : width)		1.5 - 1.8 : 1
	Focus Distance		36" - 454"
	Display size	30" - 300"	
Lens & Operation	Lens	F = 1.9 - 2.3, f = 19 - 23 mm, x 1.2 manual zoom	
	Lamp Wattage	225W	
	Expected Lamp Life*	Approximately 5,000 hours (standard mode) 6,000 hours (Eco mode)	
	Expected Filter Life**	Approximately 5,000 hours	
	Speaker Output	16W	
	Acoustic Noise Level	37 dB (29 dB in Eco mode)	
	Keystone	+/- 30° vertical only	
Compatibility	Computer	VGA, SVGA, XGA, WXGA, WXGA+/SXGA/WSXGA+/UXGA (compressed) MAC 16"	
	H-Sync	31.5 kHz - 106 kHz	
	V-Sync	56 Hz - 120 Hz	
	Composite Video	NTSC, NTSC4.43, PAL, PAL-M, -N, SECAM	
	Component Video	480i, 480p, 576i, 720p, 1080i, 1080p	
	HDMI	480i, 480p, 576i, 720p, 1080i, 1080p, Computer signal TMDS Clock 27 MHz - 150 MHz	
Connectors	Digital Input	HDMI x 1 (HDCP compliant)	
	Computer Input 1	15-pin mini D-sub x 1	
	Computer Input 2	15-pin mini D-sub x 1	
	Computer Monitor Output	15-pin mini D-sub x 1	
	Video Input		
	S-Video	Mini DIN 4-pin x 1	
	Composite Video	RCA jack x 1	
	Component Video	15-pin mini D-sub x 2 (shared with computer in 1/2)	
	Audio Input	3.5 mm stereo mini jack x 2, RCA jack (L/R) x 1, MIC-in 3.5 mm mini jack x 1	
	Audio Output	RCA jack (L/R) x 1	
	Network LAN Wired	RJ-45 port (10 base-T / 100 base-TX)	
	Network LAN Wireless	USB-A, IEEE802.11 b/g/n - optional wireless adapter required	
Ratings & Warranty	USB	Type A x 2 (PC-less presentation, wireless adapter, TB-1) Type B x 1 (USB display or mouse control)	
	Control Terminals	9-pin D-sub x 1 (RS-232 control)	
	Power Supply	AC100-120V / AC220-240V, 50/60Hz	
	Power Consumption	320W	
	Operating Temperature	40°F - 95°F (5°C - 35°C)	
	Dimensions (W x D x H)	12.6" x 9.7" x 3.4" (excl. protruding parts)	
	Weight	approx. 6.8 lbs.	
	Approvals	UL 60950-1 / cUL FCC Part 15 subpart B class B	
Warranty	3 year limited parts and labor Extended Service Contract available (additional cost)		

\* Actual lamp life will vary by individual lamp and based on environmental conditions, selected operating mode, user settings and usage. Hours of average lamp life specified are not guaranteed and do not constitute part of the product or lamp warranty. Lamp brightness decreases over time.

\*\* Actual filter life will vary by individual filter and based on environmental conditions, selected operating mode, user settings and usage. Hours of average filter life specified are not guaranteed and do not constitute part of the product warranty.

# CP-WX3030WN

HI0187-04/13 WEB  
All specifications subject to change without notice.  
3LCD and the 3LCD logo are registered trademarks of the Seiko Epson Corporation.  
©2013 Hitachi America, Ltd. All Rights Reserved.

**Hitachi America, Ltd.**

900 Hitachi Way, Chula Vista, CA 91914

Toll Free: 1.800.HITACHI • Email: dmd.info@hal.hitachi.com

Web: hitachi-america.us/projectors

