

# Symbol LS2208

Handheld scanner



#### **FEATURES**

#### Durable construction: single board construction; meets Motorola's stringent 5 ft. drop tests; scratchresistant tempered glass exit window

Designed for continuous usage all day, every day; significantly reduces downtime and repair costs

### High performance 1D laser scanner

Accurate first time scanning; always ready for the next scan; increased productivity resulting in shorter check-out lines and better customer service

Wide working range: contact to 17 in./43 cm on 100% UPC/EAN symbols Improves productivity

#### Increased productivity, lower TCO

The Symbol LS2208 handheld scanner from Motorola offers high performance scanning at a moderate price point. From the retail point-of-sale and backroom to the patient bedside or school book checkout, the Symbol LS2208 provides fast, reliable scanning in a durable, lightweight form factor, delivering enhanced productivity and efficiency while reducing your total cost of ownership (TCO).

#### **High performance scanning – fast**

With aggressive scanning capabilities and a wide working range, the Symbol LS2208 accurately captures data fast, helping employees work quickly and efficiently. And you'll be up and running fast, because the Symbol LS2208 is easy to deploy and use, thanks to its plug-and-play installation and intuitive, user-friendly design, which requires little or no training. Plus the ergonomic, balanced form factor reduces user fatigue to maximize user comfort.

#### **Durable, future-proof construction**

The Symbol LS2208 is engineered for continuous, heavy usage all day, every day and has been tested to withstand multiple 5 ft./1.5m drops to concrete. The patented single board construction eliminates a common point of failure – the interconnection between multiple boards, and the liquid polymer scan element delivers integral shock protection to further ensure reliable operation. Scratch-resistant tempered glass helps preserve bar code scanning accuracy. Integrated multiple interfaces, universal cable compatibility and support for emerging symbologies provide the investment protection you need to help ensure that the scanner you buy today will work with the system you use tomorrow.

#### Proven quality you can trust

When you choose the Symbol LS2208, you receive the added assurance of purchasing a product from Motorola — the global leader in handheld bar code scanning with millions of scanners in use every day by the world's largest retailers worldwide. And since even the most durable scanners require a support plan, Motorola's Service from the Start Advance Exchange Support provides next-business-day delivery of a replacement device for true service peace of mind. This offering also includes Motorola's unique Comprehensive Coverage, which extends normal wear and tear to cover accidental damage to exit windows, scan elements, housings and more at no extra charge — virtually eliminating your unforeseen repair expenses.

For more information about the LS2208 handheld scanner, visit us at www.motorolasolutions.com/ LS2208 or access our global contact directory at www.motorolasolutions.com/enterprisemobility/ contactus Symbol LS2208

#### Multiple interfaces: available

Simplifies installation and integration; future-proof solution helps ensure compatibility with your host/ POS today and tomorrow

#### Plug-and-play; universal

cable; intuitive scanning Rapid deployment; single cable connects to any computing environment; practically eliminates setup and training time for faster return on investment

#### Ergonomic and

**lightweight design** Reduces user fatigue with sleek, balanced form for maximum user comfort and productivity

#### Hands-free Intellistand™

Enables presentation scanning and easy switching between hands-free and handheld modes

#### Advanced Data Formatting (ADF)

Enables users to modify data prior to sending to host computer, reducing costly modifications to the host software

## Symbol LS2208 Specifications

Physical Characteristics			
Dimensions:	6 in. H x 2.5 in. W x 3.34 in. D 15.2 cm H x 6.3 cm W x 8.4 cm		
Weight:	5.15 oz./146 gm		
Voltage and Current:	5 volts +/- 10% at 130 mA typical, 175 mA max		
Power Source:	Host power or external power supply		
Color:	Cash Register White or Twilight Black		
Performance Characteristics			
Scanner Type:	Bi-directional		
Light Source:	650 nm visible laser diode		
Scan Element Frequency: 50Hz			
Scan Rate:	100 scans per second typical		
Nominal Working Distance:	See chart below.		
Print Contrast:	20% minimum reflective difference		
Roll (Tilt): 1	1 +/- 30 degrees		
Pitch: <sup>2</sup>	2 +/- 65 degrees		
Skew (Yaw): <sup>3</sup>	3 +/- 60 degrees		
Code 128, Code 128	UPC/EAN, UPC/EAN with Supplementals, 39, Code 39 Full ASCII, Code 39 TriOptic, Full ASCII, Codabar, Interleaved 2 of 5, 93, MSI, Code 11, IATA, GS1 DataBar ts, Chinese 2 of 5		

Interfaces Supported:	USB, RS232, Keyboard Wedge, Wand, IBM 468x/9x, Synapse and Undecoded	
User Environment		
Operating Temp.:	32° to 122° F/0° to 50° C	
Storage Temp.:	-40° to 158° F/-40° to 70° C	
Humidity:	5% to 95% relative humidity, noncondensing	
Drop Specifications:	Unit functions normally after repeated 5 ft./1.5 m drops to concrete	
Ambient Lighting Tolerance:	Tolerant to typical artificial indoor and natural outdoor (direct sunlight) lighting conditions. Fluorescent, Incandescent, Mercury Vapor, Sodium Vapor, LED <sup>4</sup> : 450 Ft Candles (4,844 Lux) Sunlight: 8000 Ft Candles (86,111 Lux)	
Electrostatic Discharge:	Conforms to 15 kV air discharge and 8 kV of contact discharge	

# Accessories Hands-Free Intellistand™: 20-61019-01R or 20-61019-02R Regulatory Electrical Safety: Certified to UL1950, CSA C22.2 No. 950, EN60950/IEC950 EMI/RFI: FCC Part 15 Class B, ICES-003 Class B, European Union EMC Directive, Australian SMA, Taiwan EMC, Japan VCCI/MITI/Dentori. Laser Safety: CDRH Class II, IEC Class 2 Environmental: Compliant with RoHS directive 2002/95/EEC

#### Warranty

The Symbol LS2208 is warranted against defects in workmanship and materials for a period of 5 years (60 months) from date of shipment, provided that the product remains unmodified and is operated under normal and proper conditions. See full warranty for details.

1 - Roll (Tilt): Controlled by rotating the wrist clockwise or counterclockwise

2 - Pitch: Controleed by dropping or raising the wrist

3 - Skew (Yaw): Controlled by rotating the wrist from left to right or vice versa

4 - LED lighting with high AC ripple content can impact scanning performance

	Depth of Field		
Label Density	LS2208		
Paper Label	English	Metric	
Code 39 – 5 mil	2-50" - 6.00"	6.00 – 15.25 cm	
Code 39 – 7.5 mil	1.50" - 10.00"	3.80 – 25.40 cm	
Code 39 – 10 mil	1.00" - 14.25"	2.54 – 14.25 cm	
100% UPC – 13 mil	0 – 17.00″	0 – 43.00 cm	
Code 39 – 20 mil	0 – 23.00″	0 – 58.50 cm	
Code 39 – 40 mil	0 - 30.00"	0 – 76.00 cm	



motorola.com

Part number SS-LS2208-A. Printed in USA 10/12. MOTOROLA, MOTO, MOTOROLA SOLUTIONS and the Stylized M Logo are trademarks or registered trademarks of Motorola Trademark Holdings, LLC and are used under license. All other trademarks are the property of their respective owners. © Motorola Solutions, Inc. 2012. All rights reserved. Specifications are subject to change without notice.