

## 3.7kW Single-Phase Metered PDU, 208/230V (8 C13 & 2 C19), C20 / L6-20P Adapter, 12 ft. (3.66 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HV



### Highlights

- Metered single phase 16A 208/230V PDU
- 1U horizontal rackmount; Digital current meter
- C20 input with L6-20P plug adapter; 12-ft. (3.66 m) line cord
- 10 total outlets (8 C13, 2 C19)
- Reversible housing; 6.5 in. / 16.5 cm depth
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

### Package Includes

- Rackmount PDU
- C19 to L6-20P plug adapter
- Rack mounting brackets

### Features

- 16/20A single phase 208/230V Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with C20 input cable and L6-20P adapter; 12-ft. (3.66 m) line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks  
Back panel grounding lug
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

## Specifications

| OVERVIEW                       |                                      |
|--------------------------------|--------------------------------------|
| UPC Code                       | 037332159014                         |
| PDU Type                       | Metered                              |
| INPUT                          |                                      |
| PDU Input Voltage              | 208/230V                             |
| Recommended Electrical Service | Single-phase 16/20A 230/208V service |



|  |  |
|--|--|
| Maximum Input Amps                           | 16   |
| Maximum Input Amps Details                   | Agency de-rated to 16A continuous  |
| PDU Plug Type                                | NEMA L6-20P; IEC-320 C20   |
| Input Phase                                  | Single-Phase   |
| Input Cord Details                           | Includes 12 ft. / 3.6m C19 to C20 power cable and L6-20P plug adapter                                      |
| Input Cord Length (ft.)                      | 12   |
| Input Cord Length (m)                        | 3.66   |
| <b>OUTPUT</b>                                |  |
| Output Capacity Details                      | 3.68kW (230V), 3.33kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet |
| Frequency Compatibility                      | 50 / 60 Hz   |
| Output Receptacles                           | (8) C13; (2) C19   |
| Output Nominal Voltage                       | 208/230V   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Front Panel LCD Display                      | Digital display reports total PDU output current in amps   |
| <b>PHYSICAL</b>                              |  |
| Material of Construction                     | Metal  |
| Form Factors Supported                       | 1U rackmount. Includes mounting accessories for 2-4 post racks   |
| Minimum Device Depth (cm)                    | 25.40  |
| Minimum Device Depth (in.)                   | 10   |
| Minimum Device Depth (mm)                    | 254  |
| Minimum Required Rack Depth (cm)             | 24.13  |
| Minimum Required Rack Depth (inches)         | 9.5  |
| PDU Form Factor                              | Horizontal (1U)  |
| Shipping Dimensions (hwd / cm)               | 5.59 x 29.46 x 51.82   |
| Shipping Dimensions (hwd / in.)              | 2.20 x 11.60 x 20.40   |
| Shipping Weight (kg)                         | 3.40   |
| Shipping Weight (lbs.)                       | 7.50   |
| Unit Dimensions (hwd / in.)                  | 1.75 x 17.5 x 6.5  |
| Unit Dimensions (hwd / cm)                   | 2,87 x 44,4 x 16,5   |
| Unit Weight (lbs.)                           | 6.80   |
| Unit Weight (kg)                             | 3.08   |
| <b>ENVIRONMENTAL</b>                         |  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                      |  |
|--------------------------------------|--|
| Operating Temperature Range          | 0C ~ 40C (32F ~ 104F)  |
| Storage Temperature Range            | -30°C to +50°C (-22°F to +122°F)   |
| Relative Humidity                    | 5-95% non-condensing   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| TVSS Grounding                       | Rear grounding lug   |
| <b>STANDARDS &amp; COMPLIANCE</b>    |  |
| Certifications                       | Tested to IEC62368-1 (CE/EU), Class A (Emissions), NOM (Mexico), RETIE (Columbia), EAC/PCT (Russia), GOST, RoHS compliant, TAA Compliant |
| Certification Details                | Series Number(s) AGPD7985  |
| <b>WARRANTY</b>                      |  |
| Product Warranty Period (Worldwide)  | 2-year limited warranty  |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>