



## DataTraveler HyperX Predator

### The most powerful HyperX USB Flash drive combines extreme speed with high capacity.

Kingston's DataTraveler® HyperX® Predator USB Flash drive offers the fastest speeds from Kingston® and the highest capacities available in the world. Speeds up to 240MB/s read and 160MB/s write<sup>1</sup> (in USB 3.0) mean users can quickly access, edit and transfer their files and applications directly from the drive with no performance lag. Capacities up to 1TB<sup>2</sup> allow users to store their entire digital world on the DT HyperX Predator.

This prestigious drive is compliant with next-generation USB 3.0 specifications to take advantage of USB 3.0 ports in newer notebooks and desktops, and it includes a USB 3.0 dongle. It's also backwards compatible with USB 2.0 systems to maximize current investments.

DT HyperX Predator offers superior quality in a high-end design. Its zinc alloy metal casing makes it shock-resistant; all drives must pass extensive durability and shock testing. It also features a custom Kingston key ring and HyperX Valet Keychain for added value.

For added peace of mind, this drive is backed by a five-year warranty, free technical support and the legendary reliability that makes Kingston the world's independent memory leader.

- > Dramatic speed up to 240MB/s<sup>1</sup>
- > Monstrous capacity up to 1TB
- > Exclusive metal casing with stylish finish



S P E E D	
READ	WRITE
240MB/sec <sup>1</sup>	160MB/sec <sup>1</sup>

\*Based on Internal Testing

Features/specs on reverse >>

## DataTraveler HyperX Predator

### FEATURES/BENEFITS

- > **Highest capacities** — uncompromised data storage to carry your digital world on a portable USB drive
- > **Highest performance** — unparalleled speeds to save time while transferring content rich data
- > **USB 3.0** — latest USB standard guarantees backwards compatibility with USB 2.0
- > **Zinc alloy metal casing** — resilient protection for data in a cutting-edge design
- > **HyperX valet keychain** — exclusive accessory for a stylish twist to portable storage
- > **Guaranteed** — five-year warranty and free technical support for added peace of mind

### SPECIFICATIONS

- > **Capacities<sup>2</sup>** 512GB, 1TB
- > **Speed<sup>1</sup>** USB 3.0: 240MB/s read and 160MB/s write  
USB 2.0: 30MB/s read and 30MB/s write
- > **Backwards compatible** with USB 2.0
- > **Dimensions** without key ring : 2.8346" x 1.0606" x 0.8268"  
(72mm x 26.94mm x 21mm)  
with key ring : 3.4854" x 1.0606" x 0.8268"  
(88.53mm x 26.94mm x 21mm)
- > **Operating Temperature** 32°F to 140°F (0°C to 60°C)
- > **Storage Temperature** -4°F to 185°F (-20°C to 85°C)



<sup>1</sup> Speed may vary due to host hardware, software and usage.

<sup>2</sup> Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash memory Guide at [kingston.com/flashguide](http://kingston.com/flashguide).

<sup>3</sup> Requires a host device with a USB 3.0 port

THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2013 Kingston Technology Corporation. 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved.  
All trademarks and registered trademarks are the property of their respective owners. MKD-252.1US

SUPREME PERFORMANCE  
STYLISH  
PHOTOS  
VIDEO  
GAMES  
ENTHUSIAST  
SUPREME PERFORMANCE  
PHOTOS  
VIDEO  
GAMES  
ENTHUSIAST  
PHOTOS  
VIDEO  
GAMES  
ENTHUSIAST



### COMPATIBILITY TABLE

Operating System	USB 3.0 <sup>3</sup>	USB 2.0
Windows® 8	✓	✓
Windows® 7 (SP1)	✓	✓
Windows Vista® (SP1, SP2)	✓	✓
Windows XP (SP3)	✓	✓
Mac OS X v. 10.6.x +	✓	✓
Linux v 2.6.x +	✓	✓

### KINGSTON PART NUMBERS

DTHXP30/512GB

DTHXP30/1TB

**HYPER**®

