

HI DEFINITION USB "BOOM FREE" STEREO HEADSET WITH
ARRAY MICROPHONES AND 3D SURROUND SOUND RECORDING



Music
Listening



VOIP



Video
Conferencing



Computer
Gaming



Speech
Recognition



Stereo
Recording



Hi Fidelity speaker
drivers with acoustic
bass expansion



USB soundcard with
digital sample rates
for Hi definition
audio



Binaural microphone
placement for 3D
surround sound
recording



Adaptive beam forming
noise cancellation for
boom free microphone
VoIP communications

*Red represents
voice direction



(AVAILABLE IN BLACK AND WHITE)

MIC INPUT	STEREO OUTPUT
<ul style="list-style-type: none"> •A/D Conversion Resolution 16 bit •THD + N -84 dB •Supply Bias Resistor 2.2K Ohm @ 3.3VDC •Frequency Response 20-20,000 Hz •Input Range 0 - 1.25 Vrms •Dynamic Range 95 dB •Record Gain Range -6 to 33 dB 	<ul style="list-style-type: none"> •D/A Conversion Resolution 16 bit •THD + N -91 dB •Frequency Response 20-20,000 Hz •Output Load 32 Ohm •Output Voltage 1.27 Vrms <p>CONNECTION</p> <ul style="list-style-type: none"> • Standard USB 2.0 •Microphone Jack 3.5mm (Red) •Speaker Jack 3.5mm (Green)



USB HD AUDIO
ADAPTER



FOLDS FLAT



VOLUME/MUTE
CONTROL



AUDIOCOMMANDER SOFTWARE

An intuitive graphical user interface that controls the SuperBeam headsets' beam forming, noise cancellation, speaker equalization and Digital Audio Recorder with AE3D surround sound recording feature.

*AUDIO FILTERS FOR PC AND MAC