

Xerox® Phaser® 3610 and
Xerox® WorkCentre® 3615
Letter-size
Black-and-white Printer
and Multifunction Printer



Phaser® 3610 Printer and
WorkCentre® 3615
Multifunction Printer
More speed. More expandability.
Professional quality results.

xerox

Xerox® Phaser® 3610 Printer and Xerox® WorkCentre® 3615 Multifunction Printer

Produce professional-looking documents quickly. With the Phaser 3610 printer and WorkCentre 3615 multifunction printer, you'll get best-in-class speed¹, expanded capabilities and professional-looking print quality for your busy office.

Your Productive Advantage

With best-in-class¹ speed, print resolution and media capacity, your busy office can maximize workflow and minimize waiting.

- **Built for speed.** Press print and the Phaser 3610 and WorkCentre 3615 are off and running, delivering 47 ppm – the fastest black-and-white print speed in their class¹.
- **True multifunction capability.** The intuitive 4.3-inch color touch screen on the WorkCentre 3615 lets you program your next job while another is in progress.
- **Digitize...and simplify.** Easily turn cumbersome hard copy forms and documents into portable, digital files. Enjoy the added convenience of sharing your digital files automatically via email. You can even send your files to an established network folder or export them to any USB memory device.
- **Easily scan legal-sized pages.** With the WorkCentre 3615 legal-sized platen, you can scan larger pages without disassembling your bound documents.
- **Expand your capabilities.** Customize to your specific business needs with optional Wi-Fi or Productivity Kit. Plus, adding up to three additional trays lets you expand your work to fit different paper sizes and stocks, or extend media capacity during peak workloads.
- **Dependable day after day.** Enjoy quick startup and everyday operation. Plus handle device administration remotely from any networked computer's browser with Xerox® CentreWare® IS.
- **Print when and where you want.** With Apple® AirPrint™, you can print email, and important office documents directly from your mobile iOS device when connected to your office Wi-Fi network. And when working offsite, you can use Xerox® PrintBack to print documents back at the office so they are waiting for you when you return.

Powerful Capabilities Made Affordable

Even small work teams can benefit from the powerful and affordable options and capabilities delivered by the Phaser 3610 and WorkCentre 3615.

- **All-in-one savings.** The WorkCentre 3615 combines the functions of a copier, printer, scanner and fax machine into a single value-packed unit that can generate savings on energy and supplies costs.
- **Reduce your paper usage.** You'll dramatically cut your paper usage and related costs thanks to automatic two-sided printing (DN configurations). Plus, N-up printing lets you print multiple pages on one sheet – a useful option when sharing presentations.
- **Freedom, unplugged.** With optional Wi-Fi capabilities, the Phaser 3610 and WorkCentre 3615 are ready to go to work wherever they're needed, regardless of wired network infrastructure.
- **Increase your efficiency.** Extra-high capacity toner cartridges allow you spend less time loading supplies and more time getting work done.
- **Keep your information safe.** Secure Print keeps your sensitive documents out of the wrong hands by requiring users to enter a personal identification number at the device to print documents.

Attention-grabbing Print Quality

No matter what business you're in, the Phaser 3610 and WorkCentre 3615 deliver images that get your work noticed.

- **Crisp details.** Add definition and clarity to your documents with true print resolution of up to 1200 x 1200 dpi. Your printed communications never looked better.
- **Unique Xerox® EA Toner.** Fuses at a much lower temperature, reducing power consumption by up to 20% and CO₂ emissions by up to 35%, compared to conventional toner.



Phaser 3610. Print.



A full productivity toolbox in one powerful device. Choose your task. The Xerox® WorkCentre® 3615 Multifunction Printer has the right tools to deliver outstanding performance, so you're more productive and efficient every day.



1
A 60-sheet Duplex Automatic Document Feeder scans two-sided originals for copy, scan and fax jobs.

2
The WorkCentre 3615 includes a 4.3-inch touch screen with easily understood instructions and help screens to streamline walkup operations.

3
An easily accessible USB port allows users to quickly print from or scan to any standard USB memory device.

4
250-sheet output tray with tray-full sensor.

5
150-sheet Multipurpose Tray handles media sizes from 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm.

6
With the 550-sheet paper tray, standard paper capacity for the WorkCentre 3615 totals 700 sheets.

7
Up to three optional 550-sheet paper trays increase total paper capacity to 2,350 sheets.

8
Optional stand provides storage for toner cartridges, paper and other supplies.

9
Place the Phaser 3610 or WorkCentre 3615 anywhere you need it with the optional Wireless Networking Adapter.

Device Specifications		Xerox® Phaser® 3610N	Phaser 3610DN	Xerox® WorkCentre® 3615DN				
Speed	Up to 47 ppm letter / Up to 45 ppm A4							
Duty Cycle	Up to 110,000 pages / month ¹							
Processor / Memory	400 MHz / 512 MB (1 GB max. with optional Productivity Kit)		525 MHz / 1 GB					
Connectivity	10/100/1000Base-T Ethernet, High-Speed USB 2.0 Direct Print ² , Optional Wi-Fi (with Xerox® Wireless Networking Adapter)							
Print and Copy	Resolution	Up to 1200 x 1200 dpi		Print: Up to 1200 x 1200 dpi; Copy: Up to 600 x 600 dpi				
First-page-out Time (as fast as)	As fast as 6.5 seconds		Print: As fast as 6.5 seconds; Copy: As fast as 8.5 seconds					
Page Description Languages	PCL® 5e and 6 emulations, PostScript® 3™ emulation, PDF emulation							
Print Features	Booklet printing, Scaling, Fit to page, Watermarks, Custom-size pages, N-up, Toner Save mode, Secure Print, Collation, Print from USB memory device ²							
Mobile Printing	Apple AirPrint™, Xerox® PrintBack							
Scan	Speed	NA	Up to 40 images per minute (ipm)					
Destinations	NA	TWAIN/WIA Scanning via USB or Network, Scan to Computer via SMB, Scan to Server via FTP, Scan to Email with LDAP Support, Scan to USB Memory Device, WSD Scanning		JPEG/TIFF/Multipage TIFF/PDF File Formats, Up to 1200 x 1200 dpi, 24-bit Full Color Scanning, Email Address Book (up to 100 email addresses, up to 10 email group addresses), Express Scan Manager, Xerox® Scan to PC Desktop® SE Small Business Edition (1-seat license), Scan to Network Address Book (Up to 32 Destinations)				
Features								
Fax	Fax Features ³	NA	MH/MR/MMR/JBIG Compression, Reject Junk Fax, Distinctive Ring Pattern Detection, Fax Forwarding to Fax, Email and Server with/without Local Print Polling Receive, Delayed Start (up to 24 hours), Broadcast Sending (up to 200 destinations), Fax Address Book (up to 200 speed dial), Secure Fax Receive					
LAN Fax Features	Delayed Start (up to 24 hours), Broadcast Sending (up to 30 destinations), Zoom, Auto Fit, Rotation, N-up, Watermark, Phonebook (up to 500 speed dial numbers, up to 500 group dial, phonebook stored on PC)							
Security			Standard		Secure HTTPS (SSL, Secure LDAP), IPsec, 802.1X Authentication, Network Authentication, IPv6, SNMPv3, IP Filtering, Secure Print, Secure Fax Receive			
Paper Input	Standard	NA		Duplex Automatic Document Feeder (DADF): 60 sheets; Custom sizes: 5.5 x 5.5 in. (140 x 140 mm) to 8.5 x 14 in. (216 x 356 mm)				
	Optional	Multipurpose Tray: Up to 150 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm						
		Tray 1: Up to 550 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm						
		3 Additional Trays: Up to 550 sheets each; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm						
Total Capacity (std. / max.)	700 sheets / 2,350 sheets							
Paper Output	250 sheets							
Automatic Two-sided Output	N/A	Standard						
Warranty	One-year on-site warranty, earn free service coverage with Xerox eConcierge®, Xerox® Total Satisfaction Guarantee							

¹ Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; ² Available on the WorkCentre 3615 only; ³ Requires analog phone line

Device Management

Xerox® CentreWare® IS Services, CentreWare® Web, Email Alerts, Apple® Bonjour

Print Drivers

Microsoft® Windows® XP and above, 2003 Server and above; Mac OS® 10.5 and above; Red Hat® Enterprise 4, 5; Fedora® Core 14–16; SUSE® 11, 12, IBM® AIX-5®; HP-UX® 11, 11i; Solaris® 9, 10; Ubuntu®, Xerox® Global Print Driver®, Xerox® Mobile Express Driver®

Font Capability

136 PostScript Fonts; 93 PCL Fonts

Media Handling

Duplex Automatic Document Feeder: Simplex: 13 to 32 lb. bond / 50 to 125 gsm; Duplex: 13 to 32 lb. bond / 50 to 125 gsm; Multipurpose Tray: 16 lb. bond to 80 lb. cover / 60 to 216 gsm; Tray 1: 16 lb. bond to 80 lb. cover / 60 to 216 gsm; 3 Additional Trays (Optional): 16 lb. bond to 80 lb. cover / 60 to 216 gsm

Media Types

Plain, Plain Thick, Card Stock, Lightweight / Heavyweight, Rough Surface, Labels, Envelopes, Letterhead, Hole Punched

Operating Environment

Temperature: 59° to 82° F / 15° to 28° C; Humidity: 20% to 70%; Sound Power: Printing: 7.48 B(A); Standby: 5.3 B(A); Sound Pressure: Printing: 56.0 dB(A), Standby: 30 dB(A); Warm-up Time (from Power Save – UI Ready): <20 seconds, Warm-up Time from Power Save (first page printed): <20 seconds

Electrical

Power: 110–127 VAC, 50/60 Hz, 11A or 220–240 VAC, 50/60 Hz, 6A; Phaser 3610: Continuous Printing: 686 watts; Ready (Standby): 52 watts; energy Saver Mode (Sleep): 2 watts; WorkCentre 3615: Continuous Printing: 698 watts; Ready (Standby): 59 watts; energy Saver Mode (Sleep): 4 watts

Dimensions (W x D x H)

3610N/DN: 15.5 x 16.8 x 12.4 in. / 393 x 426 x 315 mm, Weight: 28.7 lb. / 13 kg; 3615: 19.5 x 19.4 x 21.6 in. / 495 x 492 x 549 mm, Weight: 47.4 lb. / 21.5 kg

Certifications

UL 60950-1:2007/CSA 60950-1-07+A1:2011, FDA/CDRH – Class 1 Laser Product, FCC Part 15, Class A, Canada ICES-003, Class A, CE marked, Low Voltage Directive 2006/95/EC, EN 60950-1, 1st Edition, EN 60825-1 – Class 1 Laser Product, EMC Directive 2004/108/EC, EN 55022, Class B, RoHS Directive 2011/65/EU, WEEE Directive 2002/96/EC, ENERGY STAR® qualified (3610DN configuration and WorkCentre 3615), Citrix Ready, Blue Angel

What Comes in the Box

- Phaser 3610 Printer or WorkCentre 3615 Multifunction Printer
- Toner Cartridge (5,900 page capacity*)
- Drum Cartridge
- Quick Installation Guide, Quick Use Guide, Driver CD, Documentation CD (User Manual, System Admin Guide)
- Power Cable
- Fax Cord (WorkCentre 3615)

Supplies Recycling Program

Consumables for the Phaser 3610 and WorkCentre 3615 are part of the Xerox Green World Alliance Supplies Recycling Program. For more information, please visit the Green World Alliance website at www.xerox.com/gwa.

Supplies

Standard Capacity Toner Cartridge: 5,900 pages*	106R02720
High Capacity Toner Cartridge: 14,100 pages*	106R02722
Extra-high Capacity Toner Cartridge: 25,300 pages*	106R02731
Drum Cartridge: 85,000 pages	113R00773

Options

550-sheet Feeder (Phaser 3610)	497K13620
550-sheet Feeder (WorkCentre 3615)	497K13630
Productivity Kit (512 MB RAM Memory) – Phaser 3610 only	497K13640
Productivity Kit (4 GB Device Memory)	497K13650
Stand	497K13660
Wireless Networking Adapter	097S04409

* Average standard pages. Declared Yield in accordance with ISO/IEC 19752. Yield will vary based on image, area coverage and print mode.

For more information, call **1-877-362-6567** or visit us at www.xerox.com/office

©2013 Xerox Corporation. All rights reserved. Xerox®, Xerox and Design®, CentreWare®, Global Print Driver®, Mobile Express Driver®, Phaser®, Scan to PC Desktop®, WorkCentre® and Xerox eConcierge® are trademarks of Xerox Corporation in the United States and/or other countries. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency (DN configurations). ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. The information in this brochure is subject to change without notice. 9/13 BR6697 36CBR-02UA

