APC Service Bypass Panel

Service Bypass Panels with a BBM switch for use with APC Smart-UPS® products up to 3kVA.

SBP1500RM





Designed to work with the world's most popular network and server UPS.

SBP2200RM



The Service Bypass Panels provide a wrap around system to allow easy maintenance of a UPS by isolating it from the critical load. The panels can be rack (2U) or wall mounted and are available with an integrated Power Distribution Unit (PDU).

- > Reliable
- > Compact
- > Easy to use
- > Break Before Make (BBM) switch

SBP3000RM





APC Service Bypass Panel

SBP1500RM

SBP2200RM

Standard features:

- Bypass/UPS switch allows the switching of the supply to the load between the incoming supply and the UPS, so the UPS can be isolated for maintenance.
- 2 Equipment Outlets allowing the SBP to support multiple loads.
- Output receptacle to feed UPS input.
- Input receptacle to receive the output from the UPS.
- 5 Input receptacle to receive the external supply (utility).
- 6 Equipment outlet circuit breaker providing outlet protection.

3 By 3 6	2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2
5	SBP3000RM
APC .	Million Marie

Product feature	SBP1500RM	SBP2200RM	SBP3000RM	
Input / Output ratings				
Nominal Input/Output voltage	120V	120V	120V	
Maximum total current	15A	20A	16A	
Switch characteristics				
Type / Transfer Time	Break Before Make (BBM) / 4ms max.			
Connections				
External supply input connection	NEMA 5-15P	NEMA 5-20P	NEMA L5-30P	
UPS Input / Output connections	NEMA 5-15P	NEMA 5-20P	NEMA L5-30P	
Load connections	NEMA 5-15R (8)	NEMA 5-15R (6)	NEMA 5-20R (4)	
		NEMA 5-20R (2)	NEMA L5-30R (1)	
Physical				
Dimensions (H x W x D)	3.5" x 17.0" x 3.0" (89.00mm x 432.00mm x 76.00mm)			
Net weight	6.5 lbs (2.95 kg)	6.5 lbs (2.95 kg)	9.8 lbs (4.45 kg)	
Conformance				
Regulatory Approvals	TUV			
Standard Warranty	2 years repair or replace			
Environmental Compliance	RoHS 7b Exemption, REACH: Contains No SVHCs			

