

Projectors





X1 Series

The Acer X1 Series projector boasts outstanding performance with rich colors, superb clarity, excellent 3D1 entertainment and a true 24p1 frame rate for a cinema-like experience. A long-lasting lamp life and practical lamp design keep maintenance costs low. And, Acer EcoProjection technology reduces power in standby mode from 5 W to 1 W, while Acer ColorSafe technology preserves the color integrity of your images even after prolonged use of the projector. [Acer Projection Calculator](#)



Lively display

Enjoy immersive visuals for games, movies and photographs beamed from the Acer X1 Series projector, certified for leading 3D1 solutions. Beyond that, advanced technologies depict optimal color balance and allow accurate image projection, even on colored walls. Plus, an exceptional resolution and high brightness project crystal-clear images.



Installation flexibility

This chic-looking projector is designed to simplify lamp replacement even when it's ceiling mounted. Correction technologies ensure the right orientation and present perfect view, while digital magnification project interesting details of your displayed content to your preferred spot. What's more, dedicated ports allow you to connect other devices to your projector.



Dynamic usability

The Empowering Key provides one-touch access to essential tools, including new-generation management that helps you create a customized startup screen. This smart projector also delivers instant projection of wide-format content without complicated resolution settings.



Eco-friendly functionality

Acer EcoProtection technology reduces power in standby mode from 5 W to 1 W to conserve energy. Other eco-conscious technologies include long-lasting lamp life, a power-saving mode, and automatic shutdown after a pre-set period without signal input.

X1110

Display Panel 0.55" DarkChip™ 3 DMD - contrast Ratio 4500:1 - brightness 2,500 ANSI Lumens (Standard) - 2,000 ANSI Lumens (ECO) - Projection Screen Size (Diagonal) 29" (73cm) ~ 300" (762cm) - Lamp life 4,500 Hours (Standard) - 6,000 Hours (ECO) - Projection Mode Front - Rear - Front-Ceiling - Rear-Ceiling - Weight 5.7 lbs (2.6 Kg)
Part Number EY.K3005.001

X110

Display Panel 0.55" DarkChip™ 3 DMD - contrast Ratio 4000:1 - brightness 2,500 ANSI Lumens (Standard) - 2,000 ANSI Lumens (ECO) - Projection Screen Size (Diagonal) 23" (58cm) ~ 300" (762cm) - Lamp life 4,000 Hours (Standard) - 5,000 Hours (ECO) - Projection Mode Front - Rear - Front-Ceiling - Rear-Ceiling - Weight 4.9 lbs (2.2 Kg)
Part Number EY.K0101.059

X1210K

Display Panel 0.55" DMD - contrast Ratio 2000:1 - brightness 2,300 ANSI Lumens (Standard) - 1,840 ANSI Lumens (ECO) - Projection Screen Size (Diagonal) 29" (73cm) ~ 300" (762cm) - Lamp life 4,500 Hours (Standard) - 6,000 Hours (ECO) - Projection Mode Front - Rear - Front-Ceiling - Rear-Ceiling - Weight 5.7 lbs (2.6 Kg)
Part Number EY.K3105.001

Prices and Specifications are subject to change without notice

