

CradlePoint COR IBR600/IBR650

INTEGRATED BROADBAND ROUTERS

IBR600/IBR650 Series – Hardened for Machine-to-Machine



COR IBR600

The CradlePoint COR Series is built for your M2M network. The CradlePoint COR is an affordable, highly featured compact router with an embedded modem designed for critical business and enterprise applications that require 24/7 connectivity.

With its compact size, sleek metal case, mounting bracket, and external mobile broadband and WiFi* (IBR600 only) antennas, CradlePoint COR is ideal for use in high-availability portable or fixed applications like ATMs, kiosks, surveillance, vehicles, etc.

CradlePoint COR provides instant network connectivity with a built-in modem – just add a mobile broadband plan or insert an activated SIM and go. It also supports traditional wired data networks like DSL, cable, or T1 for maximum network flexibility. Business-continuity features like failover/failback come standard in CradlePoint COR. When configured for failover, COR detects network failures and seamlessly switches over to a secondary WAN – keeping your network online.

CradlePoint COR provides VPN endpoint functionality, VLAN support, IPv6 support, multiple remote management methods including SMS, modem data usage management and alerts, GPIO support, USB-to-serial console passthrough support for out-of-band management of connected devices,** and the ability to be part of a PCI-DSS compliant solution. It allows for secure access to company networks for enterprise applications and provides a secure way to transmit sensitive data to and from a remote site.

EXTENDED ENTERPRISE LICENSE

CradlePoint's Extended Enterprise License provides advanced routing and security features: BGP, OSPF, RIP, VRRP, STP, NHRP, L2TP, and NEMO/DMNR.

Subscription required. See cradlepoint.com/eel for details.

THE HEART OF YOUR M2M NETWORK

- For use in 24/7 business-critical installations such as ATMs, kiosks, surveillance, vehicles, etc.
- WiFi* (IBR600) and no-WiFi (IBR650) options available
Wireless 2x2 MIMO "N" WiFi (802.11 b/g/n)*
- Increase your network availability with WiPipe™-powered automatic failover and failback
- Supports both wireless and wired Internet connections (two Ethernet ports for either LAN/LAN or WAN/LAN)
- Several models available with 4G and/or 3G support for US and international carriers
- Certified for shock and vibration in accordance with MIL STD 810G and SAE J1455 – be confident in the device's ability to survive challenging environments, including vehicles
- IPsec VPN termination (tunnel, NAT-T, and transport) with GRE support and site-to-site dynamic VPN with NHRP
- Create a custom-branded hotspot with our captive portal feature (include ToS, advertisements, etc.)*
- Standalone active GPS support on -PWD models (1x1 "N" WiFi support)*

CRADLEPOINT ENTERPRISE CLOUD MANAGER

Rapidly deploy and dynamically manage networks at geographically distributed locations with Enterprise Cloud Manager, CradlePoint's next generation application platform. Improve productivity, reduce costs, and enhance the intelligence of your network and business operations.

Subscription required. See cradlepoint.com/ecm for details.

**WiFi is only supported on IBR600 models. IBR650 models have no WiFi radio.*

***Full-size USB port with hardware version 1.3*



POWER / RESET / LAN / WAN / USB**
COR IBR600



SIM SLOT / ON-OFF / LEDs / SIGNAL STRENGTH
COR IBR600

cradlepoint.com/cor

COR IBR600/IBR650 Integrated Broadband Router

Internet Access and Device Connectivity

Includes integrated 3G/4G modem (see attached for options and specifications)

2 Ethernet LAN/WAN ports for Ethernet-enabled devices or landline Internet

Wireless 2x2 MIMO "N" WiFi (802.11 b/g/n)*

Supports up to 64 WiFi connections at a time*

Two SSIDs (with individual security, bandwidth limits, and QoS settings; separate critical traffic or create a public WiFi hotspot)*

Security

IPsec VPN (up to 5 concurrent sessions) and GRE Tunneling option, also supports passthrough VPN connections (IPsec, L2TP, PPTP)

Layer 2 Tunneling Protocol (L2TP)**

WEP, WPA, WPA2, WPA2 Enterprise with AES encryption for secure WiFi*

802.1Q VLAN support to isolate, segment and secure network traffic

SPI (stateful packet inspection) firewall and NAT (network address translation) to prevent unwanted access to connected computers

Variety of security features (URL filtering, IP & traffic filtering, DMZ, port forwarding) for safer Internet access

Advanced security mode and reporting to facilitate PCI-DSS compliance

Flexibility

First-time and advanced setup wizards for easy, swift, and secure setup

Remote management with CradlePoint Enterprise Cloud Manager

SNMP v1/2c/3, CLI over SSH, and SMS

IP passthrough support provides 3G/4G-to-Ethernet adapter

Create a WiFi hotspot with a captive portal (terms of service, ads, etc)*

Network failover support & load balancing

GPIO for additional hardware control, serial console available (USB-to-serial)

LAN/WAN affinity to assign specific LAN traffic to a WAN

Enterprise routing protocols:** BGP, OSPF, RIP

VRRP for enterprise router redundancy**

GPS NMEA GGA, VGT, and/or RMC sentence support

IPv6 support

Advanced APN management

Network Mobility (NEMO) support for session continuity in mobile networks**

Roaming control and ability to force 3G or 4G bands

Service, Support, and Warranty

CradleCare Support Agreement with 24/7 technical support, software upgrades, and advanced hardware exchange – 1, 3, and 5 year options

Limited 1 year warranty included, access to software updates and hardware repair or replacement – 3 and 5 year warranty extensions available

CradleCare Site Survey and Installation services offered for rapid deployment

IBR600/IBR650 Differences

IBR600: Includes WiFi, hotspot services/captive portal, WiFi as WAN

IBR650: WiFi excluded in order to facilitate PCI and HIPAA compliance

*WiFi-related items are only supported on IBR600 models

**Requires an Extended Enterprise License

Specifications

WAN Integrated modem, 10/100 Ethernet port, WiFi as WAN*
LAN WiFi (802.11 b/g/n)*, two 10/100 Ethernet ports (WAN or LAN)

TEMPERATURE -20°C to 60°C (-4°F to 140°F) operating modem as WAN
 -20°C to 50°C (-4°F to 122°F) operating Ethernet as WAN
 -30°C to 70°C (-22°F to 158°F) storage

RELATIVE HUMIDITY (non-condensing) 10% to 85%, operating
 5% to 90%, storage

POWER DC input steady state voltage range: 9 - 18VDC
 Recommended inline fuse for vehicle installations: 1.5A fast-blow (see vehicle best practices installation guide for details)

WiFi* (IBR600) Transmit power: 15 dBm typical for all modes; receive sensitivity: -68 dBm @ HT20 (11n), -65 dBm @ HT40 (11n), -72 dBm typical @ 54 Mbps (11g), -84 dBm typical @ 11 Mbps (11b); antennas: 5 dBi gain

SIZE 3.3-in x 4-in x 0.9-in (85mm x 102mm x 22mm)
WEIGHT 7.2 oz (200g)

CERTIFICATIONS FCC, WiFi Alliance*, Shock/Vibration (MIL STD 810G and SAEJ1455), carrier certifications (see individual SKUs for additional certifications)

What's In The Box

COR IBR600/IBR650 Integrated Broadband Router w/ metal mounting bracket

External 3G/4G mobile broadband modem antennas (2) (SMA) w/ support for GPS on auxiliary connection (some models), finger tighten only

External WiFi antennas (2) reverse SMA*, 5 dBi gain, finger tighten only

12V / 1.5A power supply w/ locking connector; GPIO/power cable available

Quick Start Guide with warranty information

Accessories

High-gain external antennas (Omni-directional, Patch, Yagi, 12" Mag-mount, 4" Mini mag-mount), GPIO/power cable, see www.cradlepoint.com/COR for more

Requirements

Internet Service and Modem Active mobile broadband plan with cellular provider or Ethernet-based Internet connection (DSL, cable, satellite, T1)

Browser (to configure router) Minimum of Firefox v2.0, Internet Explorer v7.0, Chrome, or Safari v1.0

Router Details

Security NAT, SPI, ALG, inbound filtering of IP addresses, port blocking, service filtering (FTP, SMTP, HTTP, RPL, SNMP, DNS, ICMP, NNTP, POP3, SSH), protocol filtering, WAN ping (allow/ignore), 802.1X Ethernet port security

Redundancy and Load Balancing Failover/failback with 4G, 3G, Ethernet with rule selection, advanced load balancing options (round robin, spillover, data usage, rate), WAN failure detection, VRRP**

Intelligent Routing UPnP, DMZ, virtual server/port forwarding, routing rules, NAT-less routing, wired or wireless WAN-to-LAN IP passthrough, route management, per-interface routing, content filtering, IP filtering, website filtering, per-client Web filtering, local DHCP server, DHCP client, DHCP relay, DNS, DNS proxy; ALGs: PPTP, L2TP, PPPoE passthrough, IPsec passthrough, FTP (passive), FTP (active), SIP, TFTP, IRC, MAC address filtering, Dynamic DNS, LAN/WAN affinity, VLAN support (802.1Q), STP, enterprise routing protocols: BGP/OSPF/RIP, multicast proxy support, IP setting overrides, Network Mobility (NEMO)**, IPv6

Management CradlePoint Enterprise Cloud Manager (subscription-based); web-based GUI (local management); optional RADIUS or TACACS+ username/password; remote WAN web-based management w/access control (HTTP, HTTPS); SNMP v1, v2c, & v3; CLI over SSH, SSH to serial, SSH to telnet; API; one-button firmware upgrade; modem configuration, update, and management; modem data usage w/ alerts, per-client data usage; custom AT scripting to modems; SMS

Performance & Health Monitoring WiPipe™ advanced QoS with traffic shaping, Modern Health Management (MHM) improves connectivity of modem, SSID-based priority, WAN port speed control, several levels of basic and advanced logging for troubleshooting

VPN (IPsec) Tunnel, NAT-T, and transport modes; connect to CradlePoint, Cisco/Linksys, CheckPoint, Watchguard, Juniper, SonicWall, Adtran, etc.; certificate support; Hash (MD5, SHA128, SHA256, SHA384, SHA512), Cipher (AES, 3DES, DES), support for 5 concurrent connections, GRE tunneling, multiple networks supported in a single tunnel, site-to-site dynamic VPN with NHRP**, L2TP**

GPS Active standalone GPS on -PWD models, passive standalone GPS on others; GUI mapping as well as local (LAN) or remote (WAN) server logging; NMEA GGA, VGT, and/or RMC sentence support

Ordering information

CradlePoint COR models	Modem Technology	Carrier / Location	Antenna Symbol	IBR600 (WiFi)	IBR650 (no WiFi)
LE-VZ	LTE/EVDO	Verizon	■ ▲	✓ ¹	✓
LP-AT	LTE/HSPA+	AT&T	◆ ▲	✓ ¹	✓
LP	LTE/HSPA+	Canada	◆ ▲	✓ ¹	✓ ²
LP2-EU	LTE/HSPA+	Europe	◆ ▲	✓ ¹	✓ ²
P	HSPA+	Generic	▲	✓	✓
P-INTL	HSPA+	International	▲	✓	✓
P-AT	HSPA+	AT&T	▲	✓ ²	✓
W	WiMAX	CLEAR	●		✓
E-VZ	EVDO	Verizon	▲	✓	✓
E-SP	EVDO	Sprint	▲	✓	✓
NM (no modem)	-	-	-	✓	✓

1 -PWD version available (IBR600LE-VZ-PWD, IBR600LP-AT-PWD, IBR600LP2-EU-PWD, IBR600LP-PWD2) that comes with an active GPS connection at 3.3 V and 100 mA max; IBR600LP2-EU-PWD, IBR600LP-PWD2 versions require MOQ

2 Requires minimum order quantity (MOQ)

Accessories (see CradlePoint's antenna ordering and installation guide for more antenna information)	
Part # 170587-000	Directional Patch antennas for external (outside) mounting
Part # 170588-000	Directional Yagi (Log-Periodic) antennas for external (outside) mounting
Part # 170586-000	Omni-directional antennas for external (outside) mounting
Part # 170605-000	12" Mag-mount antenna
Part # 170606-000	4" Mini mag-mount antenna
Part # 170585-000	COR 2 meter power & GPIO cable (direct wire)
Part # 170584-000	COR wall power adapter
Part # 170446-002	COR international wall power adapter (for IBR600P/IBR650P, IBR600LP2-EU)
Part # 170593-000	COR mounting bracket

CradlePoint Enterprise Cloud Manager



DEPLOY AND MANAGE THE INTELLIGENT NETWORK

Rapidly deploy and dynamically manage networks at geographically distributed locations with Enterprise Cloud Manager, CradlePoint's next generation application platform. Improve productivity, reduce costs, and enhance the intelligence of your network and business operations.

- **DEPLOYMENT** – configure devices by groups or individually, and update firmware easily with a few clicks.
- **MANAGEMENT** – monitor device statuses in real-time and set proactive alerts for optimized 3G/4G data usage and network uptime.
- **INTELLIGENCE** – view network analytics and manage security and PCI compliance.

Annual and multi-year licenses available. See cradlepoint.com/ecm for details.

CradleCare Support and Services	
CradleCare Support Agreement	When your applications are mission critical, you need the assurance that only a CradleCare Support Agreement can provide: 24-hour coverage every day, all year – including holidays. With a CradleCare Support Agreement, you will be assigned an account engineer* for consistency and follow-up on all your cases, with periodic case reviews provided. • Complete technical support, 24/7 coverage; unlimited 24-hour technical support center assistance; extended warranty; next-day parts replacement; assigned account engineer*; guaranteed response times; online video-based training sessions; software bug fixes and upgrades; advanced replacement; access to CradlePoint Enterprise Advanced Services Knowledge Base and online documentation. <i>*Account engineer for customers with 50+ sites.</i>
CradleCare Extended Warranty	This plan represents an extension of the standard 1-year CradlePoint warranty to 3 or 5 years; one-time enterprise technical support; software bug fixes; access to CradlePoint Enterprise Advanced Services Knowledge Base and online documentation; hardware repair/replacement.
CradleCare Standard 3G/4G Site Survey	Comprehensive carrier analysis for optimal performance: on-site engineer with proprietary site survey tool; 3G/4G RF testing on the major carriers; WiFi coverage testing; specified operating location; external antennas and POE testing; mapping and photos; data capture; report generation, including recommendations.
CradleCare Standard Installation	Deploy the experts to ensure a successful installation and operations: Installation Statement of Work (SOW); installation, mounting of CradlePoint equipment; installation of customer-specific equipment; cabling and mounting of antennas; extended wiring; configuration of all equipment; operational testing; report generation.

Verizon SKUs

Active GPS w/ WiFi

COR IBR600LE-VZ 4G/3G LTE/EVDO for Verizon
COR IBR650LE-VZ

Technology: LTE, EVDO Rev A

Downlink Rates: LTE 50 Mbps, EVDO 3.1 Mbps (theoretical)

Uplink Rates: LTE 50 Mbps, EVDO 1.8 Mbps (theoretical)

Frequency Bands:

- LTE Band 13 (700MHz)
- CDMA EVDO Rev A/1xRTT (800/1900 MHz)

Module Power: LTE 23 +/- 1 dBm, EVDO 24 +/- 1 dBm (typical conducted)

Module: Sierra Wireless MC7750

Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (CDMA) gain; finger tighten only; support for GPS on aux connection

GPS: standalone GPS support

Power:

idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W)
Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)

Industry Standards & Certs: FCC, WiFi Alliance (IBR600 only), Verizon, Verizon NEMO/DMNR for Primary Wireless Access

Certification Part Number: IBR600LE, IBR650LE

COR IBR600LE-VZ-PWD Active GPS w/ LTE Verizon

Technology: LTE, EVDO Rev A

Downlink Rates: LTE 50 Mbps, EVDO 3.1 Mbps (theoretical)

Uplink Rates: LTE 50 Mbps, EVDO 1.8 Mbps (theoretical)

Frequency Bands:

- LTE Band 13 (700MHz)
- CDMA EVDO Rev A/1xRTT (800/1900 MHz)

Module Power: LTE 23 +/- 1 dBm, EVDO 24 +/- 1 dBm (typical conducted)

Module: Sierra Wireless MC7750

Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (CDMA) gain; finger tighten only;

GPS: active standalone GPS support; SMA connector (with included adapter) with 3.3V @ 100mA max; WiFi reduced to 1x1 N

Power:

idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W)
Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)

Industry Standards & Certs: FCC, WiFi Alliance, Verizon, Verizon NEMO/DMNR for Primary Wireless Access

Certification Part Number: IBR600LE

COR IBR600E-VZ 3G EVDO for Verizon
COR IBR650E-VZ

Technology: EVDO Rev A

Downlink Rates: 3.1 Mbps (theoretical)

Uplink Rates: 1.8 Mbps (theoretical)

Frequency Bands:

- CDMA EVDO Rev A/1xRTT (800/1900 MHz)

Module Power: 24 +/- 0.5 dBm (typical conducted)

Module: Sierra Wireless 5728v

Module Antennas: two SMA male (plug), 2 dBi gain; finger tight is sufficient; maximum torque spec is 7 kgf-cm

GPS: standalone GPS support

Power:

idle: typical=300mA@12V (3.6W) worst case=600mA@12V (7.2W)
Tx/Rx: typical=500mA@12V (6W) worst case=1000mA@12V (12W)

Industry Standards & Certs: FCC, WiFi Alliance (IBR600 only), Verizon

Certification Part Number: IBR600E, IBR650E

AT&T SKUs

Active GPS w/ WiFi

4G

COR IBR600LP-AT COR IBR650LP-AT	4G/3G LTE/HSPA+ for AT&T
Technology: LTE, HSPA+	
Downlink Rates: LTE 50 Mbps, HSPA+ 21.1 Mbps (theoretical)	
Uplink Rates: LTE 50 Mbps, HSPA+ 5.76 Mbps (theoretical)	
Frequency Bands: - LTE Band 17 (700 MHz), Band 4 (AWS) - HSPA+/UMTS (850/1900/2100 MHz) - GSM/GPRS/EDGE (850/900/1800/1900 MHz)	
Module Power: LTE 23 +/- 1 dBm, UMTS 23 +/- 1 dBm (typical conducted)	
Module: Sierra Wireless MC7700	
Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (HSPA+) gain; finger tighten only; support for GPS on aux connection	
GPS: standalone GPS support	
Power: idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W) Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)	
Industry Standards & Certs: PTCRB, FCC, WiFi Alliance (IBR600 only), AT&T	
Certification Part Number: IBR600LP, IBR650LP	

COR IBR600LP-AT-PWD	Active GPS w/ LTE for AT&T
Technology: LTE, HSPA+	
Downlink Rates: LTE 50 Mbps, HSPA+ 21.1 Mbps (theoretical)	
Uplink Rates: LTE 50 Mbps, HSPA+ 5.76 Mbps (theoretical)	
Frequency Bands: - LTE Band 17 (700 MHz), Band 4 (AWS) - HSPA+/UMTS (850/1900/2100 MHz) - GSM/GPRS/EDGE (850/900/1800/1900 MHz)	
Module Power: LTE 23 +/- 1 dBm, UMTS 23 +/- 1 dBm (typical conducted)	
Module: Sierra Wireless MC7700	
Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (HSPA+) gain; finger tighten only	
GPS: active standalone GPS support; SMA connector (with included adapter) with 3.3V @ 100mA max; WiFi reduced to 1x1 N	
Power: idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W) Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)	
Industry Standards & Certs: PTCRB, FCC, WiFi Alliance, AT&T	
Certification Part Number: IBR600LP	

No-WiFi

3.7G

COR IBR650P-AT	HSPA+ for AT&T
Technology: HSPA+	
Downlink Rates: HSPA+ 21 Mbps (theoretical)	
Uplink Rates: HSPA+ 5.76 Mbps (theoretical)	
Frequency Bands: - HSPA+/UMTS (850/1900/2100 MHz) - GSM/GPRS/EDGE (850/900/1800/1900 MHz)	
Module Power: UMTS 23 +/- 1 dBm (typical conducted)	
Module: Sierra Wireless 8705	
Module Antennas: two SMA male (plug), 2 dBi gain; finger tighten only; maximum torque spec is 7 kgf-cm	
GPS: standalone GPS support	
Industry Standards & Certs: PTCRB, GCF-CC, FCC, AT&T	
Power: idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W) Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)	
Certification Part Number: IBR650P	

Sprint SKUs

COR IBR600E-SP
COR IBR650E-SP

3G EVDO for Sprint

Technology: EVDO Rev A

Downlink Rates: 3.1 Mbps (theoretical)

Uplink Rates: 1.8 Mbps (theoretical)

Frequency Bands:

- CDMA EVDO Rev A/1xRTT (800/1900 MHz)

Module Power: 24 +/- 0.5 dBm (typical conducted)

Module: Sierra Wireless 5728v

Module Antennas: Two SMA male (plug), 2 dBi gain; finger tighten only; maximum torque spec is 7 kgf-cm

GPS: standalone GPS support

Power:

idle: typical=300mA@12V (3.6W) worst case=600mA@12V (7.2W)

Tx/Rx: typical=500mA@12V (6W) worst case=1000mA@12V (12W)

Industry Standards & Certs: FCC, WiFi Alliance (IBR600 only), plus carrier specific certifications as required

Certification Part Number: IBR600E, IBR650E

CLEAR SKUs

No-WiFi

4G

COR IBR650W	4G WiMAX for CLEAR
Technology: WiMAX 802.16e Wave 2	
Downlink Rates: 10 Mbps peak, 6 Mbps average	
Uplink Rates: 5 Mbps peak, 1.2 Mbps average	
Frequency Band: 2500 MHz band	
Module Power: 23.5 +/- 0.5 dBm (RSU/CPE)	
Module: Beceem 250 chipset	
Module Antennas: two SMA male (plug), 5 dBi gain; finger tighten only; maximum torque spec is 7 kgf-cm	
GPS: no GPS support	
Power: idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W) Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)	
Industry Standards & Certs: FCC, CLEAR	
Certification Part Number: IBR650W	

International SKUs

4G

COR IBR600LP2-EU 4G/3G LTE/HSPA+ for Europe

Technology: LTE, HSPA+

Downlink Rates: LTE 50 Mbps, HSPA+ 21.1 Mbps (theoretical)

Uplink Rates: LTE 50 Mbps, HSPA+ 5.76 Mbps (theoretical)

Frequency Bands:

- LTE (800/900/1800/2100/2600 MHz)
- HSPA+/UMTS (900/2100 MHz)
- GSM/GPRS/EDGE (900/1800/1900 MHz)

Module Power: LTE 23 +/- 1 dBm, UMTS 23 +/- 1 dBm (typical conducted)

Module: Sierra Wireless MC7710

Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (HSPA+) gain; support for GPS on aux connection; finger tighten only

GPS: standalone GPS support

Power:

idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W)
Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)

Industry Standards & Certs: CE, WiFi Alliance, GCF-CC

Certification Part Number: IBR600LP2

Includes power adapter kit for US, EU, and UK.

COR IBR600LP 4G/3G LTE/HSPA+ for Canada

Technology: LTE, HSPA+

Downlink Rates: LTE 50 Mbps, HSPA+ 21.1 Mbps (theoretical)

Uplink Rates: LTE 50 Mbps, HSPA+ 5.76 Mbps (theoretical)

Frequency Bands:

- LTE Band 17 (700 MHz), Band 4 (AWS)
- HSPA+/UMTS (850/1900/2100 MHz)
- GSM/GPRS/EDGE (850/900/1800/1900 MHz)

Module Power: LTE 23 +/- 1 dBm, UMTS 23 +/- 1 dBm (typical conducted)

Module: Sierra Wireless MC7700

Module Antennas: two SMA male (plug), 1 dBi (LTE), 2 dBi (HSPA+) gain; finger tighten only; support for GPS on aux connection

GPS: standalone GPS support

Power:

idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W)
Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)

Industry Standards & Certs: PTCRB, FCC, IC, WiFi Alliance, Bell, Rogers, TELUS

Certification Part Number: IBR600LP

CradlePoint products with the -EU and -INTL SKUs enable and disable WiFi channels to comply with EU law. The -EU and -INTL SKUs are not legal for use in North America.

The -EU and -INTL versions come with an adapter kit for non-USA/Canada power outlets (includes US, EU, and UK options).

COR IBR600P(-INTL) HSPA+ for International COR IBR650P(-INTL)

Technology: HSPA+

Downlink Rates: HSPA+ 21 Mbps (theoretical)

Uplink Rates: HSPA+ 5.76 Mbps (theoretical)

Frequency Bands:

- HSPA+/UMTS (850/900/1900/2100 MHz)
- GSM/GPRS/EDGE (850/900/1800/1900 MHz)

Module Power: UMTS 23 +/- 1 dBm (typical conducted)

Module: Sierra Wireless 8705

Module Antennas: two SMA male (plug), 2 dBi gain; finger tighten only; maximum torque spec is 7 kgf-cm

GPS: standalone GPS support

Industry Standards & Certs: PTCRB, GCF-CC, FCC, IC, CE, WiFi Alliance (IBR600 only)

Power

idle: typical=350mA@12V(4.2W) worst case=700mA@12V(8.4W)
Tx/Rx: typical=600mA@12V(7.2W) worst case=1200mA@12V(14.4W)

Certification Part Number: IBR600P, IBR650P

3.7G

NO MODEM SKUs

The CradlePoint COR now includes versions without integrated modems:

- IBR600NM (WiFi)
- IBR650NM (no WiFi)



Attach a USB modem for 3G/4G functionality. (A full-size USB port was introduced with hardware version 1.3.)