



## Serial PCI Card

One External DB9 Port

Part No.: **158206**

---

Add one serial port with fewer conflicts.

Compatible with most RS232 peripherals, the Manhattan Serial PCI Card with one external DB9 port is an ideal solution for attaching a serial device — modems, barcode scanners, printers and more — through a single PCI card. Its high-speed 16C550/16C450 UART serial DB9 Com port fully supports PCI IRQ sharing even if accessed simultaneously to help save valuable resources for other expansion cards. Universal bus power design for 5 volts and 3.3 volts allows for greater variety of peripheral devices.

### Easy Installation

Windows XP/Server 2003/Vista/7/8 32/64-bit compatibility, plug-and-play capability and automatic IRQ and IO address selection make installation easy to help avoid configuration conflicts with other devices.

### Features:

- Adds one high-speed 16C550/16C450 UART serial DB9 Com port to desktop computers
- Maximum 115.2 kbps throughput
- Fits standard and low-profile PCI slots
- Universal bus power design for 5 V and 3.3 V
- Fully supports PCI IRQ sharing
- Automatically selects IRQ and Com address
- Three-Year Warranty

### Specifications:

#### Standards and Certifications

- CE
- FCC
- RS-232c
- PCI 2.3
- RoHS
- WEEE

#### Port Specifications

- Serial DB9 male connection
- Maximum 115.2 kbps throughput
- MosChip 9865 chipset

#### Bus Specifications

- PCI 2.3 32-bit, 33 MHz
- Supports 32/64-bit PCI slot
- 5 / 3.3V bus power

#### Physical

- Dimensions: 124 x 122 x 23 mm (4.9 x 4.8 x 0.9 in.)
- Weight: 1.8 oz. (51 g)

#### System Requirements

- Requires available punch-out expansion and PCI slots
- Windows XP/Server 2003/Vista/7/8 32/64-bit compatible

#### Package Contents

- Serial PCI Card
- Low-profile and standard brackets
- Instructions



