

5:4 IPS Monitor LED Back-lit

▶ 19MB35P-B

▶ 19MB35PM-B

19" class (19.0" measured diagonally)



Features

READER MODE NEW!

- Reader Mode provides optimal conditions for reading by reducing blue light helping to protect your eyes. With just a touch of a button, you can comfortably read on the monitor for extended periods of time.

FLICKER-SAFE NEW!

- Flicker-Safe new dimming technology is applied to minimize the flicker level that causes eye fatigue. With almost-zero flicking, watching for long periods of time is easy and comfortable.

COLOR CALIBRATED

- Experts have conducted color calibration tests at the production line for accurate color. LG IPS Monitor provides the most accurate and lifelike color for your advanced viewing pleasure.

SUPER ENERGY SAVING

- LG's Super Energy Saving Mode reduces power consumption without lowering the brightness of the monitor.

Specifications

Native Display Resolution 1280 x 1024

High Brightness 250 cd/m²

Contrast Ratio 1,000:1, 5,000,000:1 (DCR)

5MS Response Time

Built-in Speakers (19MB35PM Only)

Tilt, Swivel, Pivot, Height Adjustable, Base Detachable Stand

Vesa™ Compliant Wall Mountable

3-Year Limited Warranty Parts/Labor/Backlight


5:4 IPS Monitor

LED Back-lit

▶ 19MB35P-B


▶ 19MB35PM-B

19" class (19.0" measured diagonally)




Rear Jack Panel

19MB35P-B



19MB35PM-B



PANEL	Model	19MB35P-B	19MB35PM-B
Panel Size		19" class (19.0" measured diagonally)	
Panel Type		IPS	
Color Gamut (CIE1976)		72%	
Color Depth(Number of Colors)		16.7M colors	
Pixel Pitch(mm)		0.294(H) x 0.294(V)	
Aspect Ratio		5:4	
Native Resolution		1280 x 1024	
Brightness		250 cd/m ²	
Contrast Ratio (Typ.)		1,000:1	
Dynamic CR (DCR)		5,000,000:1	
Response Time		5ms (G to G)	
Viewing Angle		178°/178°	
Surface Treatment		Hard Coating (3H), Anti-glare	
SIGNAL (INPUT)	D-Sub	Yes	
	DVI-D	Yes	
AUDIO (INPUT)	PC Audio In	No	Yes
AUDIO (OUTPUT)	Headphone	No	Yes
SPEAKER	Type	No	2ch Stereo
	Audio Output (Watt)	No	1W x 2

SPECIAL FEATURES	Model	19MB35P-B	19MB35PM-B
DDC/CI		Yes	
HDCP		Yes	
Intelligent Auto (Auto Resolution)		Yes	
Key Lock		Yes	
Plug & Play		Yes	
Reader Mode		Yes	
Flicker Safe		Yes	
Factory Calibration		Yes	
SUPER Energy saving		Yes	
SIX Axis Control		Yes	
CABINET	Color	Black with Hairline Finish	
Monitor w/stand		16.1" x 8.3" x 18.9"	
Monitor Weight	8.4 lbs	7.7 lbs	
Monitor w/o stand		16.1" x 2.3" x 13.3"	
Monitor Weight	8.0 lbs	5.3 lbs	
Carton Dimensions		18.8" x 16.5" x 8.4"	
Packed Weight		10.6 lbs	
Base Detachable		Yes	
Tilt (Angle)		-5° (front) ~ 20°(rear)	
Swivel (Angle)		Yes	
Height (mm)		110mm range	
Pivot		Yes (0° ~90°)	
VESA™ Standard Mount Interface		75mm x 75mm	
POWER	Power Type	Built-In Power (Power only)	
Power Supply		100-240Vac, 50/60Hz	
Output (for Speaker)	No	27W(12V/2.3A)	
Power Consumption			
Normal On (EPA 6.0)	13W	15W	
Normal On (Typ.)	18W	18W	
Power Save/Sleep Mode (Max)		0.3W	
DC Off (Max)		0.3W	
FREQUENCY	Analog (H-Frequency)	30~83kHz	
	Analog (V-Frequency)	56~75Hz	
	Digital (H-Frequency)	30~83kHz	
	Digital (V-Frequency)	56~75Hz	
STANDARD CERTIFICATIONS	Safety	TCO (6.0)/UL(cUL)/TUV-GS/TUV-ERGO	
	EMC	FCC-B / CE	
	EPA (6.0)	Yes	
	ISO 13406-2 (ISO 9241-307)	Yes	
	EPEAT	Yes (Gold)	
	Windows	Yes (Windows 8)	
WARRANTY	3-Year Limited Warranty (Parts/Labor/Backlight)		
UPC	7 19192 19304 8	7 19192 19383 3	
ACCESSORIES	Power Cord		
	D-Sub		
	DVI-D		
	PC Audio	No	Yes



 **LG**
Life's Good
LGsolutions.com

LG Electronics U.S.A., Inc.
HE B2B Division
2000 Millbrook Drive
Lincolnshire, IL 60699

Customer Service: 888.865.3026
www.LGsolutions.com/support

Contact your LG Regional Sales Representative:
Channel: 800.897.8871
Hospitality: 800.228.1234
E-mail: info@LGsolutions.com

All screen images are simulated. Dimensions and weights are approximate. Design, specifications, and features subject to change without notice.

© Copyright 2014 LG Electronics USA, Inc. All Rights Reserved. "LG Life's Good" is a registered trademark of LG Corp.

ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. In Plane Switching is a trademark of LG Philips LCD Ltd. VESA is a trademark of Video Electronics Standards Association. HDMI, the HDMI logo and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing LLC.

All other product and brand names are trademarks or registered trademarks of their respective companies.