

HSM® Cutline G-Series Guillotines

G3210/G4620/G3225/G4640

Trim every document to the favored size – even photos, film and other flexible material. The HSM guillotines consist of a solid base plate with maximum cutting lengths from 12.8" up to 18.1". The high quality cutting blade, the effective integrated clamping and the precise side stop inspire even professionals.



The benefits of the guillotines of HSM:

- Precise cut due to solid cutting blade bracket
- Precise and hand guarded side stop for accurate cutting edges
- Handle ergonomically designed for optimal action of force
- High quality cutting blade made of hardened steel (except G3210)
- Solid base plate with scaling in cm/inch, angles and conventional/ special formats
- Easy to handle automatic, integrated clamping at the cutting edge with hand guard
- Stop buffer for a precise adjustment (except G3210)
- Foldable protective shield (all models)
- Easy to carry due to the grip at the side
- Easy removal of paper leftovers due to the integrated groove

Product-number	Model	Max. paper format	Cutting capacity in sheet	Cutting length in inches	Dimensions (WxDxH) in inches	Clamping method
1000911	G3210	A4	10	12.8" x 6.1"	23.8" x 11" x 2.95"	manual
1000912	G4620	A3	20	18.11" x 9"	29" x 14.25" x 4.8"	automatic
1000913	G3225	A4	25	12.8" x 9"	23.9" x 12.13" x 4.8"	automatic
1000914	G4640	A3	40	18.11" x 12.6"	29.5" x 15.98" x 5.24"	automatic

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service / 800.613.2110

Great Products, Great People.

HSM®