

HSM® Classic

411.2 document shredder

Professional series workhorse is suitable for 20-25 person office.



- Keypad for constant operation and reverse
- Hardened 100% solid steel cutters can handle the occasional paper clip or staple
- Practical storage space with optional paper trays for paper stacks
- Auto stop when container is full or door is open
- Powerful, specially adjusted motor for longer periods of use - with thermal protection for high performance
- Tried and tested closed-tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life
- Anti-Jam technology designed to easily and quickly reverse out paper in the event the machine is overloaded
- Heavy duty castors for effortless mobility
- Cross cut and micro cut shredders should be oiled regularly to maintain top working condition
- Optional auto-oiler available for cross cut and micro cut
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1566	HSM1568	HSM1569
Cutting type	Strip cut	Cross cut	Micro cut
Cutting size	1/4"	1/8" x 2"	1/32" x 7/16"
Security level DIN 32757-1	2	3	5
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-3 / O-2 / T-3 / E-2	P-6 / F-3
Cutting capacity per run in sheets	65 - 67	38 - 40	17 - 19
Cutting Speed	24 ft / min	24 ft / min	24 ft / min
Throat opening	16"	16"	16"
Motor at maximum # of sheets	2100W	2100W	2100W
Motor power (horsepower)	2.82	2.82	2.82
Voltage	115 V / 60Hz	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	37 4/5" x 23 2/5" x 18 1/2"	37 4/5" x 23 2/5" x 18 1/2"	37 4/5" x 23 2/5" x 18 1/2"
Weight	163 lbs	181 lbs	181 lbs
Shred-bin volume	38.5 gal	38.5 gal	38.5 gal
Cutting capabilities			

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downington, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®