

HSM® Classic

102.2 document shredder

Ideal device for small offices and home offices



- High quality materials for security and durability
- Automatic start/stop control
- Energy Management Control System Zero Power: consumes zero power in standby mode
- Working width is 9"
- Cross cut models can shred up to approximately 7 sheets per run; strip cut models up to 18 sheets (see specifications table below)
- Rocker switch for on/off and reverse
- Hardened 100% solid steel cutting rollers can handle occasional standard paper clips or staples
- Powerful drive for high performance; motor with protected thermal fuse
- Runs quietly
- Level indicator through inspection window in the waste container
- Tried and tested closed-tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life of shredder
- Effortless emptying of the waste container via the removable housing top
- Uses an 11 gallon capacity shred bag; Part #HSM1310



HSM part#	HSM1104	HSM1105
Cutting type	Strip cut	Cross cut
Cutting size	1/4"	5/32" x 1"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / T-2 / E-2	P-4 / F-1
Cutting capacity per run in sheets	18	7
Cutting Speed	12 ft / min	12 ft / min
Throat opening	9"	9"
Motor at max. no. of sheets	150W	150W
Motor power (horsepower)	0.20	0.20
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	19 7/10" x 14 1/3" x 10 7/10"	19 7/10" x 14 1/3" x 10 7/10"
Weight	13 lbs	14 lbs
Shred-bin volume	5.7 gal	5.7 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service / 800.613.2110

Great Products, Great People.

HSM®