

## Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: P005-12N



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 1 ft.

### Features

**C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 1-ft. (0.31 m) length helps reduce cable clutter.

### Highlights

- Recommended for powering computers, servers and other network devices
- 1-ft. (0.31 m) length allows flexibility in placing devices, while avoiding cable clutter
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 1-ft. (0.31 m) away in your data center
- Extend an existing power connection up to 1-ft. (0.31 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P005-12N Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 1-ft. (0.31 m), Black

## Specifications

OVERVIEW	
UPC Code	037332155924
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	1
Cable Length (m)	0.3
Cable Length (in.)	12
Cable Length (cm)	30.48
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>