

HSM® Powerline

FA500.3 Premium shredder

Designed for destroying large amounts of media and for continuous operation.



- Material infeed via a conveyor belt—for optimum loading and maximum throughputs.
- Practical loading table for simple loading.
- Touch-sensitive keypad for continuous and reverse operation.
- Auto stop with LED indicates when shred bin is full.
- Automatic reverse for paper jams.
- Convenient trolley with extremely sturdy, reusable shred-bin bag.
- Very sturdy gear motor with chain drive for maximum throughputs.
- Transportable on wheels.
- Anti-Jam Technology designed to easily and quickly reverse out paper in the event that the machine is overloaded.



HSM part#	HSM1991	HSM1993
Cutting type	Cross cut	Cross cut
Cutting size	9/32" x 1 1/2" – 3 5/32"	1/16" x 9/16"
Security level DIN 32757-1	3	4
Security level DIN 66399	P-3 / O-2 / T-3 / E-2	P-5 / O-4 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	500-550	120-130
Cutting speed	42 ft / min	42 ft / min
Throat opening	20"	20"
Motor at max. no. of sheets	9.2kW	9.2kW
Motor Power (Horsepower)	10	12.75
Voltage	3x208 V / 60Hz	3x208 V / 60Hz
Dimensions (H x W x D)	71" x 46" x 71"	71" x 46" x 71"
Weight	1,742 lbs	1,742 lbs
Shred-bin volume	140 gallons	140 gallons
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.