

4-Port USB DVI KVM Switch

GCS1004



- One DVI console controls up to four USB interface computers
- DVI-D KVM cable set - Includes two 44-pin Custom KVM cables (4ft & 6ft) to connect up to four computers
- Fully compliant with DVI specification (Digital only)
- Supports multi-function and wireless mouse/keyboard
- Audio enabled – full bass response provides a rich experience for 2.1 channel surround sound systems
- Video resolution – up to 1920 x 1200 @60Hz; 1080p Full HD
- Auto Scan Mode for monitoring all computers
- Multiplatform support – Windows®, Linux®, Mac, FreeBSD and Oracle® Solaris
- Console mouse port emulation/bypass feature supports most mouse drivers and multifunction mice
- Hot Pluggable - Add or remove computers for maintenance without powering down the switch
- HDCP compliant
- Video DynaSync™
- Power on Detection - Automatically switches to the next powered-on computer when the other is turned off
- Computer selection via front panel pushbuttons, hotkeys, and mouse switching function
- USB 2.0 mouse port can be used for USB hub and USB peripheral sharing
- Complete keyboard emulation for error-free booting
- Mac/Sun keyboard support and emulation
- Firmware Upgradable
- Plug & Play - No software installation required

4-Port DVI KVM Switch

This IOGEAR DVI KVM Switch GCS1004 allows users to access up to four computers from a single USB keyboard, USB mouse, and DVI monitor. It supports resolutions up to 1920 x 1200 @60Hz. With IOGEAR's DynaSync™, there is no more delay or change of video resolution when switching between or booting the computers. It also comes equipped with an audio line out and has power on detection – it will automatically switch to the next powered-on computer when the other is turned off. It also allows each computer to access any peripherals connected to the USB 2.0 port and with its audio enabled, users can listen to the audio output of each computer on one set of speakers.

The setup is quick and easy; users just need to plug the cables into their appropriate ports. There is no software to configure. Since GCS1004 intercepts keyboard input directly, it supports multiple computing platforms (PC x86 / x64, Macintosh PowerPC, and Oracle® Solaris Microsystems Sparc).


There are three convenient methods users can use to access the computers: port selection push buttons located on the unit's front panel; hotkey combinations entered from the keyboard; and mouse port-switching by simply double-clicking on the scroll wheel of a USB mouse to change the ports.



4-Port USB DVI KVM Switch

How does it work?

- Plug your keyboard and mouse into the USB console ports
- Plug your console monitor into the DVI console port and turn on your monitor
- Plug the KVM cables into their appropriate ports and power on the computers



Product Requirements

- **Console:**
 - 1 DVI display
 - 1 set of USB keyboard and mouse
 - Speakers (optional)
- **Computers:**
 - 1 DVI Port
 - 2 USB Ports
 - Audio ports (optional)
 - Computers with sound support
- **Operating Systems:**
 - Windows® XP, Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1
 - Mac OS 9 to 10.x
 - Oracle® Solaris
 - Linux®, Unix and other USB supported systems*

Package Contents

- 1 x GCS1004 4-Port USB DVI KVM Switch
- 1 x 4ft 44-pin Custom KVM Cable set
- 1 x 6ft 44-pin Custom KVM Cable set
- 1 x Power Adapter
- 1 x User Manual
- 1 x Warranty Card

*Additional drivers and support may be needed

Specifications

Function	GCS1004	Dimensions	GCS1004
Unit Dimensions			
Height			1.06" (2.69cm)
Depth			3.25" (8.26cm)
Length			7.88" (20.02cm)
Unit Package Dimensions			
Width			11.25" (28.58cm)
Height			6.94" (17.63cm)
Depth			4.00" (10.16cm)
Master Carton			
Width			12.81" (32.54cm)
Height			15.06" (38.18cm)
Depth			11.81" (30.00cm)
Master Carton Qty.			6
Weight			
Master Carton Wt.			24.50lbs (11.11kg)
Unit Pack Wt.			3.85lbs (1.75kg)
Unit Wt.			1.10lbs (0.499kg)