

DVI over Cat5/6 Extender, Box-Style Remote Repeater for Video, DVI-I Dual Link, Up to 175 ft. (53 m), TAA

MODEL NUMBER: **B140-110**



Extend and expand a Tripp Lite B140-Series DVI over Cat5 installation

Description

The B140-110 remote repeater unit can be added to your Tripp Lite B140-Series HDMI over Cat5 installation to expand the range and number of monitors. It transmits a DVI-D Single-Link signal up to 175-ft. (53.34 m) away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's N202-Series). The B140-110 is compatible with all operating systems, and is plug and play, with no software or drivers required. It features a built-in Equalization control for adjustment of the video image. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple; just insert the B140-110 repeater into the middle of your installation (Cannot be used with Passive extender kits or Passive receiver units). In the case of a B140-101X active extender kit, the built-in DVI connector on the transmitter is connected to the DVI source. It is then connected via Cat5e/6 cable to the B140-110, which is connected via Cat5e/6 cable to the B140-101X receiver unit. Finally, a monitor is connected to both the repeater and receiver units using Tripp Lite P561-Series DVI cable (not included).

- Connect up to four remote units (three repeaters and one active receiver) in a single chain, for a total of 4 displays. (An active receiver should be the last unit in a chain)
- A 1920 x 1080 @ 60Hz signal can be extended up to 125-ft. (38.1 m) from each repeater to the next unit in the channel, or a 1024 x 768 @ 60Hz signal can be extended up to 175-ft. (53.34 m)

Features

- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz

Highlights

- Insert into your Tripp Lite B140-Series DVI over Cat5 installation to expand the range and number of monitors (Cannot be used with Passive extender kits or Passive receiver units)
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 125-ft. (38.1 m), or a 1024 x 768 @ 60Hz signal up to 175-ft. (53.34 m)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Compatible with all operating systems
- Plug and play, no software or drivers required
- Features a built-in Equalization control for adjustment of the video image
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Package Includes

- B140-110 Extender / Repeater Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output:



- Extends a 1920 x 1080 @ 60Hz signal up to 125-ft. (38.1 m), or a 1024 x 768 @ 60Hz signal up to 175-ft. (53.34 m)
- Insert into your Tripp Lite B140-Series DVI over Cat5 installation to expand the range and number of monitors (Cannot be used with Passive extender kits or Passive receiver units)
- Add up to four remote units (three repeaters and one active receiver) in a single chain, for a total of 4 displays. (An active receiver should be the last unit in a chain)
- A 1920 x 1080 @ 60Hz signal can be extended up to 125-ft. (38.1 m) from each repeater to the next unit in the chain, or a 1024 x 768 @ 60Hz signal can be extended up to 175-ft. (53.34 m)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Features a built-in Equalization control for adjustment of the video image
- HDCP compatible
- Compatible with all operating systems
- Plug and play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

5V, 2A)

- Mounting Hardware
- Screwdriver for Equalization Adjustment

Specifications

OVERVIEW	
UPC Code	037332168085
Product Type	Transceiver
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
Technology	DVI; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 720P Range (ft)	175
Max 1080P Range (ft)	125
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Receiver/Transceiver Video Output	DVI-I
Signal Range (ft)	175ft @ 1024 x 768 XGA 125ft @ 1920 x 1080 UXGA
Signal Range (m)	53.34m @ 1024 x 768 XGA 38.1m @ 1920 x 1080 UXGA
Range Extension using other Tripp Lite product	175ft
Recommended Cabling	N202-Series Cat6 Patch Cable
3D Video Supported	Yes



POWER	
Power Source	Unit (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power (Green); Activity (Orange)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-01
Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / cm)	5.59 x 18.29 x 16.51
Shipping Dimensions (hwd / in.)	2.20 x 7.20 x 6.50
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
Unit Dimensions (hwd / cm)	2.54 x 11.43 x 6.35
Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Unit Packaging Type	Box
Unit Weight (kg)	0.18
Unit Weight (lbs.)	0.4
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)



Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85%, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	175
Max 480P Range (ft)	175
Max 1440 x 900 Range (ft)	175
Max 1080i Range (ft)	125
Max 480i Range (ft)	175
Max 640 x 480 Range (ft)	175
Max 800 x 600 Range (ft)	175
Max 1600 x 1200 Range (ft)	175
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
CONNECTIONS	
Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>