

Model QH8011B	
Camera	
Camera Type	Bullet
Camera Technology	SDI
Image Sensor size	1/3"
Image Sensor Type	CMOS
Image Resolution	1920 x 1080
Megapixels (digital)	2
Effective Pixels	2010 x 1092
Lens Size	3.3mm to 12mm
Angle of View	72 to 22
IR Cut Filter	Yes
Night Vision	
IR LEDS	36
Infrared Wavelength	850nM
Min Lux Illumination	0 (LEDS on)
Night Vision Range	100 ft
Additional Image Features	
Auto Iris	DC drive, close/open/auto (0-255 adjustable)
On Screen Display	No
Backlight Compensation	BLC and HLC
Electronic Shutter	1/50s-1/67,500s
Gain Control	Auto
Wide Dynamic Range	Level adjustable
Noise Reduction	3D
PTZ	
Horizontal Rotation	Not Applicable
Vertical Tilt	Not Applicable
Preset and Cruise Patterns	Not Applicable

Audio	
Audio Range	Not Applicable
Audio Microphone	Not Applicable
Connectivity	
Connector Types	SDI BNC
Other Connections	2.1mm power
Wireless	No
Remote Monitoring	
Use as Standalone	No
Compatible Mobile Devices	None
Compatible Systems	SDI DVRs
Power	
Power Supply	12V 500mA
Power Consumption	3.25W, 5.88W (LEDs ON)
Physical	
Weatherproof	Yes
IP Rating	IP66
Body Construction	Metal
Mounting Hardware	Screws
Weight	21 oz
Dimensions (WxDxH)	3 x 6.75 x 3 in (w/o bracket)
Operating Temperature	14° to 122°F

