

## Swivel/Tilt Wall Mount for 26" to 55" TVs and Monitors

MODEL NUMBER: **DWM2655M**



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWM2655M Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 26 to 55 inches.

Adjust the display's viewing angle to fit your environment and comfort level. A 120° swivel, -15° to +15° tilt and -5° to +5° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 110 lbs (49.9 kgs).

Mounting hardware included. Built-in bubble level allows accurate display leveling. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm

### Features

**Mounts Your TV or Monitor to the Wall** Fits most flat-panel televisions, monitors and other displays from 26 to 55 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Viewing angle adjusts to fit your environment and comfort level. Mounting hardware included.

**Convenient One-Touch Adjustment** 120° swivel, -15° to +15° tilt and -5° to +5° screen level adjustment capability provides comfortable viewing from multiple angles.

**Durable Metal Construction** Supports up to 110 lbs (49.9 kgs). Scratch-resistant powder-coated finish blends with any décor. Built-in bubble level allows accurate display leveling.

**VESA Compliance** Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm

### Highlights

- Fits most flat-panel displays from 26 to 55 in.
- One-touch adjustment for comfortable viewing
- 120° swivel, -15° to +15° tilt and -5° to +5° screen adjustment
- Supports up to 110 lbs (49.9 kgs)

### Package Includes

- DWM2655M Swivel/Tilt Wall Mount for 26" to 55" TVs and Monitors
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332183637
Device Compatibility	Monitor/HDTV
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 120 Swivel; -5/+5 Level Adjustment
Minimum Screen Size (in.)	26
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Minimum Screen Size (cm)	66.04
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Min/Max Arm Extension (cm)	12.5 min to 51.5 max
Min/Max Arm Extension (in.)	4.92 min to 20.27 max
Number of Displays	1
Shipping Dimensions (hwd / cm)	11.68 x 55.63 x 23.37
Shipping Dimensions (hwd / in.)	4.60 x 21.90 x 9.20
Shipping Weight (kg)	8.65
Shipping Weight (lbs.)	19.06
Unit Dimensions (hwd / cm)	20.32 x 51.5 x 19.5
Unit Dimensions (hwd / in.)	8 x 20.28 x 7.67
Unit Weight (kg)	8.37
Unit Weight (lbs.)	18.45
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cord Management	No
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Approvals	RoHS3, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>