



The VisionTek Mini DisplayPort to HDMI 2.0 Active adapter allows you to connect your mDP device to your HDMI display or projector. An HDMI cable (sold separately) is required for this Mini DisplayPort to HDMI adapter. The Mini DisplayPort to HDMI adapter transmits high-definition audio and video from your mDP device to an HDTV, display or monitor with HDMI for video streaming or gaming. The Mini DisplayPort to HDMI adapter connects and configures displays in Extended Desktop or Mirrored Displays configurations.

VisionTek's Mini DisplayPort Male to HDMI 2.0 Female Adapter supports high resolutions of up to 4K Ultra HD (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps.



PN 900691 | UPC 7 84090 03240 9



NOTE: This adapter is not bi-directional. This adapter converts mini DisplayPort to HDMI only, not vice-versa.

VisionTek Display adapters offer a quick solution for your display needs. Our adapters work across all operating systems including OS X, Linux and Windows XP, Windows 7, Windows 8, and Windows 10. Where necessary, our adapters are active for expanded compatibility with multi monitor displays, docks, and digital signage. AMD Eyefinity is also supported with our adapters. Each VisionTek adapter has been extensively tested with HP, Dell, Lenovo and Mac systems to ensure a wide range of system compatibility.

Key Features

- Supports resolutions up to 4K UHD (3840 x 2160 @ 60Hz).
- Fully HDMI 2.0 compatible.
- Connect your mDP device to a HDMI display, TV or projector. (Not reversible, only supports DP to HDMI)
- Supports AMD Eyefinity Multi-display capability.
- No O/S driver required.
- Plug 'n Play with no power input requirement.
- One Year Warranty.

All specifications are subject to change without notice. Products may not be available in all markets. The VisionTek name and design are registered trademarks of VisionTek Products, LLC. All other registered and unregistered trademarks are the property of their respective owners.

FOR MORE INFORMATION CONTACT: 1-866-883-5411 | sales@visiontek.com