

The Planar® PLL2010W is a 20" widescreen edge-lit LED LCD monitor that is a great value for home or office. This slim, space-saving monitor delivers superb performance at a great price point.



SPECIFICATION	DETAIL
Product Name	PLL2010W
Planar Part Number	997-7687-00
Viewable Size	19.5" diagonal (17.01" x 9.44")
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	170° Horizontal and 160° Vertical
Response Time (typ)	5 ms
Brightness (Typical)	250 cd/m ²
Display Type	Edge-Lit LED LCD
Display Resolution	1600 x 900
Tilt Range	-5° to +20°
Palette	16.7 million colors
Pixel Pitch	0.2715 mm
Refresh Rate	55~76 Hz (60 Hz recommended)
Dimensions (W x H x D)	18.37" x 13.43" x 7.00" (465.5 mm x 341.09 x 177.81 mm)
Dimensions without Stand	18.37" x 11.21" x 1.82" (465.50 mm x 284.70 mm x 46.33 mm)
Panel Depth	1.82" (46.33 mm)
Display Weight	5.95 lb (2.7 kg)
Display Weight (w/o stand)	5.31 lb (2.41 kg)
Shipping weight	8.16 lb (3.7 kg)

Video Inputs	Analog and Digital (DVI-D w/HDCP)
HDCP	Yes
External Connections	1 - DVI 24-pin connector; 1 - VGA D-sub 15-pin video connector
Audio Output	Not applicable. No speakers.
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	18W Typical, (0.5W standby)
Power Requirements	AC 100/240 VAC
VESA Compatible/Location	Built-in 100 mm VESA, back
Product Approvals	FCC-B, CE, UL/cUL, RoHS II
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot, discreet branding
In the Box	PLL2010W 20" LCD Monitor, Power cord, VGA cable, User's guide
UPC	8 10689 00146 1

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 9/22/2017

© Copyright 2017 Planar Systems, Inc. All rights reserved