

Digi TransPort® WR44

Enterprise Class Wi-Fi to Cellular Router

Enterprise class, commercial grade Wi-Fi to cellular router with flexible interface options ideal for mobile and transportation applications.



Overview

The Digi TransPort WR44 cellular router is an all-in-one mobile communications solution with true enterprise-class routing, security and firewall. This multifunction cellular router features a flexible design with integrated Wi-Fi access point, USB, serial and 4-port Ethernet switch, as well as a variety of configuration options including multiple serial ports (async or sync), GPS or I/O telemetry modules.

The Digi TransPort family offers an advanced routing, security and firewall feature set including stateful inspection firewall and integrated VPN. Enterprise-class protocols incorporate BGP, OSPF and VRRP+, a patented technology built upon the popular VRRP failover standard providing true auto sensing, auto failure and auto recovery of any line drop.

Digi TransPort WR44 is ideal for transportation and mobile applications. Flexible power options include 11-58 VDC barrel or molex connectors for direct integration into vehicle applications. Digi Remote Manager™ provides easy setup, configuration and maintenance of large installations of Digi TransPort devices.

Related Products



Digi TransPort® VC7400
VPN Concentrator




Digi Remote Manager™



Accessories

Application Highlight



Features/Benefits

- Enterprise class cellular routers with advanced dynamic routing, security and firewall features
- High speed cellular interfaces: GSM GPRS/EDGE/HSPA/CDMA EV-DO
- Optional integrated 802.11 b/g Wi-Fi access point and 4-port Ethernet switch
- Flexible interfaces including serial (async/sync), GPS, USB and telemetry, with flexible DC power options
- Powerful integrated end user programming
- Digi Remote Manager software for easy setup, configuration, and maintenance
- Available in industrial and commercial grade platforms



Specifications

Digi TransPort® WR44

Wireless Interfaces

WWAN**

LTE - EMEA (L1)	800/850/900/1800/1900/2100/2600MHz; 3G fall back to 850/900/1900/2100MHz and 2G fall back to 850/900/1800/1900MHz; Transfer Rate (max): 50 Mbps Up, 100 Mbps Down
LTE - North America (L5)	Multi-Carrier (Verizon, AT&T, and Sprint) 700/850/1700(AWS)/1900 MHz; 2G/3G GSM fall back to 850/900/1700AWS/1800/1900/2100MHz; 2G/3G CDMA fall back to 800/1900MHz; Transfer Rate (max): 50 Mbps Up, 100 Mbps Down
LTE - North America (L6)	700/850/1700(AWS)/1900MHz; 2G/3G fall back to 850/1900MHz; Transfer Rate (max): 50 Mbps Up, 100 Mbps Down (Coming Summer 2104)
LTE - Verizon (L8)	700/1700(AWS)MHz; No 2G/3G fall back; Transfer Rate (max): 50 Mbps Up, 100 Mbps Down (Coming Summer 2104)
LTE - Verizon (L9)	700/1700(AWS)MHz; 3G fall back to 850/1900MHz; Transfer Rate (max): 50 Mbps Up, 100 Mbps Down (Coming Summer 2104)
HSPA+ (U9)	850/900/1700 (AWS)/1900/2100MHz; Transfer Rate (max): 5.76 Mbps Up, 21 Mbps Down
GSM-R (R5)	900/1800/1900MHz (TRM-5); GPRS Class 10; Transfer rate (max): 42.8 Kbps Up, 85.6 Kbps Down
Edge (E1)	GPRS/EDGE Class 10; 850/900/1800/1900 MHz; Transfer rate (max): 236 Kbps Up/Down
CDMA EV-DO (Dx)	450 MHz; EV-DO Rev B; R-UIM support; Transfer rate (max): 14.7 Mbps Up; 5.4 Mbps Down
CDMA 1xRTT (Bx)	N/A
Connector	Ux, Lx variants: 2 x 50 Ω SMA (Center pin: female); E1, Dx, Bx variants: 1 x 50 Ω SMA (Center pin: female)
SIM Slots	2
SIM Security	SIM slot cover plate optional

Wi-Fi*

Standard	802.11b/g/n
Modes	Access point, Client and support for multiple SSID
Transmit Power	20 dBm + 1.0/-1.5 dBm
Receive Sensitivity	54 Mbps / <-72 dBm and 11 Mbps / -90 dBm
Security	Open or shared key authentication; WEP (64- and 128-bit) encryption; WPA/WPA2 with RADIUS (WPA Enterprise and pre-shared keys)
Connectors	2 x 50 Ω RP-SMA (Center pin: male)

GPS*

Channels	50
Sensitivity	-163 dB
Protocol	NMEA 0183 V2.3 sentence output; +3.3 VDC active antenna drive; NMEA stream to local serial port or over TCP/IP
Navigation	Galileo ready
Augmentation	SBAS
Cold Start	< 27 seconds TTFF (90%)
Horizontal Accuracy	< 2.5 meters (90%)
Velocity Accuracy	0.1m/s
Connector	1 x 50 Ω SMA (Center pin: female)
Additional Features	Send GPS via UDP/IP, TCP/IP (up to two destinations) or serial; Customize and/or send data using Python; GPS status query; Time source capable

Other

XBee	N/A
Satellite	N/A

Wired Interfaces

Serial

Ports	1; Expansion cards available to increase serial ports
Standard	RS-232; Expansion cards available in RS-422/485
Async/Sync	Async; Expansion cards available in sync
DTE/DCE	DCE
Signal Support	TXD, RXD, RTS, CTS, DTR, DCD, DSR, RI
Flow Control	Software (XON/XOFF), Hardware supported

* Optional hardware

** Transfer rates are network operator dependent

*** Reduced cellular performance may occur outside of -20° C to +60° C. Standard temperature power supplies may reduce temperature range.

****The enclosure rating is self-declared and has not been formally verified by an independent lab.

Specifications

Digi TransPort® WR44

Wired Interfaces	
Serial (Continued)	
COM Port Redirector	RealPort®
Connector	DB-9 female
Ethernet	
Ports	4
Standard/Physical Layer	IEEE 802.3; 10/100 Base-T
Data Rate/Mode/Interface	10/100 Mbit/s; Full or Half duplex; Auto MDI/MDIX
Connector	RJ-45
I/O	
Digital I/O	Input: 4 - 28 VDC / Output: 28 VDC 50 mA max
Connector	4-pin Molex (1 pin for input; 1 pin for I/O; the other 2 pins are used for DC power)
USB	
Ports	1
Standard	USB 2.0
Signaling	Full- or low-speed
Connector	Type A
DSL*	
Technology	VDSL2, ADSL2+, ADSL2, ADSL
Standard	Option of Annex A/M or B
Connector	RJ-11
Protocol	RFC 2364 PPPoA, RFC 2516 PPPoE, RFC 2684 Bridged Ethernet, RFC 1483 Routed IP (all either LLC or VC-Mux); PPP and ATM PVC support
Other	
Expansion Cards	Optional expansion cards available for GPS, fleet, telemetry (digital/analog I/O), ISDN/PSTN, serial and DialServ.
Software/Management	
Remote Management	Device Cloud (cloud based); Digi Remote Manager™ (user installed/managed); SNMP v1/v2c/v3 (user installed/managed)
Local Management	Web Interface (HTTP/HTTPS); CLI (Telnet, SSH, SMS, Serial port)
Management/Troubleshooting Tools	FTP, SFTP, SCP, Protocol Analyzer with PCAP for Wireshark, Event Logging with Syslog and SMTP, NTP/SNTP
Programming Tools/Environments	Python, DIA, Digi ESP™
Software Packages (See next page for details)	Enterprise
Memory	128 MB NAND Flash/64 MB DDR2 SDRAM
Power	
Input	9 – 36 VDC
Consumption	15W max, 8.5W typical
Connector	Locking barrel and 4-pin terminal block (2 pins are used for power; the other 2 pins are used for I/O).
DC Power Cord*	Locking barrel to bare wire or 4-pin connector to bare wire
DC Power Supply*	100-240 VAC 50/60 Hz; Option of standard temperature or extended temperature
Battery Backup	None

* Optional hardware

** Transfer rates are network operator dependent

*** Reduced cellular performance may occur outside of -20° C to +60° C. Standard temperature power supplies may reduce temperature range.

****The enclosure rating is self-declared and has not been formally verified by an independent lab.

Specifications

Digi TransPort® WR44

Power	
Dimensions (L x W x H)	WR44: (non-DSL variants): 5.7 in x 8.3 in x 1.6 in (145 mm x 210 mm x 40 mm) WR44: (DSL variants): 5.7 in x 10.4 in x 1.6 in (145 mm x 264 mm x 40 mm)
Weight	WR44: (non-DSL variants): 1.98 lb (0.9 kg) WR44: (DSL variants): 2.25 lbs (1 kg)
Status LEDs	Power, LAN, Wi-Fi, Serial/DSL, WWAN (Link, Act, SIM), Signal strength
Material/Rating****	Industrial (Metal)/ IP30
Mounting	Brackets for wall mount & DIN rail sold separately
Environmental	
Operating Temperature ***	Standard temp variants: 0° C to +40° C; Extended temp non-Wi-Fi variants: -40° C to +75° C; Extended temp Wi-Fi variants: -20° C to +75° C
Storage Temperature	-40° C to +85° C
Relative Humidity	0% to 95% (non-condensing) @ 25° C
Ethernet Isolation	1.5 kV RMS
Serial Port Protection (ESD)	15 kV
Hazardous (Class 1 Div 2)	N/A
Conformal Coating	N/A
Approvals	
GSM/UMTS	PTCRB, NAPRD.03, GCF-CC, R&TTE, EN 301 511
CDMA/EV-DO	CDG TIA/EIA-690, CDG TIA/EIA-98-E
Cellular Carriers	Certified by most major carriers.
Safety	UL 60950, CSA 22.2 No. 60950, EN60950
Emissions/Immunity	CE, FCC Part 15 Class B, AS/NZS CISPR 22, EN55024, EN55022 Class B (WR44 models with VDSL are Class A)
Industry	E-Marking (72/245/EEC, 2009/19/EC); Automotive Non-Immunity (2004/104/ EC, 2005/49/EC, 2005/83/EC, 2006/28/EC); (Specification for environmental tests for ground vehicle installations - covers temperature, humidity, vibration and shock)
Warranty	
Product Warranty	5 years

Software Packages		Enterprise
Protocols	Same as Standard plus Device Cloud by Etherios™; Dynamic DNS client compatible with BIND9/No-IP/DynDNS	
Security/VPN	Stateful inspection firewall with scripting, address and port translation; VPN: IPsec with IKEv1, IKEv2, NAT Traversal; SSL, SSLv2, SSLv3, FIPS 197, Open VPN client and server; PPTP, L2TP; VPN Tunnels: 5 included. Additional available: WR21 (5 max.), WR41 (50 max.), WR44/WR44R/WR44RR (200 max.); Cryptology: SHA-1, MD5, RSA; Encryption: DES, 3DES and AES up to 256-bit; Authentication: RADIUS, TACACS+, SCEP for X.509 certificates; Content Filtering (via 3rd party); MAC Address Filtering; VLAN support; Ethernet Port Isolation	
Routing/Failover	IP pass-through ; NAT, NAPT with IP Port Forwarding; Ethernet Bridging; GRE; Multicast Routing; Routing Protocols: PPP, PPPoE, RIP (v1, v2) OSPF, SRI, BGP, iGMP routing (multicast); IPv6 (firmware upgradable); RSTP (Rapid Spanning Tree Protocol); IP Failover: VRRP, VRRP+TM; Automatic failover/failback to second GSM network/Standby APN	
Other Protocols	DHCP; Dynamic DNS client compatible with BIND9/No-IP/DynDNS; QoS via TOS/DSCP/WRED	
Specialty/Legacy Protocols	RealPort®; Modbus UDP/TCP to serial; X.25 including XOT, SNA/IP, TPAD and PAD; Protocol switch*	

* Optional hardware

** Transfer rates are network operator dependent

*** Reduced cellular performance may occur outside of -20° C to +60° C. Standard temperature power supplies may reduce temperature range.


****The enclosure rating is self-declared and has not been formally verified by an independent lab.

Expansion Cards

Connector

Specification

Available for Digi TransPort WR41/WR44/WR44 R





Sync/Async Serial Port (S1)	 1 x DB-25	X.21/RS-422/RS-232 synchronous/ asynchronous serial port
Async Serial Ports (A3)	 3 x RJ-45	3x asynchronous RS-232 serial ports
PSTN (P1)	 1 x RJ-45	PSTN interface that can be used to dial out and receive calls. A PPP session is created over which IP traffic can be sent and received.
DialServ (P3)	 1 x RJ-11 (FXS)	Dial tone simulator to emulate local telco.
ISDN (I1)	 1 x RJ-45	ISDN Basic Rate Interface (BRI) which can be configured either as a TE (terminal endpoint) or as NT-1 (network termination). The option also includes an additional asynchronous serial port via a second RJ-45 port.
ISDN-U/PSTN (I3)	 1 x RJ-11, 1 x RJ-45	ISDN-U interface suitable for the USA plus PSTN interface. Can be configured for Bell-103 modulation in leased line mode as well as a normal PSTN interface.
Telemetry 1 (T1)	 1 x 14-pin terminal block	4 x Opto-isolated digital output ports and 1 x Opto-isolated digital input port. It also provides a relay I/O port, voltage monitoring port, and internal temperature monitoring. Fully programmable via Python for embedded Digi TransPort applications.
Telemetry 2 (T2)	 1 x 14-pin terminal block	4 x Analog and 4 x Digital I/O ports fully programmable via Python for embedded Digi TransPort applications.
GPS (G1)	 1x SMA	Fully-integrated GPS tracking. See main specifications area for details.
Fleet (F1)	 1 x 4-pin, 1 x 15-pin, 1 x SMA	Flexible transportation/fleet focused applications requiring CAN bus, J1708, GPS, Non-isolated digital I/O, Ignition Sense, 3-Axis accelerometer, and power control of Digi TransPort interfaces. Fully programmable via Python for embedded Digi TransPort applications.

Device Management Features

- View of all remote devices and their connection status
- Automatic registration of newly connected devices
- Remote device configuration
- Actions include device grouping and scheduling of operations
- Monitoring of user specified events
- Device statistic and report generation
- Alarm generation and alerting
- Secure access to all devices from web browser, anywhere
- Remote reboot of device and default reset
- Remote device management with Device Cloud

Easy Remote Configuration and Management




Line Art

Digi TransPort WR44 (DSL variant)



Digi TransPort WR44



Visit www.digi.com for part numbers.

DIGI SERVICE AND SUPPORT - You can purchase with confidence knowing that Digi is here to support you with expert technical support and a strong five-year warranty. www.digi.com/support

91001557
D6/814

Digi International
Worldwide HQ
877-912-3444
952-912-3444

Digi International
France
+33-1-55-61-98-98
www.digi.fr

Digi International
Japan
+81-3-5428-0261
www.digi.co.jp

Digi International
India
+91-80-4287-9887

Digi International
Singapore
+65-6213-5380

Digi International
China
+86-21-5150-6898
www.digi.cn

BUY ONLINE • www.digi.com

