HP Compaq LA1956x
19-inch LED Backlit Monitor

Get reliable power and performance in a small, ultra-slim LED display that complements desktops without sacrificing space.

Maximize productivity with a smart business monitor for the workplace with the reliable performance and fully loaded design of the HP Compaq LA1956x 19-inch LED Backlit Monitor

Absolute business performance

Keep effortless productivity flowing with a true business-class display loaded with smart features to help you do more.

- Give your employees more room to spread out, open more applications, multitask with ease, and expand graphic-intensive projects.
- Get clear, bright detail for text and graphics with a 5:4 aspect ratio that supports a variety of legacy requirements.
- Bring work to life with the incredible picture quality, fast on/off switching times, and brilliant imagery of LED backlighting.
- Transfer data quickly with convenient, side access to an integrated dual-port USB 2.0 hub.
- Get the latest digital display technology of DisplayPort and DVI-D with HDCP support plus legacy VGA connectivity.

Purpose-driven design

Improve user comfort with a completely adjustable stand. Set the monitor high or low to suit a range of user preferences, and deliver clear views from multiple angles with swivel rotation and 30° of vertical tilt. Scroll less when reading longer e-mails and web pages[1] with 90° pivot rotation. Free up valuable desk space with standard VESA mounting[2] compatibility.

Save energy, reduce your impact

Help lower your overall bottom line with a display packed with award-winning eco-certifications. Change your company's environmental story and start thinking green with a responsible design and energy-efficient components that help reduce your power consumption.

Our team is here for your team

Stand secure with your investment and gain peace of mind for the future. Rely on HP's best-in-class service and support, and relax with a standard, three-year limited warranty for parts, labor and on-site service. Get real-time chat and prompt e-mail responses from your very own team of support technicians or extend and customize your coverage through HP Care Pack Services.[3]

HP Compaq LA1956x 19-inch LED Backlit Monitor

Part number	A9S75AA
Panel type	TN (Twisted Nematic) LED Backlit LCD
Viewable image area	**48,25 cm** (19 in) diagonally measured
Viewing angle	Up to 170° horizontal/160° vertical (10:1 minimum contrast ratio)
Brightness[4]	250 nits (cd/m^2)
Contrast ratio[4]	1000:1 (typical); 1,000,000:1 (dynamic)
Response rate[4]	5 ms (on/off)
Frequency	Horizontal: 24 to 83 kHz; Vertical: 50 to 76 Hz
Native resolution	1280 x 1024 @ 60 Hz
Resolutions supported	1280 x 1024 @ 60 Hz, 1280 x 960 @ 60 Hz, 1280 x 800 @ 60 Hz, 1280 x 720 @ 60 Hz, 1024 x 768 @ 60 Hz, 800 x 600 @ 60 Hz, 640 x 480 @ 60 Hz
Input signal	Three connectors: (1) 15-pin mini D-sub analog VGA (cable included) and (1) DVI-D (cable included in select regions), and (1) Display Port (cable included in select regions)
User controls (on-screen display)	Size and positioning, contrast, brightness, clock, clock phase, selectable color temperature, serial number, mode displayed, sleep timer, input selection, factory reset, individual color contrast, full-screen resolution
Input power	Auto-Sensing, (90 to 265 VAC)
Power consumption	Maximum: 35 watts; Typical: 27 watts ; Power saving: <0.5 watts standby; <.0.5 watts off
Dimensions (h × w × d)	Packaged: **48,6 x 42,2 x 19 cm** (19.1 x 16.6 x 7.48) Unpacked w/stand: **41,7x 36,6 to 48,6 x 19,2 cm** (16.4 x 14.4 to 19.1 x 7.5 in) Head only: **41,7 x 4,7 x 34,7 cm** (16.4 x 1.8 x 13.6 in)
Weight	Packaged: **6,2 kg** (13.67 lb); Unpacked w/stand: **4,5 kg** (9.92 lb); Head only: **2,8 kg** (6.17 lb)
Base features	Tilt: -5° to + 25° vertical; Swivel: ± 180° horizontal; Pivot: 90° into portrait orientation; Height: **12 cm** (4.7 in) adjustment range
Environmental	Operating: **5° to 35° C** (41° to 95° F); Non-operating: **-20° to 60° C** (-34° to 140° F)
Options[2]	**HP LCD Speaker Bar**—Part number NQ576AA: Powered directly by the connected PC, the Speaker Bar seamlessly attaches to the monitor's lower bezel to bring full audio support to select HP flat panel monitors. Features include dual speakers with full sound range and dual external headphone jacks. Sold separately. For more information, refer to the product's QuickSpecs. **HP LCD Monitor Quick Release**—Part number EM870AA: An easy-to-use, VESA-compliant, LCD monitor mounting solution that allows you to quickly and securely attach an LCD monitor to a variety of stands, brackets, arms or wall mounts. For more information, refer to this product's QuickSpecs document. **HP USB Graphics Adapter**—Part number NL571AA: Enables connection of up to six simultaneous displays to help you boost productivity and multi-task across several open applications. Use one Adapter to bridge between a notebook or desktop PC and second monitor or use multiple Adapters to connect several displays to each other. **HP Business PC Security Lock Kit**—Part number PV606A: Attaches to the rear of the PC with a six-foot steel cable that can be used to secure a PC or peripherals such as mice, keyboards, monitors or USB security devices to protect them against unauthorized removal by physically connecting the system to an anchor point.
Certification and compliance	TCO 5.0 Displays, ISO 9241-307, CISPR Requirements, VCCI Approvals, KC and KCC (Korean) Requirements, CSA 60950-1, UL 60950-1, EN55022 Class B, CNS 13438 Class B, IEC 60950-1, China Energy Label (CEL), China MEPS, Korea MEPS (pending, Energy Boy), SmartWay – NA only - Energy logistics, EUP Lot 6 Tier 1 AS/NZS 3548 Class B Approval, "GS" Mark, TUV Approvals, GEEA, CE Marking, FCC Part 15 class B Approval, ENERGY STAR® qualified, EN55024 Class B, EN60950 -1, CUL, CCIB, CCEE, IT ECO (EDS), EPEAT® Gold (select regions)[5]
Limited warranty[3]	Protected by HP, including a 3 years parts, 3 years labor, and 3 years onsite service (3/3/3) standard limited warranty. Optional Care Pack Services are extended service contracts which go beyond your standard warranties.

1. Internet access required and sold separately.
2. Optional accessories sold separately.
3 HP Care Pack Services extend service contracts beyond the standard warranties. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts from date of hardware purchase. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at www.hp.com/go/lookuptool. Additional HP Care Pack Services information by product is available at www.hp.com/hps/carepack.
4. All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
5. EPEAT® Gold where HP registers commercial display products. See www.epeat.net for registration status in your country.