

Xerox® Phaser® 3052 and
Xerox® WorkCentre™ 3215

Letter / A4

Printer and Multifunction Printer



Xerox® Phaser® 3052 Printer and Xerox® WorkCentre™ 3215 Multifunction Printer

Work harder and smarter.

xerox 

Xerox® Phaser® 3052 Printer and Xerox® WorkCentre™ 3215 Multifunction Printer

Value-packed productivity. The ultra-compact Phaser 3052 printer and WorkCentre 3215 multifunction printer deliver the fast printing, total reliability and space-saving convenience today's individuals and small work teams depend on.

The world is your office.

- **Just the right fit.** Designed for tight spaces, both the printer and multifunction printer also feature quiet operation and built-in wireless networking for even greater office flexibility.
- **Wi-Fi Direct.** Now mobile phones, tablets and laptop computers can make a secure connection directly to the printer or multifunction printer even if you don't have an existing wireless network.
- **Save time.** The generous paper capacity of 250 sheets means you reload paper less often, and the 40-sheet Automatic Document Feeder means less time standing in front of the device.
- **Stay connected.** Both devices are network ready, including Ethernet, Wi-Fi and USB, enabling you to easily connect one user or your entire work team.
- **Enhanced mobility.** Print documents from your Apple iPhone or iPad using the built-in support for Apple® AirPrint™.

A better way of working.

- **Your office optimised.** Run your office effectively and seamlessly with the WorkCentre 3215, which combines print, copy, scan, fax and email functions in one space saving device.
- **Save more than money.** With Power Save and Toner Save modes, and the Earth Smart print driver, you can choose to spend less on electricity and consumables.
- **Xerox service and support.** Count on outstanding Xerox quality, reliability, performance, and a standard one-year warranty.

High performance.

- **Work done fast.** With a print speed as fast as 27 ppm and first-page-out time as fast as 8.5 seconds, you'll get work done quickly, letting you focus on business at hand.
- **Powerful results.** With the 600 MHz processor and standard 256 MB memory, the Phaser 3052 and WorkCentre 3215 print even the most complex jobs quickly and accurately.
- **No down time.** Reliable operation handles big print volumes with ease and keeps your business up and running no matter the workload.
- **Superior output.** Crisp 4800 x 600 dpi enhanced image quality provides you with high caliber, professional documents highlighting outstanding print quality with sharp text and crisp graphics.



Phaser 3052. Print.

A new level of possibilities. The Xerox® WorkCentre™ 3215 makes office workflow even more efficient by building on the impressive capabilities of the Xerox® Phaser® 3052 with the addition of copying, scanning, email and faxing.

WorkCentre 3215 highlights:

- The compact, quiet and lightweight WorkCentre 3215 fits perfectly in tight, busy spaces.
- Solid performance is backed by ease-of-use. The user-friendly front panel, with intuitive buttons and a two-line LCD display, make it easy to find your most-needed functions quickly.
- Save time copying and scanning multiple page documents with the 40-sheet Automatic Document Feeder.
- Colour and black and white scanning quickly converts paper into electronic documents, ready to be saved to a network, desktop folder or inserted into an application.
- Scan to Email enables sending paper documents directly to email recipients from the front panel - no need to walk back and forth from the multifunction printer to your computer.
- Comprehensive copy features include reduce/enlarge, auto background suppression, 3-level darkness control, collation, ID card copy and N-up layouts.



WorkCentre 3215. Copy. Print. Scan. Fax. Email.

Phaser 3052 Quick Facts

- Print up to 27 ppm / 26 ppm A4
- Built-in Wi-Fi connectivity
- 600 x 600 dpi; 4800 x 600 enhanced image quality
- Powerful 600 MHz processor
- Speedy first-page-out time as fast as 8.5 seconds

WxDxH:

14.5 x 13.2 x 8.4 in. / 368 x 335 x 213 mm

Weight:

16.4 lbs., 7.4 kg



WorkCentre 3215 Quick Facts

- Print and copy up to 27 ppm / 26 ppm A4
- Built-in Wi-Fi connectivity
- Print at 600 x 600 dpi; 4800 x 600 enhanced image quality
- Powerful 600 MHz processor
- Speedy, first-page-out time as fast as 8.5 seconds
- Scan up to 600 x 600 dpi in black and white and colour

WxDxH:

15.8 x 14.3 x 14.4 in. / 401 x 363 x 365 mm

Weight:

24.7 lbs., 11.2 kg

Xerox® Phaser® 3052 / Xerox® WorkCentre™ 3215

Device Specifications	Phaser 3052NI	WorkCentre 3215NI
Speed	Up to 27 ppm Letter / 26 ppm A4	
Duty Cycle ¹	Up to 30,000 pages / month	
Processor / Memory	600 MHz / 256 MB	
Connectivity	10/100Base-T Ethernet, Wi-Fi b/g/n, High-Speed USB 2.0	
Print and Copy		
Resolution	600 x 600 dpi (up to 4800 x 600 enhanced image quality)	Print: 600 x 600 dpi (up to 4800 x 600 enhanced image quality); Copy: Up to 600 x 600 dpi (up to 1200 x 1200 dpi enhanced image quality)
First-page-out Time	As fast as 8.5 seconds	Print: As fast as 8.5 seconds; Copy: As fast as 10 seconds
Page Description Languages	PCL® 5e and 6 emulations	PCL® 5e and 6 emulations, PostScript® 3™ emulation
Print Features	Toner Save Mode, Booklet Printing, Poster Printing, Skip Blank Pages, N-up Printing, Scaling, Reduce/Enlarge, Fit to Page, Watermarks, Overlays, Custom-size Pages, Print Order, Edge Enhancement, Brightness Adjustment, Contrast Adjustment, Paper Selection by Attribute, Earth Smart Driver Settings, Bidirectional Print Drivers, Job Monitoring, Store and Recall Driver Settings	
Mobile Printing	Apple® AirPrint™, Xerox® PrintBack	
Scan Features	N/A	Scan via TWAIN/WIA, Scan to PC, Scan to WSD, Scan to Email, Up to 600 x 600 dpi resolution (Up to 1200 x 1200 enhanced), Colour, Black and White, 8-bit Greyscale, PDF/JPEG/TIFF
Fax Walk-Up Fax Features ²	N/A	MH/MR/MMR/JBIG/JPEG Compression, Auto Answer, Auto Redial, Auto Reduction Broadcast Sending, Colour Fax Send, Junk Fax Filter, Distinctive Ring, Fax Address Book, Fax Forward to Fax, Secure Fax Receive, Receive Fax Forward to PC
LAN Fax Features		Broadcast Sending, Fax Address Book
Security Standard	Secure HTTPS (SSL), IPsec, 802.1X Authentication, WPA2 Personal, IPv4 and IPv6 Filtering, MAC Address Filtering, SNMPv3, USB Port Disablement	
	N/A	Network Authentication (Kerberos/SMB/LDAP), Secure LDAP, SMTP over SSL/TLS, WPA2 Enterprise, Scan to Email Authentication
Paper Input Standard	Main Tray: Up to 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm; Manual Feed Slot: 1 sheet; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm	Automatic Document Feeder (ADF): 40 sheets; Custom sizes: 5.8 x 5.8 in. x 8.5 x 14 in. / 148 x 148 mm to 216 x 356 mm; Main Tray: Up to 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm; Manual Feed Slot: 1 sheet; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm
Paper Output	150 sheets	120 sheets
Automatic Two-sided Printing	Manual	
Warranty	One-year on-site warranty (geography dependent)	

¹ Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; ² Requires analogue phone line

Device Management

Xerox® CentreWare® Internet Services, Xerox® CentreWare® Web, Email Alerts, Apple® Bonjour, Xerox® Easy Print Manager

Print Drivers

Microsoft® Windows® 8 (32-/64-bit), 7 (32-/64-bit), Vista (32-/64-bit), 2000, XP (32-/64-bit), 2003 Server (32-/64-bit), 2008 Server (32-/64-bit), 2008R2 (64-bit); Server 2012; Mac OS® 10.5-10.9; Red Hat Enterprise Linux 5, 6; Fedora 11-19; openSUSE 11.0-12.3; Ubuntu 10.04-13.04; SUSE Linux Enterprise Desktop 10, 11; Debian 5.0-7.1; Mint 13-15; Sun Solaris 9,10,11 (x86, SPARC); HP-UX 11.0, 11i v1, 11i v2, 11i v3 (PA-RISC, Itanium); IBM AIX 5.1-7.1 (PowerPC)

Font Capability

136 PostScript fonts; 111 PCL fonts

Media Handling

Automatic Document Feeder: 16 to 28 lb. bond / 60 to 105 gsm

Main Tray: 16 to 43 lb. bond / 60 to 163 gsm

Manual Feed Slot: 16 to 58 lb. bond / 60 to 220 gsm

Media Types

Plain, Thick, Thin, Envelopes, Labels, Card Stock, Cotton, Color, Prinprinted, Recycled, Bond, Archive, Transparency

Operating Environment

Temperature: 50° to 90°F / 10° to 32°C; Humidity: 20% to 80%; Sound Pressure: Printing: 50 dB(A), ADF: 53 dB(A), Standby: less than 30 dB(A); Warm-up time (from power save): As fast as 14 seconds, FPOT from power save: As fast as 14 seconds

Electrical

Power: 110-127 VAC, 50/60 Hz, 5.5A or 220-240 VAC, 50/60 Hz, 3.2A; Continuous Printing: 417 watts; Ready (Standby): 46 watts; Energy Saver Mode (Sleep): 2.0 watts

Dimensions (W x D x H)

Phaser 3052: 14.5 x 13.2 x 8.4 in. / 368 x 335 x 213 mm

Weight: 16.4 lb. / 7.4 kg

WorkCentre 3215: 15.8 x 14.3 x 14.4 in. / 401 x 363 x 365 mm

Weight: 24.7 lb. / 11.2 kg

Certifications

Listed to UL 60950-1/CSA 60950-1-07, 2nd Edition, FDA/CDRH – Class 1 Laser Product, FCC Part 15, Class B, Canada ICES-003, Class B, CE marked, Low Voltage Directive 2006/95/EC, EN 60950-1, 2nd Edition, EN 60825-1 – Class 1 Laser Product, EMC Directive 2004/108/EU, EN 55022, Class B, EN 55024, RoHS Directive 2011/65/EU, WEEE Directive 2012/19/EU, Citrix Ready, NOM, EAC (GOST), GS Mark, Green World Alliance, WHQL, Apple AirPrint, Meditech

What Comes in the Box

- Phaser 3052 Printer or WorkCentre 3215 Multifunction Printer
- Print Cartridge (1,500 page capacity*)
- Drum Cartridge (10,000 page capacity**)
- Software (Nuance Paperport and Image Retriever, ABBYY FineReader Professional with WorkCentre 3215 only)
- Power Cable, USB Cable
- Fax Cord (WorkCentre 3215)

Supplies Recycling Programme

Consumables for the Phaser 3052 and WorkCentre 3215 are part of the Xerox Green World Alliance Supplies Recycling Programme. For more information, please visit the Green World Alliance website at www.xerox.com/gwa.

Supplies

Print Cartridge: 3,000 pages*	106R02778
Dual Pack Print Cartridge: 2 x 3,000 pages*	106R02782
Drum Cartridge: 10,000 pages**	101R00474

* Average standard pages. Declared Yield in accordance with ISO/IEC 19752. Yield will vary based on image, area coverage and print mode.

** Approximate pages. Declared Yield based on letter-/A4-size 20 lb. (75 gsm) pages. Yield will vary based on media type, size, weight, orientation, and usage patterns.

For more information, visit us at www.xerox.com/office.