

HSM® shredstar

PS825S document shredder



- Casters for mobility and shared use
- Manual reversing function
- Full bag indicator
- Overload protection
- Automatic start/stop
- Separate CD cutting unit
- Anti-Jam Technology with automatic reversing function designed to quickly and easily reverse out paper in the event the machine is overloaded
- Level indicator of waste container through inspection window
- Equipped with an Energy Management Control System (EMCS) putting shredder into energy saving standby mode after 30 minutes of being idle
- 2 year warranty on parts
- Lifetime warranty on cutting heads
- Optional: Uses a 11 gallon capacity shred bag; Part #HSM1310



HSM part#	HSM1052
Cutting type	Strip cut
Cutting size	1/4"
Security level DIN 32757-1	2
Security level DIN 66399	P-2 / O-2 / T-2 / E-2
Cutting capacity per run in sheets	25
Cutting Speed	6.9 ft / min
Throat opening	9"
Motor at maximum no of sheets	200W
Motor power (horsepower)	0.27
Voltage	115 V / 60Hz
Dimensions (H x W x D)	22.8" x 15" x 12.6"
Weight	26.4 lbs
Shred-bin volume	7.1 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
www.hsmofamerica.com
 Customer Service: 800.613.2110

Great Products, Great People.

HSM®